


swissbit®

1GB & 2GB RUGGED DDR3-10600 XR-DIMM™



- Unbuffered Rugged DDR3 XR-DIMM™
- 38 x 67.5mm form factor
- Highly rugged 24pin mezzanine connector with mounting holes
- Pin-out closely aligned to 72b SO-DIMM
- Supports Error Detection & Correction (ECC)
- 1GB & 2GB module capacity in single rank
- Speed up to EP3-10600 / DDR3-1333
- Available in Standard and Industrial Temperature Grade
[0°C to +85°C] & [-40°C to +95°C] Tcase



1GB & 2GB RUGGED DDR3-10600 XR-DIMM™

Product Features

- Full DDR3 implementation with ECC support
1GB Capacity (128Mx72 array using 9 pcs 128Mx8)
2GB Capacity (256Mx72 array using 9 pcs 256Mx8)
- Module Dimensions: 67.5 x 38.0 x 7.36 mm
- Highly rugged interface to system board using pin connector and screw attachment with enhanced resistance to shock and vibration
- 240 pin Samtec BSH-120-01-X-D-A connector
- ANSI/VITA 47-2005 shock and vibration compliant
- Available in Std & Industrial Temperature Grade:
0 °C to + 85 °C Tcase
-40 °C to + 95 °C Tcase
- EP3-10600 CL9 DDR3-1333 Mbit/s downwards compatible to DDR3-1066 CL7 and DDR3-800 CL5
- 1.5 V I/O (SSTL_15 compatible)
- Consistent with DDR3 72p S0-DIMM pin definition, easing conversion from S0-DIMM implementations
- On Board Serial Presence Detect (SPD) EEPROM with Integrated Thermal Sensor
- 72 bit wide data bus supports Error Detection and Correction (ECC)
- Compliant to XR-DIMM™ eXtremeRugged Memory Specification from SFF-SIG Small Form Factor Special Interest Group
www.sff-sig.org

	Part Number	Storage Capacity	Speed	CAS Latency	Module Configuration	DRAM Manufacturer
1GB XR-DIMM	SGV01G72A1BG1SA-CCRT	1GB	1333 Mb/s EP3-10600	CL9	128Mx72	Samsung
2GB XR-DIMM	SGV02G72A1BD1SA-CCRT	2GB	1333 Mb/s EP3-10600	CL9	256Mx72	Samsung

PART NUMBER SCHEME

SWISSBIT SALES LOCATIONS WORLDWIDE

EMEA / APAC

Swissbit AG
Industriestrasse 4
CH-9552 Bronschhofen
Switzerland

Tel. +41 71 913 03 03
Fax +41 71 913 03 15
industrial@swissbit.com

North & South America

Swissbit NA
1202 E Winding Creek
Eagle, Idaho 83616
USA

Tel. +1 208 938 4525
Fax +1 914 935 9865
sales@swissbitna.com

Japan

Swissbit Japan Inc.
4F, 2-40-16 Umesato
Suginami-ku, Tokyo 166-0011
Japan

Tel. +81 3 33 17 12 11
Fax +81 3 33 17 12 22
industrial@swissbit.co.jp