

# M12 Connectivity Quick Ship



## M12 4-Pin Black PVC Cable, 4 x 22 Awg



	Length	Wiring	Part Number	Model
Female Single Ended Straight	2 m (6.5 ft)	 1 = Brown 2 = White 3 = Blue 4 = Black	814936	BC-M12F4-22-2
	5 m (16.4 ft)		814937	BC-M12F4-22-5
	10 m (32.8 ft)		814939	BC-M12F4-22-10
Female Single Ended Right-Angle	2 m (6.5 ft)		814957	BC-M12F4A-22-2
	5 m (16.4 ft)		814958	BC-M12F4A-22-5
	10 m (32.8 ft)		814960	BC-M12F4A-22-10
Double-Ended Straight/Straight	1 m (3.2 ft)		814948	BC-M12F4-M12M4-22-1
	2 m (6.5 ft)		814949	BC-M12F4-M12M4-22-2
	5 m (16.4 ft)		814952	BC-M12F4-M12M4-22-5
Double-Ended Female Straight/Male Right-Angle	2 m (6.5 ft)		814954	BC-M12F4-M12M4-22-10
	5 m (16.4 ft)		814968	BC-M12F4-M12M4A-22-2
	10 m (32.8 ft)		814969	BC-M12F4-M12M4A-22-5
	10 m (32.8 ft)	814970	BC-M12F4-M12M4A-22-10	



## M12 5-Pin Black PVC Cable, 5 x 22 Awg



	Length	Wiring	Part Number	Model	
Female Single Ended Straight	2 m (6.5 ft)	 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray	815138	BC-M12F5-22-2	
	5 m (16.4 ft)		815139	BC-M12F5-22-5	
	10 m (32.8 ft)		815141	BC-M12F5-22-10	
Double-Ended Straight/Straight	1 m (3.2 ft)			815148	BC-M12F5-M12M5-22-1
	2 m (6.5 ft)			815149	BC-M12F5-M12M5-22-2
	5 m (16.4 ft)			815150	BC-M12F5-M12M5-22-5
	10 m (32.8 ft)	815152		BC-M12F5-M12M5-22-10	



## M12 8-Pin Black PVC Cable, 8 x 24 Awg



	Length	Wiring	Part Number	Model	
Female Single Ended Straight	2 m (6.5 ft)	 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red	815166	BC-M12F8-24-2	
	5 m (16.4 ft)		815167	BC-M12F8-24-5	
Double-Ended Straight/Straight	2 m (6.5 ft)			815174	BC-M12F8-M12M8-24-2
	5 m (16.4 ft)			815175	BC-M12F8-M12M8-24-5



Banner Engineering Corp.

1-888-373-6767 • [www.bannerengineering.com](http://www.bannerengineering.com)

© 2025 Banner Engineering Corp. Minneapolis, MN USA