

## Cooling Fan & Blower for Telecommunication

■ PWM speed control / FG / RD function is option.



Size	Model	Rating Voltage (VDC)	Rating Current (Amp)	Power Consumption (Watt)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H <sub>2</sub> O)	Noise (dBA)
40X40X20 mm	PSD1204PKB3-A(2).Z.GN	12	0.140	1.68	11000	11.8	0.56	40.0
40X40X48 mm	PSD1204PJBX-A(2).Z.GN	12	1.470	17.64	18000 (IN) 17000 (OUT)	29.8	2.65	66.2
60X60X25 mm	PSD1206PTBX-A(2).U.Z.GN	12	0.355	4.30	8100	36.4	0.64	48.2
60X60X38 mm	PSD1206PMBX-A(2).Z.GN	12	1.500	18.00	14000	69.5	1.98	62.9
60X60X38 mm	PSD4806PMB1-A(2).Z.GN	48	0.250	12.00	12000	56.8	1.46	59.4
80X80X15 mm	PSD1208PHB1-A(2).Z.GN	12	0.194	2.30	3300	39.9	0.18	38.7
80X80X25 mm	PSD1208PTBX-A(2).U.Z.GN	12	0.490	5.90	6200	70.4	0.57	51.3
80X80X38 mm	PSD4808PMBX-A(2).Z.GN	48	0.460	22.10	8000	112.0	1.31	60.5
92X92X38 mm	PSD1209PMBX-A(2).Z.GN	12	2.200	26.40	9500	151.4	2.05	54.3
97X94X33 mm	PSB1297PYB1-AY(2).Z.GN	12	0.560	6.70	3600	26.7	0.76	67.3
120X120X25 mm	PSD1212PTB1-A(2).Z.GN	12	0.825	9.90	4500	147.7	0.62	54.9
120X120X32 mm	PSD1212PLBX-A(2).Z.GN	12	1.850	22.20	4600	189.6	0.79	60.6
120X120X25 mm	PSD4812PTB1-A(2).Z.GN	48	0.218	10.50	4500	147.7	0.62	54.9
120X120X32 mm	PSB1212PLB1-AY(2).Z.GN	12	0.755	9.06	2800	38.7	1.14	55.8
120X120X38 mm	PSD1212PMBX-A(2).Z.GN	12	3.000	36.00	6000	226.5	1.20	65.5
170X150X51 mm	PSD24H0AZBX-A(2).Z.GN	24	2.300	55.20	5800	387.1	1.23	69.0
170X150X51 mm	PSD48H0AZBX-A(2).Z.GN	48	1.550	74.40	6200	417.2	1.55	70.9

- Specifications are subject to change without notice. Specifications in this catalog are for reference. For more product information, please contact your SUNON sales representative.