



xsens

MTw Awinda & Awinda station

Wireless motion tracker
& Data receiver

Specifications MTw™ Awinda™

MTw Awinda

Highly accurate, small and lightweight 3D human wireless motion tracker.
Used in a body area network, these portable and unobtrusive wireless trackers are ideal for developing customized wearable solutions.

Tracker placement
Easy fastening with Velcro straps

Internal sampling rate
1000 Hz

Latency
30 ms

Buffer time (retransmissions)
10 s

Battery life (continuous use)
6 Hours

Dimensions Tracker
47 x 30 x 13 mm
(1.85 x 1.18 x 0.51 in)

Weight
16 g (0.56 oz.)

Operating temperature range
0°C - 50°C

Static Accuracy (Roll/Pitch)
0.5 deg RMS

Static Accuracy (Heading)
1 deg RMS

Dynamic Accuracy (Roll/Pitch)
0.75 deg RMS

Dynamic Accuracy (Heading)
1.5 deg RMS



Communication

Range	Awinda station	Awinda dongle
Open space	Up to 50 m (165 ft.)	Up to 20 m (65 ft.)
Office space	Up to 20 m (65 ft.)	Up to 10 m (33 ft.)
Wireless protocol	Xsens patented Awinda protocol	
Receiver	Awinda Station / Awinda Dongle	

Tracker components

	Angular velocity	Acceleration	Magnetic field
Dimensions	3 axes	3 axes	3 axes
Full scale	± 2000 deg/s	± 160 m/s	± 1.9 Gauss

¹The patented Awinda protocol ensures highly accurate time synchronized data sampling (within ≤10 μs) in all connected MTw's, which is essential for accurate joint angles.



Awinda station

The Awinda Station can receive data from up to 20 MTw's simultaneously
Data from multiple MTw's is time-synchronized to within 10μs
Charges up to 6 MTw's simultaneously.

Specifications Awinda™ station

Operating temperature range

Ambient	-25°C - 80°C
Specified Performance	0°C - 65°C
Specifications for non-condensing environment. Avoid wet and humid conditions	

Power Supply

EU/US/UK power adapters provided

Communication

Awinda Station	PC Interface: USB
----------------	-------------------

Physical Properties

Dimensions (without antenna)	148 x 104 x 31.9 mm (5.8 x 4.1 x 1.3 in)
Weight	200g (7 oz.)

Synchronization with third party devices

4 BNC connectors	- 2 for sync in - 2 for sync out
TTL pulses	0-3.3V levels
Software configurable	

Wireless update rates

1 MTw	120 Hz
-------	--------

Awinda Dongle Specifications (Miniature version of Awinda Station)



Dimensions	20.4 x 45 x 10.6mm (0.8 x 1.8 x 0.4 in)
Weight	8g (0.28 oz.)

² Max. number of connected MTw's supported

ABOUT XSSENS

Xsens is the leading innovator in 3D motion tracking technology and products. Its sensor fusion technologies enable a seamless interaction between the physical and the digital world in applications such as industrial control and stabilization, health, sports and 3D character animation. Clients and partners include Electronic Arts, NBC Universal, Daimler, Autodesk, ABB, Siemens and various other leading institutes and companies throughout the world. Xsens is part of mCube, the provider of the world's smallest MEMS motion sensors, key enablers for the Internet of Moving Things. Xsens has offices in Enschede, Los Angeles, Shanghai and Hong Kong.

Visit xsens.com/distributors for an overview of Xsens' worldwide distributor network



Xsens Netherlands

Xsens Technologies B.V.
P.O. Box 559
7500 AN Enschede
The Netherlands

Phone: +31 88 97367 00
Fax: +31 88 97367 01
Email: info@xsens.com

Xsens North America Inc.

101 N. Pacific Coast Hwy,
Suite 306
El Segundo, CA 90245
North America

Phone: 310-481-1800
Fax: 310-416-9044
Email: info@xsens.com

Xsens AsiaPac

Unit 208, Bldg 16W
Hong Kong Science Park
Shatin
Hong Kong

Phone: +852 3618 9080
Fax: +852 3705 8994
Email: info@xsens.com

Building 1, 2nd Floor
No.333 Huangqing Road
PRC 201899
Shanghai

Phone: +86 021 31760067
Fax: +86 021 31760067
Email: china@xsens.com

© 2005–2018, Xsens Technologies B.V. All rights reserved. Information in this document is subject to change without notice. Xsens, MTi and MTi-G are registered trademarks or trademarks of Xsens Technologies B.V. and/or its parent, subsidiaries and/or affiliates in The Netherlands, the USA and/or other countries. All other trademarks are the property of their respective owners

Unless stated otherwise, all specifications are typical. Specifications subject to change without notice.
© Xsens, August 2018



xsens

www.xsens.com