

aquanex® Micro USB

USB3505

- Water-and-dust-proof
- Full IP67 Rating
- Metal Injection Moulded single-piece stainless steel shell



Vital Stats

Interface

USB Micro B

No. of Contacts

5

USB Specification

2.0

IP Rating

IP67

Mating Cycles

10,000

Profile Above PCB

4.90mm

- Horizontal top-mounted socket
- Silicone gasket to seal against panel
- USB Micro B interface with 5 contacts
- 4 through-hole shell stakes
- Metal Injection Moulded shell

Applications

Pool & Spa Controls
Hydroponics
Home Security
Consumer Electronics
Medical Equipment



GCT

gct.co/connector/usb3505