

**SPECIFICATIONS PARAMETERS VALUES UNITS RATED INPUT POWER** W MAX INPUT POWER W 5  $8 \pm 15\%$ **IMPEDANCE** OHM OUTPUT SPL @ 1W/0.5M dBA  $85 \pm 3$ (AT 0.8, 1.0, 1.2, 1.5kHz) **DISTORTION (MAX.)** 5% RESONANT FREQUENCY 450 ± 20% Hz FREQUENCY RANGE Fo ~ 20,000 Hz **HOUSING MATERIAL METAL CONE MATERIAL PAPER** MAGNET MATERIAL Nd-Fe-B **OPERATING TEMPERATURE** °C -10 ~ +50 grams **WEIGHT** 35

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

REVISION HISTORY										
LTR	DESCRIPTION	DATE	APPROVED							
-	RELEASED FROM ENGINEERING	6/20/2006								
Α	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	1/20/2009	B.R.							
В	UPDATE PARAMETERS AND DIMENSIONS	5/25/2017	M.L.							







Drawn Date

## **NOTES:**

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

UNLESS OTHERWISE SPECIFIED:	SIZE
DIMENSIONS ARE IN MILLIMETERS,	SIZE
TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	A3
AS07008P0	 

Designed by Date Che			скеа ру	Date	Approved by	Date		Drawn Date	
J.D.	6/20/2006	0/2006 E		6/20/2006	B.R.	6/20/20	006	L/20/2009	
pul.			AS07008PO-2-R						
			Chapkar			Edition	Sheet		
TY)	addic	inc	1	Speaker			_	1 / 1	

a projects unlimited compar