

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Waber-by-Tripp Lite 6-Outlet (77.6mm center-tocenter spacing) Industrial Power Strip, 6-ft. Cord

MODEL NUMBER: 6SPDX



Description

The Waber-by-Tripp Lite 6SPDX Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.520in. center-to-center spacing, 6-foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 6SPDX ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige color scheme. PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

• Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount

applications

- Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-foot AC line cord

Specifications

OVERVIEW	
UPC Code	037332108234

Highlights

- 6 outlets
- 6-ft. cord
- 12.5-in. length
- Lighted master switch
- All-metal housing

Package Includes

- 6SPDX Power Strip
- Warranty information
- Instruction manual



OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	1800	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Outlet Spacing	1.520 in.	
Outlet Orientation	Single row of 6	
Right-Angle Outlets	No	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A 120V	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	6	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
USER INTERFACE, ALERTS & CONTROLS		
Switches	Lighted combination switch / circuit breaker	
PHYSICAL		
Anti-Microbial Protected	No	
Color	Beige	
Color (AC Line Cord)	Beige	
Integrated Keyhole Mounting Slots	Yes	
Keyhole Slot Mounting Measurement (Center to Center)	203.20mm	
Material of Construction	Metal	
Outlets Measurement (Center to Center)	77.60mm	
Receptacle Color	Beige	
Shipping Dimensions (hwd / cm)	5.72 x 15.24 x 36.20	
Shipping Dimensions (hwd / in.)	2.25 x 6.00 x 14.25	
Shipping Weight (kg)	1.04	
Shipping Weight (lbs.)	2.30	



Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8	
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5	
CERTIFICATIONS		
UL1363 (Power Tap)	UL1363	
Canada	cUL	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies