

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com



Power It! 6-Outlet Safety Power Strip, 6-ft. Cord & Clip, Safety Covers

MODEL NUMBER: TLM626NS



Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 6 ft. cord
- · Rugged metal case

Package Includes

- TLM626NS Safety Power Strip
- 4 safety covers
- · Owner's manual

Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 6 ft. grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

Features

- 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more.
- Convenient transformer outlets
- A 6 ft. grounded cord with integrated cord clip reaches distant outlets.
- A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting
- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

Specifications



OVERVIEW		
UPC Code	037332140173	
OUTPUT		
Frequency Compatibility	60 Hz	
Output (Watts)	1800	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	Combo power switch and circuit breaker	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Single row	
Right-Angle Outlets	Yes	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V, 15A	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	6	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
PHYSICAL		
Shipping Dimensions (hwd / in.)	13.70 x 2.00 x 4.70	
Shipping Dimensions (hwd / cm)	34.80 x 5.08 x 11.94	
Shipping Weight (lbs.)	1.60	
Shipping Weight (kg)	0.73	
Unit Dimensions (hwd / in.)	12.23 x 2.30 x 1.28	
Unit Dimensions (hwd / cm)	31.06 x 5.84 x 3.25	
Unit Weight (lbs.)	1.34	
Unit Weight (kg)	0.61	
Material of Construction	All-metal	
Integrated Keyhole Mounting Slots	Yes	
Receptacle Color	Black	
Color (AC Line Cord)	Yellow	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Yellow; Black	
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between standard and transformer outlets = 45mm	
Keyhole Slot Mounting Measurement (Center to Center)	225mm	
Anti-Microbial Protected	No	
CERTIFICATIONS		
Approvals	cULus, RoHS	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies