



Quality Products. Service Excellence.

## Liquid-Tight, Strain Relief Cordgrips 1427CG Series



We've introduced two new lines of cord grips which are available made from nylon (**1427NCG**) or nickel-plated brass (**1427BCG**) and in a wide variety of sizes.

### Features

- Black nylon, liquid-tight cordgrip.
- Used where cable is entering or leaving an enclosure.
- Accepts a wide range of cable diameters due to large opening and highly flexible strain relief elements, together with a TPE sealing ring.
- The strain relief elements tighten in a circular sequence on the sealing ring to give outstanding strain relief without twisting or damaging the cable.
- Use the cordgrip with the smallest maximum diameter that will fit your application (see table below).
- Nylon locknut included (as shown).
- Designed to meet NEMA Type 4, 4X, 6, 6P, 12 & 13 - Protection to IP68.
- UL94-V2 flammability rating.
- UL, CSA & VDE listed.
- For a wider selection of cord grips, try our updated product lines:
  - **1427NCG** - nylon cord grips
  - **1427BCG** - brass cord grips

Part No.	Use With Wire Diameter		Mounting Hole Diameter
	Min	Max	
<b>1427CG7</b>	0.10	0.26	0.49
<b>1427CG9</b>	0.14	0.32	0.60
<b>1427CG13</b>	0.24	0.47	0.80
<b>1427CG16</b>	0.35	0.55	0.89
<b>1427CG21</b>	0.51	0.71	1.11

Tags: cord grips

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.