

## Cat5e 350MHz Snagless Molded Patch Cable (RJ45 M/M) - White, 3-ft.

MODEL NUMBER: N001-003-WH



### Description

Tripp Lite's 3-ft. White snagless category 5e (Cat5e) patch cable has 2 snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Standard, non-snagless category 5e patch cables are also available (N002-Series).

### Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 3-ft. color: White connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002-Series)
- Also available - Cat6 cables (N201-Series)

## Specifications

### Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

### System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

### Package Includes

- 3-ft. White Snagless Cat5e Patch Cable



| OVERVIEW                            |                           |
|-------------------------------------|---------------------------|
| UPC Code                            | 037332172471              |
| INPUT                               |                           |
| Cable Length (ft.)                  | 3                         |
| Cable Length (m)                    | 0.9                       |
| Cable Length (in.)                  | 36                        |
| Cable Length (cm)                   | 91.4                      |
| PHYSICAL                            |                           |
| Cable Shielding                     | UTP                       |
| Color                               | White                     |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Weight (kg)                | 0.04                      |
| Shipping Weight (lbs.)              | 0.09                      |
| Snagless Connector                  | Yes                       |
| Wire Gauge (AWG)                    | 26                        |
| Wire Type                           | Stranded                  |
| COMMUNICATIONS                      |                           |
| Network Speed                       | 1Gbps                     |
| CONNECTIONS                         |                           |
| Side A - Connector 1                | RJ45 (MALE)               |
| Side B - Connector 1                | RJ45 (MALE)               |
| FEATURES & SPECIFICATIONS           |                           |
| Technology                          | Cat5/5e                   |
| WARRANTY                            |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>