## **HellermannTyton**

## **Specification Sheet**

Part Number: 110-70083



EVO 7 Mechanical Hand Tool, Standard hand span 3.5", 1/pkg

Article Number	110-70083
Туре	EV07
Color	Black (BK)
Features & Benefits	•Advanced TLC technology provides operational reliability and durability resulting in fewer repairs and an extended lifespan. •Lightweight tool with the most technologically advanced ergonomic design for reducing work-related risks such as fatigue and injury that effect productivity. •Tension dial offers 33 precise, easy-to-read settings (with ¼" increments) that reduce subjectivity or the need for fine tuning. •Tension lock-in mechanism prevents operator from changing tension setting during critical applications.
Quantity Per	EA
Product Description	HellermannTyton's EVO 7 mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 7 Tension/Lock/Cut Technology delivers performance, safety and comfort for operators. Available in a standard grip span (EVO 7) or short grip span (EVO 7SP) for smaller hands. Additional accessories are available.

Short Description	EVO 7 Mechanical Hand Tool, Standard hand span 3.5", 1/pkg
Global Part Name	EVO7-MET/PL-BK
Technical Description	Standard Hand Span 3.5" (90mm)
Cable Ties	T18, T30, T40, T50, T80, IT18, IT50
Tension Setting Tools	Adjustable
Cable Tie Width Max (Imperial)	0.19

Plastic (PL) Metal (MET)	
MET PL	
SAE-AS90387	
	ROHS Complaint
	Certification/Specification WEB
	MET PL

Package Quantity(Imperial) 1

Package Quantity (Metric)

Customs Number	8205599000
Content Unit(BMEcat)	pcs.
Weight (Metric)	275
Weight (Imperial)	9.7

1

© 2019 HellermannTyton. All Rights Reserved.

Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions