

## BU-P3925-@

(Standard Plunger Clip, Small Wire)



- The BU-P3925 is a standard plunger clip. See part number BU-P4555 for a large wire version.
- Overall length 2.35" (59.7mm), hook ID = .09" (2.3mm)
- It can be installed to wire up to 20 AWG with a jacket as large as  $\varphi$  .09" (2.3 mm) via solder connection.
- Hook attaches to leads up to 0.060" (1.5mm).

Material: Contact Beryllium copper

Spring 304 stainless-steel

Housing Glass-filled nylon

• Ratings: Current 5 Amps

Voltage Hands-free testing to 300 VRMS Temperature -40°F (-40°C) to 221°F (105°C)

• Color: The "@" in the model number indicates color. Available colors are:

-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White

RoHS 3 compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524