

Hoods/housings for rough environments
Single locking lever

Han-
Brid

Features

- Hoods/housings for rough environments
- Corrosion resistance ASTM B117-09 (500 h)
- With glued seal

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44, IP65 / IP67, with seal screw 09 20 000 9918
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
RoHS	compliant

Specifications and approvals

DNV GL

Details

The special hoods with glued seal can be combined with standard housings (see chapter 31).

Identification	Cable entry	Part number	Drawing (dimensions in mm)
Han® M, Hoods, for Han-Brid®, With glued seal, Top entry, Pack contents: With seal screw	1x M20	19 37 003 1443	
Han® M, Hoods, for Han-Brid®, With glued seal, Side entry, Pack contents: With seal screw	1x M20	19 37 003 1643	