SRW12US33 / SRW12US33G

SmartRack® Wall-Mount Rack Enclosure Cabinets



























12 Rack Units

250 lb. Load Rating Construction



Locking Doors & Side Panels

Clear Acrylic Front Window (SRW12US33G only)

33 inch Depth

Standard 19" Rack Width

Convenient

Cable Access

Adjustable Mounting Rails

Hinged Wall Bracket

Ventilated for Ample Airflow

Reversible Cabinet


Square/ Threaded Hole Mounting




(Lockable/Removable/Reversible. SRW12US33 door is perforated; SRW12US33G door has a clear acrylic window.)

- **B** Adjustable Mounting Rails (4) (Support square and threaded hole mounting options.)
- Side Panels (2) (Lockable/Removable)
- Hinged Wall Bracket (Lockable/Reversible. Allows the cabinet to swing away from the wall for convenient rear access to equipment and cabling.)
- E Cable Access Port Covers (4) (Removable)
- Ventilation Fan Ports (4) (Support optional SRFANWM fan kit.)
- **G** Keys (2)

Also Includes: Owner's Manual, cabinet ground screw, pre-installed front door ground wire and rackmount equipment mounting hardware (36 M6 cage nuts, 36 M6 mounting screws, 36 M6 nylon cup washers and



Floor-Standing Installation: Optional SRCASTER kit adapts cabinet to roll under desks, tables or counters. (Kit includes 4 casters.)



 Wall-mount enclosures provide convenient, locking storage for rackmount IT devices and other equipment that should be off the floor, out of the way and secure

- The cabinet is fully reversible, allowing installers to change door hinges from left to right by simply rotating the unit 180 degrees before mounting
- Hinged wall bracket allows cabinet to swing away from the wall for convenient access to equipment and
- 33" depth accommodates standard-sized 1U servers and simplifies cable management

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com










SRW12US33G




Specifications · 🔾 · · · comp	LIANT ROHS
Models	SRW12US33 / SRW12US33G
Rack Spaces	12U
Equipment Mounting Depth	Up to 32.5 in. (825.5 mm)
Load Rating*	250 lb. (113.4 kg)
Unit Dimensions [H x W x D]	25.18 x 23.62 x 33.5 in. (639.6 x 600 x 851 mm)
Shipping Dimensions [H x W x D]	26.9 x 25.6 x 37.8 in. (683 x 650 x 960 mm)
Unit Weight	100 lb. (45.36 kg)
Shipping Weight	120 lb. (54.43 kg)
Standards	Tested to EIA-310-E, IEC 60297-3-100, NOM,
	RoHS and PCI-DSS standards;
	IP250 Protection Rating

The load rating includes the combined weight of the unit and installed equipment. The unit must be

mounted to a stable surface with user-supplied anchors capable of bearing the full load.





Copyright © 2017 Tripp Lite.