HellermannTyton

Specification Sheet

Part Number: 181-00320



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High Density Slotted Wall Wiring Duct, 2" x 5", Non-Adhesive, PVC, Black, 120ft/Carton

Article Number	181-00320
Туре	SLHD2X5
Color	Black (BK)
Quantity Per	carton
Product Description	HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High Density Slotted Wall Wiring Duct, 2" x 5", Non-Adhesive, PVC, Black, 120ft/Carton

Global Part Name

- Technical Description Non-Adhesive
- Length L (Imperial) 6.0
- Length L (Metric) 1.83
- Fixation Method Non-Adhesive
- Width W (Imperial) 2.0
- Width W (Metric)50.8
- Height H (Imperial) 5.07
- Height H (Metric) 128.8
- Mounting Hole Centers (Imperial) 2.0

Material

Polyvinylchloride (PVC)

Material Shortcut

Flammability

Self-extinguishing

Halogen Free

PVC

Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	EN 50085-1:2005 + A1:2013 UL CSA EN 50085-2-3_1A
UL Recognized (US)	Yes
Package Quantity (Imperial)	120
Package Quantity (Metric)	36.58
Customs Number	3925900000

© 2021 HellermannTyton. All Rights Reserved.

Contact Us Ro

RoHS/WEEE Compliance

Disclaimer

Terms and Conditions