

## Specification Sheet

Part Number: 181-00319



- Strong fingers prevent unwanted breaking.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Supplied with mounting holes to streamline installation.
- Optional covers enhance protection and appearance.

Slotted Wall Wiring Duct, 2.5" x 3", Adhesive, PVC, Black, 120ft/Carton

**Article Number** 181-00319

**Type** SLA2.5X3

**Color** Black (BK)

**Quantity Per** carton

**Product Description** HellermannTyton Slotted Wall Duct features breakaway fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a wider opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts. Pressure-sensitive, rubber-based adhesive backing aids in temporary positioning.

**Short Description** Slotted Wall Wiring Duct, 2.5" x 3", Adhesive, PVC, Black, 120ft/Carton

<b>Global Part Name</b>	SLA2.5X3-PVC-BK
<b>Technical Description</b>	Adhesive
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	1.83
<b>Fixation Method</b>	Adhesive
<b>Width W (Imperial)</b>	2.5
<b>Width W (Metric)</b>	63.5
<b>Height H (Imperial)</b>	3.07
<b>Height H (Metric)</b>	77.9
<b>Mounting Hole Centers (Imperial)</b>	4.0
<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Flammability</b>	Self-extinguishing
<b>Halogen Free</b>	No

<b>Operating Temperature</b>	+122°F (+50°C)
<b>Reach Compliant (Article 33)</b>	No
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	CSA EN 50085-1:2005 + A1:2013 UL EN 50085-2-3_1A
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity (Imperial)</b>	120
<b>Package Quantity (Metric)</b>	36.58
<b>Customs Number</b>	3925900000

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)