

Blue, Grey, Black

## **Grounding & Cleaning**

If the material is used on top of an already properly grounded surface, grounding hardware may not be necessary. Where no properly grounded surface is available, grounding hardware is required to provide a path-to-ground. Rtg compliance verification measurements must be made as outlined in ESD TR53 with a surface resistance meter.

See Tech Bulletin TB-7000 for Reztore® Surface & Mat Cleaner Application Instructions.

## **Limited Lifetime Warranty:**

Desco warrants for one year that Statfree® matting products will be free of defects in materials and workmanship and will quarantee dissipative/conductive mat properties for the life of the mat. Damage to matting caused by misuse of any kind, including using inappropriate cleaners is not covered by Desco Limited Warranty.

RoHS 3. REACH, and Conflict Minerals Statement See the Desco Industries RoHS 3. REACH, and Conflict Minerals Statement:

http://www.descoindustries.com/ROHS.aspx

See the Desco Limited Warranty:

http://desco.descoindustries.com/Limited-Warrantv.aspx

See the Desco Disclaimer:

http://desco.descoindustries.com/Disclaimer.aspx

## **Specifications Standard Document**

Meets Requirements of:

Worksurface

ANSI/ESD S20.20

**Electrical Properties Typical Values** Test Procedures/Method

FTMS 101C, M 4046 Charge Decay: <0.01sec.

Rtt Resistance:  $1 \times 10^6 \text{ to} < 1 \times 10^9 \text{ ohms}$ ANSI/ESD S4.1 and ESD TR53 1 x 10<sup>6</sup> to < 1 x 10<sup>9</sup> ohms Rtg Resistance: ANSI/ESD S4.1 and ESD TR53

**Physical Properties** 

Construction: Heat fused vinyl composite

Thickness: 0.125" (3.2mm) Color:\* Blue, Grey, Black Texture:\* Light Embossing

45 Shore "A" Hardness: ASTM-D412 >300 psi Tensile Strength: ASTM-D412 >80 lbs/inch ASTM-D624 Tear Strength: ASTM-D412 Elongation: >80% Abrasion Resistance: >750 cycles Tabor-CS17

Other Properties

Chemical Resistance: Resistance to degradation by inorganic acids, organic acids, reducing agents, aliphatic

hydrocarbons, mineral oil, aldehydes, and amines

## **Tolerances:**

Width ± 0.250"

Length ± 0.250" every 1 linear foot of running material.

Thickness ±10%

Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to relax for at least 4 hours before cutting to size. Always trim with a sharp knife or razor blade.

\*Color and texture may vary between lots and mills.

For product listings, Click Here.



Specifications and procedures subject to change without notice.



STATFREE® Z2™, VINYL, DISSIPATIVE, 3-LAYER, 0.125" (3.2MM)

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com PHONE (909) 627-8178

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407

PHONE (781) 821-8370

STATFREE Z2™ DRAWING PM-112 DATE: March 2020