

Tripp Lite
1111 W. 35th Street

Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

USB 3.0 SuperSpeed to SATA III Adapter Cable with UASP, 2.5 in. SATA Hard Drives, White

MODEL NUMBER: U338-06N-SATA-W











Connects a 2.5 in. SATA HDD or SSD to your laptop or computer's USB port for extra storage, quick disk formatting and fast data transfer.

Description

The U338-06N-SATA-W USB 3.0 SuperSpeed to SATA III Adapter Cable connects a 2.5-inch SATA hard disk drive (HDD) or solid state drive (SSD) to an available USB port on your laptop or computer. This lets you back up important data, retrieve data from an old hard drive, or store information on an external drive that you can take with you to another computer.

This adapter cable supports USB 3.0 data transfer rates up to 5 Gbps. Its UASP (USB Attached SCSI Protocol) feature reduces latency and allows the cable to perform up to 70% faster when connected to a UASP-enabled host controller.

Perfect for storing and sharing large files, such as music and video files, the U338-06N-SATA-W is compatible with SATA drives up to 4 TB. Just insert the drive into the 22-pin SATA connector, and attach the built-in USB 3.0 cable to your computer.

The U338-06N-SATA-W accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives, as well as USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds. It supports LBA-48 bit (Logical Block Addressing) and USB Mass Storage Class Bulk-Only Transport. No software, drivers or external power supply is required. Compatible with all USB-enabled operating systems.

Features

Quickly Connects a SATA Drive to Your Computer's USB Port

- Recommended for backing up, retrieving and storing large data files
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller

Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Compatible with SATA HDDs and SSDs up to 4 TB
- Plug-and-play—no external power supply required
- Compatible with all USBenabled operating systems

System Requirements

- Any USB-enabled operating system
- Available USB port (USB 3.0 required to achieve USB 3.0 speeds)
- 2.5 in. SATA drive
- UASP-enabled host controller required for UASP performance

Package Includes

U338-06N-SATA-W USB 3.0
 SuperSpeed to SATA III Adapter
 Cable, White



Compatible with 2.5 in. SATA HDDs and SSDs Up to 4 TB

- Accepts SATA III, SATA II and SATA I drives
- Backward compatible with previous USB generations
- Supports LBA-48 bit and USB Mass Storage Class Bulk-Only Transport

Easy to Use

- Plug-and-play—no software, drivers or external power supply needed
- Compatible with all USB-enabled operating systems

Specifications

OVERVIEW		
UPC Code	037332199294	
INPUT		
Bus Powered	Yes	
Product Length (in.)	6	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	Blue (Read, Write, Power)	
PHYSICAL		
Shipping Dimensions (hwd / in.)	0.50 x 4.20 x 7.10	
Shipping Dimensions (hwd / cm)	1.27 x 10.67 x 18.03	
Shipping Weight (lbs.)	0.10	
Shipping Weight (kg)	0.05	
Unit Packaging Type	Polybag	
Unit Dimensions (hwd / in.)	0.5 x 2.8 x 0.71	
Unit Dimensions (hwd / cm)	1.3 x 7.1 x 1.8	
Unit Weight (lbs.)	0.05	
Unit Weight (kg)	0.02	
Material of Construction	ABS	
Color	White	
Cable Jacket Rating	VW-1	
ENVIRONMENTAL		
Operating Temperature Range	50 to 122 F (10 to 50 C)	





Storage Temperature Range	32 to 149 F (0 to 65 C)	
Relative Humidity	10% to 80% RH, Non-Condensing	
BTUs	17.1 BTU/Hr	
Power Consumption (Watts)	5	
CONNECTIONS		
Ports	1	
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
UASP Support	Yes	
Technology	USB 3.0 (SuperSpeed); SATA/eSATA; USB	
CERTIFICATIONS		
Certifications	Tested to CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies