BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-Low Profile



ATS Part#:

Description:

ATS-51170R-C1-R0

17.00 x 17.00 x 19.50 mm BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-Low Profile

 Heat Sink Type:
 maxiFLOW

 Heat Sink Attachment:
 maxiGRIP

 Equivalent Part Number:
 ATS-51170R-C2-R0 Discontinued

*Image above is for illustration purpose only.

Features & Benefits

- maxiFLOW™ design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- maxiGRIP™ attachment applies steady, even pressure to the component and does not require holes in the PCB
- Meets Telcordia GR-63-Core Office Vibration; ETSI 300 019 Transportation Vibration; and MIL-STD-810 Shock and Unpackaged Drop Testing standards
- · Comes preassembled with high performance, phase changing, thermal interface material
- Designed for low profile components from 1.5 to 2.99mm

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	8.1 °C/W	6.7 °C/W	5.8 °C/W	5.3 °C/W	4.8 °C/W	4.5 °C/W	4.2 °C/W
	Ducted Flow	6.5	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	ТІМ	Finish			
	17.00 mm	17.00 mm	19.50 mm	31.9 mm	T766	BLACK- ANODIZED			
	 Notes: Dimension A and B refer to component size. Dimension C is the heat sink height from the bottom of the base to the top of the fin field. ATS-51170R-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint Gobain C1100F). NOTE: Saint Gobain C1100F is discontinued effective 12/31/10. Thermal performance data are provided for reference only. Actual performance may vary by application. ATS reserves the right to update or change its products without notice to improve the design or performance. 								
 ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. Optional maxiGRIPTM Installation/Removal Tool Set P/N: MGT170 Contact ATS to learn about custom options available. 									
*Image above is for illustration purpose only.	- Contact /								

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.



© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA