

Tripp Lite

Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# USB-C Dock - 4K HDMI, USB 3.2 Gen 1, USB-A Hub Ports, Memory Card, 60W PD Charging

# MODEL NUMBER: U442-DOCK10-S











USB-C dock with PD Charging adds 4K HDMI, USB-A, USB-C and memory card ports to your laptop or tablet's USB-C or Thunderbolt 3 port.

#### **Features**

USB-C Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a WorkstationThis multiport USB-C dock with PD Charging expands the potential of your Windows laptop, Chromebook, tablet or other device with a USB-C or Thunderbolt 3 port. It's ideal for transmitting digital audio and 4K video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device and more—all at the same time.

Supports USB-C DisplayPort Alternate Mode for Transmitting Audio/Video SignalsBy connecting the built-in USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers.

**Transmits Crystal-Clear 4K Video and Digital Audio**The HDMI port supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz. A DVI display may also be connected using an HDMI to DVI adapter (sold separately). HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications.

**USB-A Ports Connect Keyboards, Thumb Drives and Other USB Peripherals**Two USB 3.2 Gen 1 ports accept USB peripherals, such as flash drives, mice, keyboards and printers. They support fast data transfer rates up to 5 Gbps and are backward compatible with USB 2.0 and USB 1.1 devices. Note: Host must support USB OTG (On-the-Go).

PD 2.0 Charging Port Charges Connected Device via AC Wall ChargerThe USB-C Power Delivery port supports power output up to 20V 3A (60W), which is sufficient for charging and powering the connected source device, such as an Android smartphone or Chromebook. Just connect the device's AC wall charger to the USB-C PD port. Note: USB-C PD port does not support Quick Charge (QC).

**Allows External Memory Access**A memory card slot supports Micro SD cards for transferring data to and from your connected computer, laptop or tablet.

**Built-In USB-C Cable Connects in Either Direction**Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

### **Highlights**

- Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode
- Supports Ultra HD 4K resolutions up to 3840 x 2160 @ 30 Hz for crystal-clear video
- Supports 20V 3A (60W) power output for fast-charging compatible mobile devices
- USB-A and memory card ports allow connection of flash drives and other peripherals
- Plug-and-play operation with no software required for easy, immediate installation

#### **Applications**

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Transfer data to and from a USB flash drive or Micro SD memory card
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a microphone/headset to record a podcast or listen to music

# **System Requirements**

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI or DVI\* input
- Not for use with Thunderbolt monitors
- \*Requires adapter (sold separately)

#### Package Includes

- U442-DOCK10-S USB-C Dock, Silver
- Owner's manual



Ready to Use Right Out of the PackageThe plug-and-play USB-C dock is specifically designed for use with Windows laptops and other notebooks, smartphones, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no extra software to be downloaded or installed. Its compact footprint fits easily into your desk space without taking up much valuable room.

# **Specifications**

OVERVIEW		
UPC Code	037332213365	
Product Type	Docking Station	
Technology	HDMI; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); PD Charging	
Host Connector	USB C (MALE)	
VIDEO		
Number of Monitors Supported	1	
Video Ports	HDMI (FEMALE)	
Video Ports Details	HDMI 2.0; HDCP 2.2	
Resolutions Supported	HDMI: 4K 30Hz (3840 x 2160)	
Max Supported Video Resolution	HDMI: 3840 X 2160 (4K X 2K) @ 30HZ	
Extended Mode	No	
Mirror Mode	No	
Max Supported Color Depth	24-bit True Color	
Chroma Sub Sampling	4:4:4	
DATA		
Data Ports	(2) USB A (FEMALE)	
Data Ports Details	(2) USB-A - USB 3.2 Gen 1 (5 Gbps)	
STORAGE		
Card Slots	MICRO SD (FEMALE)	
Card Slots Details	SD 3.0	
INPUT		
Built-In Cable Length (ft.)	0.49	
Built-In Cable Length (m)	0.15	
Built-In Cable Length (in.)	5.9	
Built-In Cable Length (cm)	15	
Bus Powered	Yes	





Decident Learnity (Ca)	40	
Product Length (in.)	12	
Product Length (cm.)	30.48	
Product Length (ft.)	1	
Product Length (m.)	0.3	
BATTERY		
Battery Charging (5V/1.5A Port)	No	
POWER		
USB Power Delivery (PD) Charging Support	Yes	
USB Power Delivery (PD) Charging Specification	2.0	
CHARGING		
Total Charging Watts	60	
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)	
Charging Ports / Amps	(2) 0.9A; 3A	
PHYSICAL		
Color	Silver	
Cable Jacket Rating	VW-1	
Material of Construction	Aluminium	
Shipping Dimensions (hwd / in.)	0.80 x 5.70 x 3.20	
Shipping Weight (lbs.)	0.20	
Unit Dimensions (hwd / in.)	0.51 x 4.5 x 1.3	
Unit Packaging Type	Box	
Unit Weight (kg)	0.07	
Unit Weight (lbs.)	0.15	
ENVIRONMENTAL		
Operating Temperature Range	32 to 131 F (0 to 55 C)	
Storage Temperature Range	14 to 158 F (-10 to 70 C)	
Relative Humidity	5% to 95% RH, Non-Condensing	
BTUs	6.1 BTU/Hr	
Power Consumption (Watts)	1.80	
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB A), Up to 20V 3A (60W) Input (USB C)	





CONNECTIONS		
Ports	5	
Dock Connectors	2 x USB3.0, MICRO SD, HDMI, USB-C CHARGING	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	HDMI (FEMALE)	
Side B - Connector 2	(2) USB 3.0 A (FEMALE)	
Side B - Connector 3	MICRO SD (FEMALE)	
Side B - Connector 4	USB C (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
HDCP Specification	2.2	
USB Hub Ports	Yes	
Number of USB Hub Ports	2	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Full Duplex Support	Yes	
Suspend Mode Support	Yes	
SD Card Specification	Micro SD	
STANDARDS & COMPLIANCE		
Certifications	Tested to CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>