

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA

Telephone: 773.869.1234 www.tripplite.com

# 3-Port Portable USB 3.0 SuperSpeed Hub with Keyboard/Mouse Sharing and File Transfer

# MODEL NUMBER: U360-003-KM





Allows you to transfer files and share a single keyboard and mouse between two Windows PCs, Macs and/or OTG-compatible Android tablets and smartphones.

#### Description

The U360-003-KM 3-Port USB 3.0 SuperSpeed Hub does more than just connect USB peripherals to your computer. Built-in software allows you to share files and a single keyboard/mouse between devices:

- Two Windows personal computers (PC)
- Two Macs
- One PC and one Mac
- One PC and one Android tablet or smartphone
- One Mac and one Android tablet or smartphone

Just connect the built-in USB 3.0 cable to an available USB port on your Windows or Mac computer or laptop. Connect up to three USB devices, such as a flash drive or external hard drive, to the top ports. To transfer files from one device to another or share a keyboard and mouse with a second device, connect the included USB cable to the hub's SHARE port and an available USB port on another computer or Onthe-Go (OTG) Android device. A USB Micro-B OTG adapter is included for connecting to Android tablets and smartphones.

The U360-003-KM supports USB 3.0 data transfer rates up to 5 Gbps—ten times faster than USB 2.0—and it's backward compatible with previous USB generations. Not only can you use one keyboard/mouse combination on two devices, you can also use the clipboard sharing feature to copy data from one computer and paste it in another.

The U360-003-KM receives power through its USB connection, so no external power supply is required.

# **Highlights**

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Copy and paste data between devices
- Compact design fits easily into laptop bag
- Share one keyboard/mouse between devices
- No external power supply required

# **System Requirements**

- Windows 2000 SP3 and later (except 8 RT)
- Mac OS X 10.6 and later
- Android 2.2 and later with OTG compliance and Windroid Linker app
- Intel Pentium II or PowerPC G4 processor or higher
- 256MB RAM or higher
- 50MB hard drive space or higher
- USB 3.0 port needed to achieve
   USB 3.0 speeds

# **Package Includes**

- U360-003-KM 3-Port USB 3.0
   SuperSpeed Hub
- USB 2.0 Type-A cable (M/M), 4 ft.
- USB 2.0 Micro-B to Type-A (M/F) OTG adapter
- Owner's manual



Its compact design fits easily into a purse, backpack, briefcase or laptop bag for quick connection anywhere.

#### **Features**

# Connects to Another Computer or On-the-Go (OTG) Android Device

- Share files between 2 electronic devices
- Share a keyboard and mouse between 2 electronic devices
- Share between 2 PCs, 2 Macs, PC and Mac, PC and OTG Android device, or Mac and OTG Android device
- Built-in software transfers files between devices
- Clipboard sharing for copy/paste between computers

#### **Excellent Speed and Versatile Performance**

- Connect up to 3 USB peripherals, such as flash drive or external hard drive
- Supports USB 3.0 data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Backward compatible with previous USB generations
- Supports 11 languages— English, Spanish, French, German, Italian, Russian, Simplified Chinese,
   Traditional Chinese, Korean, Japanese, Portuguese

# Take the Hub Anywhere

- Bus-powered through USB connection—no external power supply needed
- Compact design fits into purse, backpack, briefcase or laptop bag for travelling

# **Specifications**

OVERVIEW		
UPC Code	037332190161	
PHYSICAL		
Shipping Dimensions (hwd / in.)	1.20 x 6.70 x 3.90	
Shipping Dimensions (hwd / cm)	3.05 x 17.02 x 9.91	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	
CONNECTIONS		
Ports	3	
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	(3) USB 3.0 A (FEMALE)	
Side B - Connector 2	USB 3.0 A (FEMALE)	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FEATURES & SPECIFICATIONS		
Technology	USB 3.0 (SuperSpeed); USB	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>