


#### Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# Keyspan Mini DisplayPort 1.2a to DisplayPort Cable Adapter and Video Converter, 4K x 2K/3840 x 2160 (M/F) @ 60 Hz, HDCP 2.2, 3 ft.

# MODEL NUMBER: P139-003-DP-V2B







Connects a computer with a Mini DisplayPort (mDP) output to a high-definition monitor, projector or television with a DisplayPort<sup>™</sup> input.

#### Description

The P139-003-DP-V2B Keyspan® Mini DisplayPort 1.2a to DisplayPort Cable Adapter and Video Converter connects an mDP computer to a high-definition DisplayPort monitor, projector or television. It allows you to continue using your existing DisplayPort display instead of buying a new Mini DisplayPort monitor.

Ideal for displaying crystal-clear video on a large monitor or digital sign, this three-foot cable supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, including 1080p. Nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and molded connectors last a long time. Just plug and play with no software or drivers required.

## Features

#### Sends UHD Mini DisplayPort Audio/Video to a DisplayPort Monitor

- Connects an mDP computer to a DisplayPort monitor, projector or TV
- Recommended for displaying Mini DisplayPort video on a large monitor or digital sign
- Allows you to continue using an existing DisplayPort display, instead of buying a new monitor

#### Vibrant Video Quality

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz, including 1080p
- Compliant with HDCP 2.2 and DisplayPort 1.2a

## Highlights

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Nickel-plated connectors with gold-plated contacts
- Integral strain relief
- Compliant with HDCP 2.2 and DisplayPort 1.2a
- Plug and play—no software or drivers required

#### Package Includes

 P139-003-DP-V2B Keyspan Mini DisplayPort 1.2a to DisplayPort Cable Adapter (M/F), 3 ft.



#### **Superior Materials for Superior Performance**

- Nickel-plated connectors with gold-plated contacts for excellent conductivity
- Integral strain relief for long life
- Plug and play-no software or drivers required

# **Specifications**

1
037332201768
3
0.9
36
91.44
White
1.27 x 17.78 x 22.86
0.50 x 7.00 x 9.00
0.09
0.20
MINI DISPLAYPORT (MALE)
DISPLAYPORT (FEMALE)
DisplayPort
Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies