

## External 240V Tower Battery Pack for select Tripp Lite UPS Systems (BP240V1407C-1PH)

## MODEL NUMBER: BP240V1407C-1PH



#### Description

Tripp Lite's BP240V1407C-1PH External Battery Pack with built-in 7A charger offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Includes heavy gauge cabling to connect to host UPS. Multiple BP240V1407C-1PH batteries can be daisy-chained for longer runtime configurations with appropriate contractor-supplied battery pack interconnection cabling (see manual). Internal battery charger is powered via hardwire connection to 120V 30A electrical service. COMPATIBLE UPS SYSTEMS: SU6000RT3U, SU6000RT3UHV, SU8000RT3U, SU8000RT3U,

#### Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Multiple battery packs can be daisy-chained through each other to the UPS for even longer extended run operation
- Cabling to connect one BP240V1407C-1PH is included cabling for additional battery packs is contractor supplied
- Includes built-in 7A charger powered via hardwire 120VAC 30A input connection

# **Specifications**

OVERVIEW	
UPC Code	037332146755
BATTERY	

### Highlights

- Extends runtime of compatible Tripp Lite UPS Systems using 240VDC configuration
- Includes built in 7A charger
- Includes UPS connection cabling
- 10 year design life
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases



Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime. Configuration specific cabling for multi-battery pack configurations is contractor provided.
DC System Voltage (VDC)	240
UPS Connection	Included cabling enables connection between unique UPS connector and hardwire DC terminals in battery pack. Cabling to connect multiple external battery packs is contractor provided.
Expandable Runtime	Yes
PHYSICAL	
External Battery Pack Form Factor	Tower
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	0.00 × 0.00 × 0.00
Shipping Dimensions (hwd / in.)	0.00 × 0.00 × 0.00
Shipping Weight (kg)	1,129.45
Shipping Weight (lbs.)	2490.00
Unit Dimensions (hwd / cm)	152.4 x 82.3 x 73.2
Unit Dimensions (hwd / in.)	60 x 32.4 x 28.8
Unit Weight (kg)	1,117.20
Unit Weight (Ibs.)	2463
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies