

# Solid PVC Cable

MODEL NUMBER: N022-250-GY

## Description

Tripp Lite's 250-ft. gray category 5e (Cat5e) solid PVC bulk cable is designed for premise (in-wall) cabling applications. This 24 AWG 4-pair solid cable has a PVC jacket and is rated for 350MHz/1Gbps communication. Used for all non-plenum horizontal wiring applications. Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC11801 and ETL (category 5e draft 11). Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

#### **Features**

- Designed for premise (in-wall) cabling applications
- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- · Length: 250-ft. Color: gray
- 24 AWG 4-pair solid cable with PVC jacket
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other lengths
- Available in stranded copper cable (N020-01K-GY), in plenum cable (N024-01K) and in Cat6 (N222-01K and N224-01K)
- Warranted to be free from defects in materials and workmanship for life

# **Highlights**

 Premium cabling for Category 5 and 5e applications — rated for 350 MHz/1Gbps communications

### **System Requirements**

For all non-Plenum horizontal premise (in-wall) wiring applications for Network Installations 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.

### **Package Includes**

 250-ft. Cat5e Gray Bulk Patch Cable Solid PVC 24AWG 350MHz

# **Specifications**

OVERVIEW		
UPC Code	037332013095	
INDUT		
INPUT		
Cable Length (ft.)	250	
Cable Length (m)	76.20	
PHYSICAL		
Color	Gray	
Shipping Dimensions (hwd / in.)	0.00 × 0.00 × 0.00	
Shipping Weight (kg)	3.15	
Shipping Weight (lbs.)	6.94	
FEATURES & SPECIFICATIONS		



**Tripp Lite**1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

Technology	Cat5/5e
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>