



Take it to the Extreme with ***SUPER VU-TRON[®] SUPREME***

- Super-tough construction can withstand daily abuse, temperature extremes and high-stress industrial environments.
- Class M stranding (34 AWG) on all constructions for maximum flexibility.
- Tinned copper conductors for enhanced soldering performance and corrosion resistance.
- Durable jacket is now printed with RoHS compliance, sequential footage marking, and CE Mark on 10 and 12 AWG S00W.

***Go ahead, freeze it, heat it, beat it and mistreat it...
you can't defeat it.***




**CAROL
BRAND**

CORDPRODUCTS

SUPER VU-TRON® SUPREME

Types SJ00W/S00W

***When you require superior portable power cable for the best-quality performance,
use General Cable's Carol® Brand Super Vu-Tron® Supreme cable — manufactured
with all the features and benefits you would expect for extreme applications.***





CAROL SUPER VU-TRON® SUPREME

Applications:

Conductors:

- 18 through 10 AWG fully annealed stranded tinned copper per ASTM B-174

Insulation:

- Premium-grade color-coded oil-resistant 105°C EPDM
- European Color Code: See chart below

Jacket:

- Super Vu-Tron® Supreme, yellow
- Temperature range: -50°C to +105°C UL/CSA
- Voltage rating: 300 volts Type SJOOW 600 volts Type SOOW

Jacket Marking:

- CAROL SUPER VU-TRON® SUPREME (SIZE) (MM) 105°C (UL) WATER RESISTANT (TYPE) CSA -50°C FT-1 --- P-123-103 MSHA (VOLTS) ROHS MADE IN USA
- 10 and 12 AWG SOOW only: CAROL SUPER VU TRON® SUPREME (SIZE) (MM) 105°C (UL) WATER RESISTANT (TYPE) CSA -50°C FT-1 --- P-123-103 MSHA (VOLTS) ROHS CE MADE IN USA

Applications:

- Machine tools
- Power tools
- Dockside power applications
- Motor leads
- Portable machinery
- Cranes
- Submersible pumps

Features:

- Excellent flexibility in cold temperatures
- Lasts longer in flex applications
- Integral Flexfill®
- Ozone- and weather-resistant
- UL Listed and CSA Certified for indoor and outdoor use
- Water-resistant
- Safety colored
- High heat and flame resistance
- Resistant to oils, acids and chemicals
- Excellent abrasion and cut resistance
- Sequential footage marking

Industry Approvals:

- UL Flexible Cord - UL Subject 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- OSHA Acceptable
- JC 580
- RoHS
- CE Mark on 10 and 12 AWG SOOW

Packaging:

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order



GENERAL CABLE, CAROL BRAND, SUPER VU-TRON SUPREME and FLEXFILL are trademarks of General Cable Technologies Corporation.

©2007. General Cable Corporation. Highland Heights, KY 41076

All rights reserved.

Printed in USA

TYPE SJOOW - 300 VOLT - UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INS. THICKNESS		NOMINAL O.D.		CURRENT AMPST	APPROX. NET WEIGHT LBS/M ^(S)	STD. CTN.
				INCHES	mm	INCHES	mm			
02601	2	18	41/34	0.030	0.76	0.310	7.87	10	56	1000'
02602	3	18	41/34	0.030	0.76	0.320	8.13	10	65	1000'
02603	4	18	41/34	0.030	0.76	0.345	8.76	7	80	250'
02604	2	16	65/34	0.030	0.76	0.315	8.00	13	68	1000'
02605	3	16	65/34	0.030	0.76	0.335	8.51	13	80	250'
02606	4	16	65/34	0.030	0.76	0.370	9.40	10	95	250'
02607*	2	14	105/34	0.030	0.76	0.370	9.40	18	90	250'
02608	3	14	105/34	0.030	0.76	0.375	9.53	18	110	250'
02609	4	14	105/34	0.030	0.76	0.405	10.29	15	130	250'

TYPE SOOW - 600 VOLT - UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOM. INS. THICKNESS		NOMINAL O.D.		CURRENT AMPST	APPROX. NET WEIGHT LBS/M ^(S)	STD. CTN.
				INCHES	mm	INCHES	mm			
02631*	2	18	41/34	0.030	0.76	0.365	9.27	10	75	250'
02632	3	18	41/34	0.030	0.76	0.375	9.53	10	80	250'
02633*	4	18	41/34	0.030	0.76	0.400	10.16	7	110	250'
02634	2	16	65/34	0.030	0.76	0.370	9.40	13	75	250'
02635	3	16	65/34	0.030	0.76	0.395	10.03	13	100	250'
02636	4	16	65/34	0.030	0.76	0.425	10.80	10	120	250'
02621*	5	16	65/34	0.030	0.76	0.515	13.08	8	150	250'
02637*	2	14	105/34	0.045	1.14	0.510	12.95	18	155	250'
02638	3	14	105/34	0.045	1.14	0.525	13.34	18	165	250'
02639	4	14	105/34	0.045	1.14	0.575	14.61	15	215	250'
02622*	5	14	105/34	0.045	1.14	0.675	17.15	12	285	250'
02641*	2	12	168/34	0.045	1.14	0.590	14.99	25	200	250'
02642	3	12	168/34	0.045	1.14	0.600	15.24	25	250	250'
02643	4	12	168/34	0.045	1.14	0.650	16.51	20	280	250'
02623*	5	12	168/34	0.045	1.14	0.730	18.54	16	315	250'
02645	3	10	259/34	0.045	1.14	0.660	16.76	30	320	250'
02646	4	10	259/34	0.045	1.14	0.710	18.03	25	375	250'
02624*	5	10	259/34	0.045	1.14	0.770	19.56	20	432	250'

*Non-stock item; minimum quantity purchase required.

† Green/Yellow conductor for grounding only.

(S) Actual shipping weight may vary.

COLOR CODE CHART

NO. OF COND.	COLOR
2	Black, White
3	Black, White, Green/Yellow
4	Black, White, Red, Green/Yellow
5	Black, White, Red, Orange, Green/Yellow

TOP PERFORMANCE IN THE TOUGHEST ENVIRONMENTS
Volume change (%) of SUPER VU-TRON® SUPREME after 28 days at room temperature in the following materials:

ACETIC ACID (30%)	+19.00	LINSEED OIL	+1.04
AMMONIA HYDROXIDE	+3.12	LUBE OIL	-1.82
ASTM 3 OIL	+0.26	MILK	+4.16
BEER	+4.42	NITRIC ACID (10%)	+7.29
BLEACH WATER	+2.60	SAE 30 OIL	-1.30
BUTYL ALCOHOL	-1.82	SKYDROL 500	+17.10
CORN OIL	0.00	SODIUM HYDROXIDE	+10.90
FORMALDEHYDE	+3.38	SULFURIC ACID (10%)	+2.34
GLYCOL (ANTI-FREEZE)	-2.60	TOLUENE	+30.20
HYDROCHLORIC ACID (20%)	+10.60	UNLEADED GAS	+22.10
JP-4	+10.90	WATER	+2.86
KEROSENE	+10.60		



4 Tesseneer Drive, Highland Heights, KY 41076-9753
Phone: 1.800.243.8020 Fax: 1.859.572.9262
www.generalcable.com