



Interconnect Solutions for Delivery Robot: LiDAR, Camera, Sensor, Wireless and FAN Module Connections



Visit HRS for More



LiDAR & Camera

Sensor, Wireless, and FAN Modules



ix Industrial™
Compact and Robust Cat.6A I/O




CX Series
USB Type-C Connector Supporting Up to 20Gbps

Automotive Grade



GT32 Series
1Gbps, Space-saving Shielded Signal I/O

Automotive Grade




POK15/POK16 Series
3GHz, Coaxial Wire-to-Board & Board-to-Board




LF Series
Shielded Waterproof I/O

Automotive Grade




FunctionMAX™ FX23/FX23L Series
High Speed Floating Board-to-Board with Power Contacts

Automotive Grade




FunctionMAX™ FX26 Series
Vibration Absorbing, Floating Board-to-Board



FunctionMAX™ FX30B Series
Board-to-Board Power Connectors With Misalignment Absorption

HRS Integrated Solution for Delivery Robot/AGV/AMR

Interconnect Solutions for Delivery Robot: Motor Signal, PCB, Motor Power and Battery Connections



Motor Signal & PCB

Automotive Grade



ZE05 Series
125°C Heat Resistant,
High Vibration Resistance



DF51/DF51K Series
2mm Pitch,
Positive Lock
Wire-to-Board



DF60 Series
65A Max.*Current,
Positive Lock
Wire-to-Board
*UL Standard

Motor Power & Battery

Automotive Grade



HVH-280 (Non-waterproof) Series
125°C Heat Resistant,
30A Wire-to-Board

Automotive Grade



HVH-280 (Waterproof) Series
30A Waterproof
Panel Mount I/O