
























Bourns® Multifuse® Product Guide








SURFACE MOUNT POLYMER PTCs

Model Series	Photo	Features	Footprint	Rated Voltage and Hold Current	Operating Temperature	Certifications
MF-ASML/X		Low Ohmic	0402 / 1005	0.1 A 6 VDC 0.75 A	-40 °C to +85 °C	UL, CSA, TÜV
MF-FSML/X			0603 / 1608	0.35 A 6 - 8 VDC 3 A		UL, CSA, TÜV
MF-PSML/X			0805 / 2012	0.75 A 6 - 12 VDC 4.5 A		UL, CSA, TÜV
MF-NSML/X			1206 / 3216	1.5 A 6 - 12 VDC 6 A		UL, CSA, TÜV
MF-USML/X			1210 / 3225	1.75 A 6 - 12 VDC 7 A		UL, CSA, TÜV
MF-FSHT		High Temperature	0603 / 1608	0.05 A 12 VDC 0.16 A	-40 °C to +125 °C	UL, CSA, TÜV
MF-PSHT			0805 / 2012	0.05 A 12 - 16 VDC 0.5 A		UL, CSA, TÜV, AEC-Q200
MF-NSHT			1206 / 3216	0.1 A 12 - 30 VDC 0.75 A		UL, CSA, TÜV, AEC-Q200
MF-USHT			1210 / 3225	0.1 A 12 - 36 VDC 2 A		UL, CSA, TÜV, AEC-Q200
MF-MSHT			1812 / 4532	0.2 A 9 - 42 VDC 1.75 A		UL, CSA, TÜV, AEC-Q200
MF-SMHT			2920 - 3425 / 7555 - 8764	1.36 A 16 VDC 3 A		AEC-Q200
MF-FSMF		Standard	0603 / 1608	0.1 A 6 - 15 VDC 0.5 A	-40 °C to +85 °C	UL, CSA, TÜV
MF-PSMF			0805 / 2012	0.1 A 6 - 24 VDC 1.1 A		UL, CSA, TÜV
MF-NSMF			1206 / 3216	0.05 A 6 - 60 VDC 2 A		UL, CSA, TÜV, AEC-Q200
MF-USMF			1210 / 3225	0.05 A 6 - 30 VDC 2 A		UL, CSA, TÜV, AEC-Q200*
MF-MSMF			1812 / 4532	0.1 A 6 - 60 VDC 3 A		UL, CSA, TÜV, AEC-Q200*
MF-SMDF			2018 / 5146	0.3 A 10 - 60 VDC 2.6 A		UL, CSA, TÜV
MF-LSMF			2920 / 7555	0.3 A 6 - 60 VDC 7 A		UL, CSA, TÜV, AEC-Q200*
MF-GSMF			3425 / 8764	3 A 36 VDC 3 A		UL, CSA, TÜV
MF-SM			2920 - 3425 / 7555 - 8764	0.3 A 6 - 60 VDC 3 A		UL, CSA, TÜV
MF-SM/250		Telecom	3425 / 8764	0.08 A 250 VAC , 0.13 A	-40 °C to +85 °C	UL, CSA, TÜV
MF-SM/250V			Refer to Data Sheet	0.13 A 250 VAC , 0.13 A		UL, CSA, TÜV
MF-SD/250			Refer to Data Sheet	0.13 A 250 VAC , 0.13 A		UL, CSA

*AEC-Q200 compliant - some models







Bourns® Multifuse® Product Guide

RADIAL LEADED POLYMER PTCs



Model Series	Photo	Features	Rated Voltage and Hold Current	Operating Temperature	Certifications	
MF-R		Wide selection	0.05 A 16 - 60 VDC 11 A	-40 °C to +85 °C	UL, CSA, TÜV, AEC-Q200*	
MF-RG		Compact size	3 A 16 VDC 11 A		UL, CSA, AEC-Q200	
MF-RX/72		High voltage	0.2 A 72 VDC 3.75 A		UL, CSA, TÜV	
MF-RX/250		Telecom	0.12 A 250 VAC , 0.18 A		UL, CSA, TÜV	
MF-RM		Line voltage	0.05 A 240 VAC 0.55 A		-20 °C to +85 °C	UL, CSA, TÜV
MF-RHT		High Temperature	0.5 A 16 - 32 VDC 13 A		-40 °C to +125 °C	UL, CSA, TÜV, AEC-Q200
MF-RHS		High Temperature	3.5 A 16 VDC 13 A		-40 °C to +125 °C	UL, CSA

*AEC-Q200 compliant - some models

STRAP POLYMER PTCs

Model Series	Photo	Features	Rated Voltage and Hold Current	Operating Temperature	Certifications
MF-LR		High current	1.9 A 10 - 20 VDC 9 A	-40 °C to +85 °C	UL, CSA, TÜV
MF-LS		Enhanced voltage	1.8 A 15 - 24 VDC 3.4 A		UL, CSA, TÜV
MF-S		Enhanced voltage	1.2 A 15 - 30 VDC 4.2 A		UL, CSA, TÜV
MF-SVS		Low resistance	1.7 A 10 - 16 VDC 2.7 A		UL, CSA, TÜV
MF-VS		Low resistance	1.7 A 16 VDC 2.1 A		UL, CSA, TÜV
MF-VS Narrow Body		Low resistance, slim body	1.7 A 12 VDC 2.1 A		UL, CSA, TÜV

CUSTOMIZED POLYMER PTCs

Model Series	Photo	Features	Rated Voltage and Hold Current	Certifications
MF-D		Chip or disk form	2.5 A 10 - 20 VDC 12.2 A	Upon request
MF-DC		DC motor	Customized	Upon request

www.bourns.com

"Bourns" and "Multifuse" are registered trademarks of Bourns, Inc. in the United States and other countries.
Copyright © 2026, Bourns, Inc. • Litho in USA • MIMEO • 5/26 • e/MF2606

BOURNS®