

AWG Conductor Chart

COPPER CONDUCTOR DATA

The conductors used by General Cable meet the applicable requirements of ASTM specifications B-3, B-33, B-172, B-173, B-174 and B-286 and Federal Specification QQ-W-343.

The following data covers the more commonly used conductor constructions in the electrical and electronics industry. Special constructions, not shown, are available or can be designed to meet specific requirements. It is suggested that the General Cable Product Engineering Department be contacted before a specification is finalized.

AWG	STRANDING	TYPE STRANDING	DIAMETER ⁽⁴⁾		AREA		WEIGHT		D.C. RESISTANCE 20°C ⁽²⁾				BREAK STR. LBS
			in	mm	circ. mils	sq. mm	lbs/Mft	kg/km	TIN COATING ⁽³⁾		BARE OF SILVER COATING		
									Ω/Mft	Ω/km	Ω/Mft	Ω/km	
32	7/40	Co or Bu	.0096	.254	100	.051	.21	.31	176.00	577.00	164.00	538.00	1.986
30	Solid	–	.010	.254	100	.051	.30	.45	113.00	371.00	104.00	340.00	3.157
	7/38	Bu	.012	.305	112	.057	.35	.52	106.00	348.00	92.60	303.00	
28	Solid	–	.01264	.321	159	.081	.48	.72	70.80	232.00	65.30	214.00	5.020
	7/36	Co	.015	.381	175	.089	.55	.82	67.50	221.00	59.30	194.00	
27	Solid	–	.0142	.361	202	.102	.61	.91	55.60	182.00	51.40	169.00	6.331
	7/35	Co or Bu	.017	.432	220	.111	.69	1.04	53.80	176.00	–	–	
26	Solid	–	.016	.404	253	.128	.77	1.14	44.50	146.00	41.00	135.00	7.983
	7/34	Co or Bu	.019	.483	278	.141	.87	1.29	42.50	139.00	37.30	122.00	
	10/36	Bu	.0193	.490	250	.127	.78	1.15	47.30	155.00	40.40	133.00	
	19/38	Bu or Co	.021	.533	304	.154	.97	1.44	38.90	128.00	34.10	112.00	
24	Solid	–	.0201	.511	404	.205	1.22	1.82	27.20	89.20	25.70	84.20	12.690
	7/32	Co or Bu	.024	.610	448	.227	1.38	2.05	25.70	84.20	23.10	75.90	
	16/36	Bu	.024	.610	400	.201	1.25	1.64	29.50	96.80	27.50	90.20	
	19/36	Co or Bu	.025	.635	475	.241	1.48	2.20	24.90	81.70	21.80	71.60	
22	Solid	–	.025	.643	643	.324	1.94	2.89	16.70	54.80	16.20	53.20	19.430
	7/30	Co or Bu	.030	.762	700	.355	2.19	3.26	16.60	54.40	14.80	48.60	
	19/34	Bu or Eq	.0315	.800	754	.382	2.35	3.50	15.50	50.80	13.80	45.10	
20	Solid	–	.032	.813	1,020	.519	3.10	4.61	10.50	34.40	10.10	33.20	30.890
	7/28	Co or Bu	.038	.965		.562	3.49	5.19	10.30	33.80	9.33	30.60	
	10/30	Bu	.037	.940	1,111	.507	3.14	4.67	11.40	37.40	10.40	34.00	
	19/32	Co, Bu or Eq	.040	1.02	1,000	.616	3.84	5.71	9.48	31.10	8.53	28.00	
	26/34	Bu	.039	.940	1,216	.523	3.28	4.88	11.30	37.10	–	–	
19	Solid	–	.0359	.912	1,032	.653	3.90	5.80	–	–	8.05	26.40	38.950
18	Solid	–	.0403	1.024	1,290	.823	4.92	7.32	6.77	22.20	6.39	21.00	49.120
	7/26	Co or Bu	.048	1.22	1,620	.897	5.55	8.26	6.45	21.20	5.55	19.20	
	16/30	Bu	.0475	1.207	1,770	.810	5.01	7.45	7.15	23.40	6.48	21.30	
	19/30	Co, Bu or Eq	.050	1.27	1,600	.963	5.95	8.85	6.10	20.00	5.46	17.90	
	41/34	Bu	.049	1.244	1,900	.824	5.09	7.08	7.08	23.20	6.60	21.60	
16	Solid	–	.0508	1.29	1,627	1.31	7.81	11.60	4.47	14.70	4.16	13.60	78.100
	19/294	Bu or Eq	.057	1.45	2,580	1.23	7.52	11.20	4.82	15.80	4.27	14.00	
	19/.0117	Bu	.0585	1.50	2,426	1.32	8.02	11.90	4.39	14.40	4.13	13.50	
	26/30	Bu	.0606	1.54	2,601	1.32	8.15	12.10	4.39	14.40	3.99	13.10	
	65/34	Bu	.060	1.52	2,600	1.31	8.20	11.90	4.47	14.70	4.16	13.60	
14	Solid	–	.0641	1.63	2,581	2.08	12.4	18.50	2.68	8.79	2.52	8.28	124.200
	7/0242	Co	.073	1.85	4,110	2.08	12.7	18.90	–	–	2.61	8.56	
	19/274	Co, Eq or Un	.071	1.80	4,100	1.94	12.1	18.00	3.05	10.00	2.71	8.88	
	19/.0147	Bu	.074	1.88	3,831	2.08	12.7	18.90	2.73	–	2.61	8.56	
	41/30	Bu	.077	1.96	4,106	2.08	12.9	19.20	2.81	9.22	2.53	8.30	
12	Solid	–	.0808	2.05	4,100	3.31	19.8	29.50	1.69	5.54	1.59	5.21	197.500
	7/0305	Bu	.092	2.34	6,530	3.30	20.2	30.10	–	–	1.64	5.38	
	19/254	Co, Eq or Un	.0905	2.299	6,512	3.08	19.4	28.90	1.87	6.13	1.70	5.59	
	19/.0185	Cu	.0925	2.35	6,088	3.30	20.2	30.10	–	–	1.64	5.25	
	65/30	Bu	.094	2.388	6,503	3.29	20.8	31.10	1.82	5.97	1.64	5.25	
10	Solid	–	.1019	2.588	6,500	5.26	31.4	46.80	–	–	1.00	3.28	314.500
	7/.0385	Co	.116	2.95	10,380	5.25	32.0	47.60	–	–	1.00	3.28	
	19/.0234	Bu	.117	2.97	10,376	5.27	32.0	47.60	–	–	.98	3.21	
	37/.0169	Co	.112	2.84	10,404	4.74	29.2	43.40	–	–	1.25	4.10	
	105/30	Bu	.126	3.20	9,361	5.32	33.8	49.20	1.10	3.61	.99	3.24	
8	7/.0486	Bu	.146	3.71	10,500	8.38	50.1	74.50	–	–	.65	2.13	
	19/.0295	Bu or Eq	.144	3.66	16,534	8.38	50.0	74.40	–	–	.65	2.13	
	133/29	Ro 19 x 7/29	.169	4.293	16,535	8.61	54.0	80.40	.71	2.33	–	–	
	168/30	Ro 7 x 24/30	.174	4.42	16,983	8.51	53.4	79.00	.70	2.30	–	–	
6	19/.0374	Bu	.188	4.775	16,800	13.33	81.1	121.00	–	–	.40	1.30	
	133/27	Ro 19 x 7/27	.213	5.41	26,576	13.60	84.1	125.00	.43	1.41	–	–	
	266/30	Ro 7 x 38/30	.222	5.64	26,818	13.49	83.2	124.00	.44	1.44	–	–	
4	133/25	Ro 19 x 7/25	.257	6.53	26,600	21.61	135.0	201.00	.29	.95	–	–	
	420/30	Ro 7 x 60/30	.270	6.850	42,615	21.29	140.0	208.00	.28	.92	–	–	
2	665/30	Ro 19 x 35/30	.338	8.59	42,000	33.72	213.0	317.00	.18	.59	–	–	

(1) Bu - Bunched; Co - Concentric; Eq - Equilay; Ro - Rope; Un - Unilay

(2) Typical D.C. Resistance values for uninsulated wires. Multiply by 1.04 for typical values after insulation

(3) Values are for tinned, heavy tinned, prefused, overcoated or topcoated conductors

(4) Does not meet UL conductor stranding requirements