MMBF4391L, MMBF4392L, MMBF4393L

JFET Switching Transistors N-Channel

Features

- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Drain-Source Voltage	V _{DS}	30	Vdc
Drain-Gate Voltage	V _{DG}	30	Vdc
Gate-Source Voltage	V _{GS}	30	Vdc
Forward Gate Current	I _{G(f)}	50	mAdc

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR- 5 Board (Note 1) T _A = 25°C Derate above 25°C	P _D	225 1.8	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	556	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. FR-5 = $1.0 \times 0.75 \times 0.062$ in.



ON Semiconductor®

www.onsemi.com





MARKING DIAGRAM



XXX = Specific Device Code M = Date Code* • = Pb-Free Package

(Note: Microdot may be in either location)

*Date Code orientation and/or overbar may vary depending upon manufacturing location.

MARKING & ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 2 of this data sheet.

MMBF4391L, MMBF4392L, MMBF4393L

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS	·			
Gate-Source Breakdown Voltage $(I_G = 1.0 \ \mu Adc, \ V_{DS} = 0)$	V _{(BR)GSS}	30	_	Vdc
Gate Reverse Current (V_{GS} = 15 Vdc, V_{DS} = 0, T_A = 25°C) (V_{GS} = 15 Vdc, V_{DS} = 0, T_A = 100°C)	I _{GSS}		1.0 0.20	nAdc μAdc
$ \begin{array}{l} \mbox{Gate-Source Cutoff Voltage} \\ \mbox{(V}_{DS} = 15 \mbox{ Vdc}, \mbox{I}_{D} = 10 \mbox{ nAdc}) \\ \mbox{MMBF4391LT1} \\ \mbox{MMBF4392LT1} \\ \mbox{MMBF4393LT1} \end{array} $	V _{GS(off)}	-4.0 -2.0 -0.5	-10 -5.0 -3.0	Vdc
$\begin{array}{l} \mbox{Off-State Drain Current} \\ (V_{DS} = 15 \mbox{ Vdc}, \mbox{ V}_{GS} = -12 \mbox{ Vdc}) \\ (V_{DS} = 15 \mbox{ Vdc}, \mbox{ V}_{GS} = -12 \mbox{ Vdc}, \mbox{ T}_{A} = 100^{\circ}\mbox{C}) \end{array}$	I _{D(off)}		1.0 1.0	nAdc μAdc
ON CHARACTERISTICS				
$\label{eq:constraint} \begin{array}{l} \mbox{Zero-Gate-Voltage Drain Current} \\ (V_{DS} = 15 \mbox{ Vdc}, V_{GS} = 0) \\ \mbox{MMBF4391LT1} \\ \mbox{MMBF4392LT1} \\ \mbox{MMBF4393LT1} \end{array}$	IDSS	50 25 5.0	150 75 30	mAdc
$ \begin{array}{l} \mbox{Drain-Source On-Voltage} \\ (I_D = 12 \mbox{ mAdc}, V_{GS} = 0) \\ \mbox{ MMBF4391LT1} \\ (I_D = 6.0 \mbox{ mAdc}, V_{GS} = 0) \\ \mbox{ MMBF4392LT1} \\ (I_D = 3.0 \mbox{ mAdc}, V_{GS} = 0) \\ \mbox{ MMBF4393LT1} \end{array} $	V _{DS(on)}	- - -	0.4 0.4 0.4	Vdc
$ \begin{array}{l} \text{Static Drain-Source On-Resistance} \\ (I_D = 1.0 \text{ mAdc}, \text{V}_{GS} = 0) \\ \text{MMBF4391LT1} \\ \text{MMBF4392LT1} \\ \text{MMBF4393LT1} \end{array} $	r _{DS(on)}	- -	30 60 100	Ω

SMALL-SIGNAL CHARACTERISTICS

Input Capacitance $(V_{DS} = 0 \text{ Vdc}, V_{GS} = -15 \text{ Vdc}, f = 1.0 \text{ MHz})$	C _{iss}	_	14	pF
Reverse Transfer Capacitance $(V_{DS} = 0 \text{ Vdc}, V_{GS} = -12 \text{ Vdc}, f = 1.0 \text{ MHz})$	C _{rss}	-	3.5	pF

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
MMBF4391LT1G	6J		
SMMBF4391LT1G*	6J		
MMBF4392LT1G	6K	SOT-23 (Pb-Free)	3,000 / Tape & Reel
MMBF4393LT1G	M6G		
SMMBF4393LT1G*	M6G		

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

TYPICAL CHARACTERISTICS




Figure 1. Turn-On Delay Time

1000

500

200

100

50

t_{d(off)}, TURN-OFF DELAY TIME (ns)




Figure 2. Rise Time





Figure 4. Fall Time



_

 $R_{K} = R_{D'}$

Figure 3. Turn-Off Delay Time




Figure 5. Switching Time Test Circuit




Figure 6. Typical Forward Transfer Admittance




Figure 8. Effect of Gate-Source Voltage on Drain-Source Resistance

NOTE 1

The switching characteristics shown above were measured using a test circuit similar to Figure 5. At the beginning of the switching interval, the gate voltage is at Gate Supply Voltage ($-V_{GG}$). The Drain–Source Voltage (V_{DS}) is slightly lower than Drain Supply Voltage (V_{DD}) due to the voltage divider. Thus Reverse Transfer Capacitance (C_{rss}) of Gate–Drain Capacitance (C_{gd}) is charged to $V_{GG} + V_{DS}$.

During the turn–on interval, Gate–Source Capacitance (C_{gs}) discharges through the series combination of R_{Gen} and R_K . C_{gd} must discharge to $V_{DS(on)}$ through R_G and R_K in series with the parallel combination of effective load impedance (R'_D) and Drain–Source Resistance (r_{DS}). During the turn–off, this charge flow is reversed.

Predicting turn–on time is somewhat difficult as the channel resistance r_{DS} is a function of the gate–source voltage. While C_{gs} discharges, V_{GS} approaches zero and r_{DS} decreases. Since C_{gd} discharges through r_{DS} , turn–on time is non–linear. During turn–off, the situation is reversed with r_{DS} increasing as C_{gd} charges.

The above switching curves show two impedance conditions; 1) R_K is equal to $R_{D'}$ which simulates the switching behavior of cascaded stages where the driving source impedance is normally the load impedance of the previous stage, and 2) $R_K = 0$ (low impedance) the driving source impedance is that of the generator.




Figure 7. Typical Capacitance





Figure 9. Effect of Temperature on Drain–Source On–State Resistance



Resistance and Gate-Source Voltage

NOTE 2

The Zero–Gate–Voltage Drain Current (I_{DSS}) is the principle determinant of other J–FET characteristics. Figure 10 shows the relationship of Gate–Source Off Voltage ($V_{GS(off)}$) and Drain–Source On Resistance ($r_{DS(on)}$) to I_{DSS} . Most of the devices will be within ±10% of the values shown in Figure 10. This data will be useful in predicting the characteristic variations for a given part number.


For example:

Unknown

r_{DS(on)} and V_{GS} range for an MMBF4392

The electrical characteristics table indicates that an MMBF4392 has an I_{DSS} range of 25 to 75 mA. Figure 10 shows $r_{DS(on)} = 52 \Omega$ for I_{DSS} = 25 mA and 30 Ω for I_{DSS} = 75 mA. The corresponding V_{GS} values are 2.2 V and 4.8 V.





© Semiconductor Components Industries, LLC, 2019

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative