MPN3404

Silicon Pin Diode

This device is designed primarily for VHF band switching applications but is also suitable for use in general–purpose switching circuits. It is supplied in a cost–effective TO–92 type plastic package for economical, high–volume consumer and industrial requirements.

Features

- Rugged PIN Structure Coupled with Wirebond Construction for Optimum Reliability
- Low Series Resistance @ 100 MHz: $R_S = 0.7 \Omega$ (Typ) @ $I_F = 10 \text{ mAdc}$
- Sturdy TO-92 Style Package for Handling Ease
- Pb-Free Packages are Available*



Rating	Symbol	Value	Unit
Reverse Voltage	V _R	20	Vdc
Forward Power Dissipation @ T _A = 25°C Derate above 25°C	P _D	400 4.0	mW mW/°C
Junction Temperature	TJ	+125	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
Reverse Breakdown Voltage (I _R = 10 μAdc)	V _{(BR)R}	20	-	-	Vdc
Diode Capacitance (V _R = 15 Vdc, f = 1.0 MHz)	C _T	-	1.3	2.0	pF
Series Resistance (Figure 5) (I _F = 10 mAdc)	R _S	-	0.7	0.85	Ω
Reverse Leakage Current (V _R = 15 Vdc)	I _R	-	-	0.1	μAdc



ON Semiconductor®

http://onsemi.com





TO-92 (TO-226AC) CASE 182-06 STYLE 1

MARKING DIAGRAM



A = Assembly Location

′ = Year

WW = Work Week

= Pb-Free Package
 (Note: Microdot may be in either location)

ORDERING INFORMATION


Device	Package	Shipping
MPN3404	TO-92	1000 Units / Bulk
MPN3404G	TO-92 (Pb-Free)	1000 Units / Bulk

^{*}For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MPN3404

TYPICAL CHARACTERISTICS


50



40 30 T_A = 25°C 20 0.5 0.6 0.7 0.8 0.9 1.0 V_F FORWARD VOLTAGE (VOLTS)

Figure 1. Series Resistance

Figure 2. Forward Voltage






Figure 3. Diode Capacitance


Figure 4. Leakage Current



TO-92 (TO-226) CASE 182-06 **ISSUE L**

DATE 04/18/1998







SECTION X-X

- OTES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. CONTOUR OF PACKAGE BEYOND ZONE R IS UNCONTROLLED.
 4. LEAD DIMENSION IS UNCONTROLLED IN P AND

- BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIMETE	
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.45	5.21
В	0.170	0.210	4.32	5.33
С	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.050 BSC		1.27 BSC	
Н	0.100 BSC		2.54 BSC	
ſ	0.014	0.016	0.36	0.41
K	0.500	-	12.70	
٦	0.250		6.35	
N	0.080	0.105	2.03	2.66
Р		0.050		1.27
R	0.115	-	2.93	
٧	0.135		3.43	

STYLE 5: PIN 1. INPUT

2. OUTPUT

STYLE 1: PIN 1. ANODE STYLE 2: PIN 1. CATHODE STYLE 3: PIN 1. MAIN TERMINAL 1 STYLE 4: CANCELLED 2. CATHODE 2. ANODE 2. MAIN TERMINAL 2

DOCUMENT NUMBER:	98ASB42118B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TO-92 (TO-226)		PAGE 1 OF 1	

ON Semiconductor and III are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative