

# Han CC Protected module, crimp male



Part number	09 14 004 3041
Specification	Han CC Protected module, crimp male
HARTING eCatalogue	https://b2b.harting.com/09140043041

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Modules
Series	Han-Modular <sup>®</sup>
Type of module	Han <sup>®</sup> CC Protected module

#### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	4
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	1.5 6 mm²
Rated current	40 A
Rated voltage	830 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

## Material properties

Material (insert) Polycarbonate (PC)
--------------------------------------



## Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

# Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

#### Commercial data

Packaging size	2
Net weight	12.95 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)