

# POWER TRANSFORMER PC MOUNT: WORLD SERIES

# VPP24-1250

### Electrical Specifications (@25C)

1. Maximum Power: 30.0VA

2. Input: **Series:** 230VAC, 50/60Hz; **Parallel:** 115VAC, 50/60Hz 3. Output: **Series¹**: 24.0V CT@ 1.25A; **Parallel²**: 12.0V @ 2.5A

4. Voltage Regulation: 25% TYP @ full load to no load 5. Temperature Rise: 30C TYP (45C MAX allowed)

6. Insulation Resistance:  $100M\Omega$ 

7. Hipot: 4000VAC between primary to secondary and windings to core.

8. Recommended Fuse3:

Series: Littelfuse p/n 313 1.5HXP, 1.5A 250V, slow blow, ¼ x 1 ¼ or, Cooper Bussmann p/n BKMDL-1½, 1.5A 250V, ¼ x 1 ¼ Parallel: Littelfuse p/n 313 3HXP, 3A 250V, slow blow, ¼ x 1 ¼ or, Cooper Bussmann p/n BKMDL-3, 3A 250V, ¼ x 1 ¼

#### Construction:

Dual bobbin construction with an insulated shroud, both made of a high temperature material that exceeds UL flammability requirements.

#### Safety:

Since the dual bobbin construction effectively reduces capacitance, electrostatic shielding is not required. World Series Transformers are designed and manufactured to meet the following agency approvals:

Units: In inches







#### Agency File:

UL: File E53148, UL 5085-1 and 2 (formerly UL 506), General Purpose. UL: File E65390, UL 5085-1 and 3 (formerly UL1585), Class 2/3.

CSA: File LR 221330. C22.2 NO. 66, General Purpose.

TUV: File R72103639, EN 60950, (IEC950) information Technology Equipment.

#### A. Dimensions:

7. Birrioriorio:								111 11101100
Н	W	D	Α	В	С	ML	MD	MW
1.562	2.625	2.187	0.550	0.275	1.680	-	1.75	2.187

B. PIN DIM. : 0.045 SQ

C. WT Lbs. : 1.15

D. Mounting Holes: 0.156 dia. x 4

## Connections4:

Input: Series – Pin 1 to Pin 6, Jumper Pin 4 to Pin 3

Parallel - Pin 1 to Pin 6, Jumper Pin 1 to Pin 4 and Pin 3 to Pin 6

Output: Series - Pin 7 to Pin 12, Jumper Pin 9 to Pin 10

Parallel – Pin 7 to Pin 12, Jumper Pin 7 to Pin 10 and Pin 9 to Pin 12


**RoHS Compliance:** As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

\* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.


<sup>&</sup>lt;sup>4</sup> Primary and secondary windings are designed to be connected in series or parallel. Winding are not intended to be used independently.









SIDE VIEW



BOTTOM VIEW



TOP VIEW



**SCHEMATIC** 

Publish Date: June 3, 2019

<sup>&</sup>lt;sup>1</sup> Non-Inherently limited. Class 3.

<sup>&</sup>lt;sup>2</sup> Non-Inherently limited. Class 2 not wet, Class 3 wet.

<sup>&</sup>lt;sup>3</sup> Fuse must be used on **secondary** as conditions of acceptability for UL Class2/3 operation.