



SERIES 25 Multi-Deck

FEATURES

- Multiple Code and Indexing Choices
- Reliability Tested to Listed Specifications
- Less than 1.0" Square
- Termination Choices
- Panel and Shaft Seal Option
- Manufactured to ISO 9001 and Military Standards
- Custom Configurations Available





DIMENSIONS in inches (and millimeters)





Optical and Mechanical Encoders

SPECIFICATIONS Electrical Ratings Switching Loads: 150 mA at 120 Vac, resistive; 150 mA at 28 Vdc, resistive Current Carrying Capacity: 250 mA at 28 Vdc, resistive Contact Resistance: 75 m Ω max. after life Insulation Resistance: 1000 m Ω minimum between terminals and shaft Voltage Breakdown: 1000 Vac minimum between terminals and shaft Life Expectancy: 50,000 cycles at rated loads	Mechanical Ratings Stop Strength: 10 in-lbs minimum Rotational Torque: 4-20 in-oz, dependent on the number of decks Operating Temperature Range: -65°C to +85°C Non-Turn Device: Flatted mounting bushing, .375" dia. x .320" Package Size: .865" square Termination: PC terminals, .100" on center. Decks are .200" apart Hardware: Hex nut and lockwasher supplied	Materials and Finishes Bushing: Die cast zinc alloy, tin-zinc plated Mounting Hardware: plated brass Decks, Deck Separators, End Plate: Thermoplastic Contacts and Terminals: Gold, silver, nickel- plated beryllium copper Shaft, Stop Blades: Stainless Steel Detent Balls: Steel, nickel-plated Rivets: Brass, zinc-plated
Contacts: Shorting	Hardware: Hex nut and lockwasher supplied	

ORDERING INFORMATION

