



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

7-Port Industrial-Grade USB 3.0 SuperSpeed Hub - 20 kV ESD Immunity, Metal Housing, Mountable

MODEL NUMBER: U360-007-IND











Rugged industrial-grade hub adds 7 USB 3.0 ports to your computer for connecting industrial printers, sensors and other USB devices.

Features

Industrial-Grade USB 3.0 Hub Adds up to 7 USB Devices to Your Computer

This USB 3.0 hub with a heavy-duty all-metal housing connects as many as seven USB devices, such as external hard drives, industrial printers, barcode scanners, serial devices and sensors, to your host PC, server or thin client. The durable metal housing withstands harsh physical conditions in industrial and commercial applications, such as factories, construction sites, supply rooms and warehouses.

Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers

The hub supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It is especially recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. Each downstream port provides up to 900 mA for charging mobile devices. The hub is backward compatible with previous USB standards, so you can also continue using older peripherals while getting maximum performance from current devices.

Protects Your Devices against Electrostatic Discharge (ESD) and Overcurrent

Machines on the shop floor can generate electrostatic discharges, wiping out data and damaging sensitive electronics. This seven-port hub includes ESD protection to ± 20 kV, reducing potential static damage to your connected peripherals. This feature works in tandem with ± 2.5 kV-per-port overcurrent protection to safeguard your connected devices against damage and data loss from power surges.

Plug-and-Play Hub Offers Flexible Power and Mounting Options

The U360-007-IND requires no software or drivers to download and install. It draws power from the connected computer through the included USB cable. You can also plug the included 3-wire terminal block into the hub to draw power from a power terminal, or connect a compatible 9V–40V DC LPS power supply (not included) to a standard AC outlet. The hub mounts easily to a wall or DIN rail using the included hardware.

Highlights

- Adds barcode scanner, serial device, sensor—up to 7 devices—to your host computer
- Supports USB 3.0 SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- Rugged metal housing designed to withstand harsh warehouse and factory environments
- ESD protection to ±20 kV cuts potential static damage to your connected peripherals
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 7 USB devices and peripherals to your computer or laptop
- Add easy-to-access USB ports to computers stored in a cabinet, behind furniture or other hard-to-reach location
- Mount to a wall or DIN rail in a harsh environment, such as a factory, construction site, supply room or warehouse

System Requirements

- Compatible with all USBenabled operating systems (USB 3.0 port needed to achieve USB 3.0 speeds)
- If using an optional LPS power supply, requires 9–40V DC unit with 5.5 x 2.1 x 9.5 mm output



plug with either positive pin/negative sleeve or negative pin/positive sleeve

Package Includes

- U360-007-IND 7-Port Industrial-Grade USB 3.0 SuperSpeed Hub
- USB 3.0 cable, 3 ft.
- 3-pin power terminal block
- DIN rail-mounting hardware
- Wall-mounting hardware
- Owner's manual

Specifications

OVERVIEW		
UPC Code	037332186300	
Over Current Protection	Yes	
INPUT		
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A	
External Power Supply Output Specs (V / A)	9V - 40V / 3A	
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve	
Bus Powered	Yes	
USER INTERFACE, ALERTS & CONTROLS		
	T	
LED Indicators	Green (Power, 1, 2, 3, 4, 5, 6, 7)	
PHYSICAL		
Color	Black	
Included Mounting Accessories	Yes	
Material of Construction	Steel (SGCC)	
Shipping Dimensions (hwd / cm)	6.35 x 17.27 x 10.92	





Shipping Dimensions (hwd / in.)	2.50 x 6.80 x 4.30	
Shipping Weight (kg)	0.59	
Shipping Weight (lbs.)	1.30	
Unit Dimensions (hwd / in.)	1.3 x 6.2 x 3.1	
Unit Packaging Type	Вох	
Unit Weight (kg)	0.34	
Unit Weight (lbs.)	0.75	
ENVIRONMENTAL		
Operating Temperature Range	32 to 104 F (0 to 40 C)	
Storage Temperature Range	14 to 131 F (-10 to 55 C)	
Relative Humidity	5% to 90% RH, Non-Condensing	
BTUs	110.6 BTU/Hr	
Power Consumption (Watts)	32.4	
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A 3.0)	
CONNECTIONS		
Ports	7	
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	(7) USB 3.0 A (FEMALE)	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Technology	USB; USB 3.0 (SuperSpeed)	
CERTIFICATIONS		
Certifications	Tested to Tested to CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies