Small Signal MOSFET

Single N-Channel, 60 V, 380 mA, 1.6 Ohm, SOT-23

Features

- ESD Protected
- Low R_{DS(on)}
- Surface Mount Package
- 2V Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Low Side Load Switch
- Level Shift Circuits
- DC-DC Converter
- Portable Applications i.e. DSC, PDA, Cell Phone, etc.

MAXIMUM RATINGS (T_J = 25°C unless otherwise stated)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	60	V
Gate-to-Source Voltage	V _{GS}	±20	V
	I _D	380 270	mA
	I _D	320 230	mA
Power Dissipation Steady State 1 sq in Pad Steady State Minimum Pad	P _D	420 300	mW
Pulsed Drain Current (t _p = 10 μs)	I _{DM}	5.0	Α
Operating Junction and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C
Source Current (Body Diode)	Is	300	mA
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)	TL	260	°C
Gate-Source ESD Rating (HBM, Method 3015)	ESD	2000	٧

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. Surface-mounted on FR4 board using 1 sq in pad size with 1 oz Cu.
- 2. Surface-mounted on FR4 board using 0.08 sq in pad size with 1 oz Cu.




ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(on)} MAX	I _D MAX	
60 V	1.6 Ω @ 10 V	380 mA	
	2.5 Ω @ 4.5 V	300 IIIA	

SIMPLIFIED SCHEMATIC





704 M=

Source

SOT-23 CASE 318 STYLE 21

704 = Specific Device Code*

M = Date Code*

Pb-Free Package

Gate

(Note: Microdot may be in either location)
*Specific Device Code, Date Code or overbar
orientation and/or location may vary depending upon manufacturing location. This is a
representation only and actual devices may
not match this drawing exactly.

ORDERING INFORMATION

Device	Package	Shipping [†]
2N7002KT1G, 2V7002KT1G	SOT-23 (Pb-Free)	3000 / Tape & Reel
2N7002KT7G	SOT-23 (Pb-Free)	3500 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

1

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Junction-to-Ambient - Steady State (Note 3)	$R_{ heta JA}$	300	°C/W
Junction-to-Ambient - t ≤ 5 s (Note 3)		92	
Junction-to-Ambient - Steady State (Note 4)		417	
Junction-to-Ambient - t ≤ 5 s (Note 4)		154	

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Co	ndition	Min	Тур	Max	Unit
OFF CHARACTERISTICS	-	-		-	-	-	-
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V,	I _D = 250 μA	60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J				71		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V,	T _J = 25°C			1	μΑ
		V _{DS} = 60 V	T _J = 125°C			10	
		V _{GS} = 0 V, V _{DS} = 50 V	T _J = 25°C			100	nA
Gate-to-Source Leakage Current	I _{GSS}	V _{DS} = 0 V, \	/ _{GS} = ±20 V			±10	μΑ
		V _{DS} = 0 V, \	/ _{GS} = ±10 V			450	nA
		V _{DS} = 0 V, V _{GS} = ±5.0 V				150	nA
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}$	I _D = 250 μA	1.0		2.3	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J				4.0		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	$V_{GS} = 10 \text{ V, } I_D = 500 \text{ mA}$ $V_{GS} = 4.5 \text{ V, } I_D = 200 \text{ mA}$			1.19	1.6	Ω
					1.33	2.5	
Forward Transconductance	9FS	V _{DS} = 5 V,	I _D = 200 mA		530		mS
CHARGES AND CAPACITANCES							_
Input Capacitance	C _{ISS}	., .,			24.5	45	pF
Output Capacitance	C _{OSS}	0.0	f = 1 MHz, = 20 V		4.2	8.0	
Reverse Transfer Capacitance	C _{RSS}	• 08	- 20 1		2.2	5.0	
Total Gate Charge	Q _{G(TOT)}				0.7		nC
Threshold Gate Charge	Q _{G(TH)}	V _{GS} = 4.5 V	, V _{DS} = 10 V;		0.1		
Gate-to-Source Charge	Q_{GS}	I _D = 2	00 mA		0.3		
Gate-to-Drain Charge	Q_{GD}				0.1		
SWITCHING CHARACTERISTICS, V_{GS}	= V (Note 6)						
Turn-On Delay Time	t _{d(ON)}				12.2		ns
Rise Time	t _r	V _{GS} = 10 V,	V _{DD} = 25 V,		9.0		
Turn-Off Delay Time	t _{d(OFF)}	I_D = 500 mA, R_G = 25 Ω			55.8		
Fall Time	t _f				29		
DRAIN-SOURCE DIODE CHARACTER	ISTICS						
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V,	T _J = 25°C		0.8	1.2	V
		I _S = 200 mA	T _J = 85°C		0.7		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 5. Pulse Test: pulse width \leq 300 μ s, duty cycle \leq 2%

Surface-mounted on FR4 board using 1 sq in pad size with 1 oz Cu.
 Surface-mounted on FR4 board using 0.08 sq in pad size with 1 oz Cu.

^{6.} Switching characteristics are independent of operating junction temperatures

TYPICAL CHARACTERISTICS




Figure 5. On-Resistance vs. Gate-to-Source Voltage

Figure 6. On–Resistance Variation with Temperature

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Diode Forward Voltage vs. Current




Figure 10. Threshold Voltage with Temperature

TYPICAL CHARACTERISTICS




Figure 11. Thermal Response - 1 sq in pad




Figure 12. Thermal Response - minimum pad



SOT-23 (TO-236) CASE 318-08 **ISSUE AS**

DATE 30 JAN 2018

SCALE 4:1 D - 3X b

TOP VIEW







RECOMMENDED SOLDERING FOOTPRINT



DIMENSIONS: MILLIMETERS

NOTES:

- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: MILLIMETERS.
 3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH.
 MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH,

PROT	RUSIONS, OR GATE BURRS.	
		T

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.039	0.044
A1	0.01	0.06	0.10	0.000	0.002	0.004
b	0.37	0.44	0.50	0.015	0.017	0.020
С	0.08	0.14	0.20	0.003	0.006	0.008
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.080
L	0.30	0.43	0.55	0.012	0.017	0.022
L1	0.35	0.54	0.69	0.014	0.021	0.027
HE	2.10	2.40	2.64	0.083	0.094	0.104
T	0°		10°	0°		10°

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code

= Date Code

= Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 1 THRU 5: CANCELLED	STYLE 6: PIN 1. BASE 2. EMITTER 3. COLLECTOR	STYLE 7: PIN 1. EMITTER 2. BASE 3. COLLECTOR	STYLE 8: PIN 1. ANODE 2. NO CONNECTION 3. CATHODE
OT (1 F O			

SOT-23 (TO-236)

STYLE 9:	STYLE 10:	STYLE 11:	STYLE 12:	STYLE 13:	STYLE 14:
PIN 1. ANODE	PIN 1. DRAIN	PIN 1. ANODE	PIN 1. CATHODE	PIN 1. SOURCE	PIN 1. CATHODE
ANODE	SOURCE	CATHODE	CATHODE	2. DRAIN	2. GATE
CATHODE	3. GATE	CATHODE-ANODE	ANODE	3. GATE	ANODE

STYLE 15:	STYLE 16:	STYLE 17:	STYLE 18:	STYLE 19:	STYLE 20:
PIN 1. GATE	PIN 1. ANODE	PIN 1. NO CONNECTION	PIN 1. NO CONNECTION	PIN 1. CATHODE	PIN 1. CATHODE
CATHODE	CATHODE	ANODE	CATHODE	ANODE	ANODE
ANODE	CATHODE	CATHODE	ANODE	CATHODE-ANOD	E 3. GATE

STYLE 21:	STYLE 22:	STYLE 23:	STYLE 24:	STYLE 25:	STYLE 26:
PIN 1. GATE	PIN 1. RETURN	PIN 1. ANODE	PIN 1. GATE	PIN 1. ANODE	PIN 1. CATHODE
SOURCE	OUTPUT	2. ANODE	2. DRAIN	2. CATHODE	2. ANODE
3 DRAIN	3 INPLIT	3 CATHODE	3. SOURCE	3. GATE	NO CONNECTION

STYLE 27: PIN 1. CATHODE 2. CATHODE 3. CATHODE	STYLE 28: PIN 1. ANODE 2. ANODE 3. ANODE	
DOCUMENT N	UMBER: 98ASB42226B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

DESCRIPTION:

PAGE 1 OF 1

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative