Features

Regulated Converter

- Universal input 85-264VAC
- <250mW No load power consumption
- -25°C to +80°C Operating temperature, with derating
- Class II installations (without FG)
- Continuous SCP, OCP
- IEC/EN/UL60950 & IEC/EN/UL62368 certified

RECO **AC/DC** Converter

RAC02-GB

2 Watt **Single Output EMC Class B**



Description

The RAC02-GB series are low cost AC/DC power supplies, ideal for PCB mounted, compact, board level industrial applications. They feature universal AC input voltage range, regulated and short-circuit-proof isolated DC outputs, low standby power consumption and -25°C to +80°C operating temperature range. The RAC02-GB have a built-in Class B / FCC Part 15 EMC filter, are certified to EN60950 and EN62368 safety standards and come with a three year warranty.

Selection Guide					
Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ [%]	Max. Capacitive Load ⁽¹⁾ [μF]
RAC02-3.3SGB	85-264	3.3	500	63	500
RAC02-05SGB	85-264	5	400	63	500
RAC02-12SGB	85-264	12	167	68	200
RAC02-15SGB	85-264	15	140	63	200
RAC02-24SGB	85-264	24	83	63	200

Notes:

Note1: Measured with all input voltages at +25°C with constant resistant mode at full load


















ULIEC/EN60950-1 certified UL/IEC/EN62368-1 certified CAN/CSA-C22.2 No. 62368 certified IEC/EN62368-1 certified

CB Report

Model Numbering



Ordering Examples:

RAC02-12SGB 12Vout Single Output EMC Class B



Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS						
Parameter	Condition			Min.	Тур.	Max.
Internal Input Filter						Pi-type
Input Voltage Range (2,3,4)	nom.	Vin = 230VAC		85VAC	230VAC	264VAC
Input Current		115VAC 230VAC				50mA 30mA
Inrush Current	cold start at +25°C	115V/ 230V/	-			30A 40A
No load Power Consumption					180mW	250mW
Input Frequency Range				47Hz		63Hz
Minimum Load				0%		
Power Factor		115VAC 230VAC			0.55 0.42	
Start-up Time		115VAC 230VAC			250ms 200ms	2s 2s
Hold-up time		115VAC 230VAC				20ms 80ms
Internal Operating Frequency	100% lo	100% load at nominal Vin			65kHz	
		0°C to 80°C	3.3Vout 5Vout 12Vout 15Vout 24Vout			100mVp-p 100mVp-p 200mVp-p 200mVp-p 240mVp-p
Output Ripple and Noise	20MHz BW	-25°C to 0°C	3.3Vout 5Vout 12Vout 15Vout 24Vout			200mVp-p 200mVp-p 300mVp-p 300mVp-p 300mVp-p


Notes:


Note2: No proper operation with DC input voltage

Note3: The products were submitted for safety files at AC-Input operation

Note4: Refer to "Line Derating"

Efficiency vs. Load









Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

REGULATIONS		
Parameter	Condition	Value
Output Accuracy	-25°C to +80°C	±6.0% max.
Line Regulation	-25°C to +80°C	±2.0% max.
Load Regulation	-25°C to +80°C	6.0% max.





PROTECTIONS				
Parameter		Туре		Value
Input Fuse (5)		internal fusible resisto		sible resistor, $1\Omega/1W$
Short Circuit Protection (SCP)	be	low 100mΩ	cont	inuous, auto recovery
Over Voltage Category				OVCII
Over Current Protection (OCP)		3.3Vout 5Vout 12Vout 15Vout 24Vout		hiccup mode
Class of Equipment				Class II
Isolation Voltage (6)	I/P to O/P	I/P to O/P rated for 1 minute		3kVAC
Isolation Resistance				100M Ω min.
Insulation Grade				reinforced
Leakage Current		I/P to O/P		0.25mA max.


Notes:

Note5: Refer to local safety regulations if input over-current protection is also required

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note7: For operation at 230VAC, an external MOV is recommended. The Varistor should comply with IEC-61051-2. e.g. EPCOS S14 series

Protection Circuit





Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

ENVIRONMENTAL				
Parameter	Cond	ition		Value
Operating Temperature Denge	@ natural convection 0.1m/s	full loa	ıd	-25°C to +70°C
Operating Temperature Range	@ Hatural convection o. IIII/s	refer to "Derati	ng Graph"	-25°C to +80°C
Maximum Case Temperature				+120°C
Temperature Coefficient				0.03%/K
Operating Altitude (8)				4000m
Operating Humidity	non-con	densing		5% - 95% RH max.
Pollution Degree				PD2
Shock				10-150Hz, 2G 10min./1cycle, period 60min. each along x,y,z axes
Vibration	according to M	IIL-STD-202G		20G/11ms pulse, 3 times at each x, y, z axes
MTBF (9)	according to MIL-HDBK-21	7F method 2	+25°C	1691 x 10 ³ hours
INITOL	according to MIL-HDBK-21	71, 1116ti 10ti Z	+70°C	424 x 10 ³ hours

Notes:


Note8: Recognized by UL for safe operation up to 4000m. High altitude operation may impact the performance and lifetime.

Contact RECOM Techsupport for detailed information


Note9: Based on calculation for 5Vout

Derating Graph

(@ Chamber and natural convection 0.1m/s)



Line Derating



SAFETY AND CERTIFICATIONS				
Certificate Type (Safety)	Report / File Number	Standard		
Information Technology Equipment, General Requirements for Safety	SA1804152L01001	IEC60950-1:2005 2nd Edition + Am2:2013 EN60950-1:2006 + A12:2011 + A2:2013		
Audio/Video, information and communication technology equipment - Part1: Safety requirements	E196683-A5 and E19668-A6001	UL62368-1, 2nd Edition CAN/CSA-C22.2 No. 62368-1-14		
Audio/Video, information and communication technology equipment - Part1: Safety requirements (CB Scheme)	SA1804152S 001 -	IEC62368-1:2014 2nd Edition		
Audio/Video, information and communication technology equipment - Part1: Safety requirements	5A16041325 001	EN62368-1:2014+A11:2017		
RoHS2		RoHS 2011/65/EU + AM2015/863		
continued on next page				



Series


Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)


EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements		EN55032, Class B
Information technology equipment - Immunity characteristics - Limits and methods of measurement	EA1804152E 01001	EN55024:2010 + A1:2015
ESD Electrostatic discharge immunity test	Air ±2, 4, 8kV Contact ±2, 4kV	EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3:2006 + A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: ±1.0kV	EN61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port: L-N ±1.0kV	EN61000-4-5:2014, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port 3V	EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	50Hz, 1A/m	EN61000-4-8:2009, Criteria A
	Voltage Dips >95%	EN61000-4-11:2004, Criteria A
Voltage Dips and Interruption	Voltage Dips 30%	EN61000-4-11:2004, Criteria B
	Voltage Interruptions >95%	EN61000-4-11:2004, Criteria B
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013


DIMENSION AND PHYSICAL CHARACTERISTICS


Parameter	Туре	Value
Material	case	black plastic (UL94V-2)
Material	PCB	FR4 (UL94V-0)
Dimension (LxWxH)		33.7 x 22.2 x 19.0mm
Weight		12g typ.

Dimension Drawing (mm)









	Recommended Footprint Details	S
	2.54	
<u>↓</u>		
2.54	1 02	3 ↔
2.5		
	Top View	4 ¢ j
	+++++++++++++++++++++++++++++++++++++++	
		1 1 1 1

Pin Connections

Pin #	Single
1	VAC in (L)
2	VAC in (N)
3	-Vout
4	+Vout

Tolerance: Pin length: -0.5/+0.9 $xx.x = \pm 0.5$ mm $x.xx = \pm 0.25mm$



Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

PACKAGING INFORMATION			
Parameter	Туре	Value	
Packaging Dimension (LxWxH)	tube	470.0 x 36.4 x 26.4mm	
Packaging Quantity		20pcs	
Storage Temperature Range		-25°C to +85°C	
Storage Humidity	non-condensing	5% - 95% RH max.	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 3/2019 PA-6