


# Lead (Pb)-Bearing Thick Film, Rectangular, **Semi-Precision Chip Resistors**



### **FEATURES**

HALOGEN FREE

- · Low temperature coefficient (50 ppm/K) and tight tolerances (± 0.25 %)
- Lead (Pb)-bearing termination plating on Ni barrier layer
- Metal glaze on high quality ceramic
- · Material categorization: For definitions of compliance please see www.vishav.com/doc?99912

STANDARD ELECTRICAL SPECIFICATIONS										
MODEL	CASE SIZE INCH	CASE SIZE METRIC	POWER RATING P <sub>70</sub> W	LIMITING ELEMENT VOLTAGE U <sub>max.</sub> AC <sub>RMS</sub> /DC V	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE Ω	SERIES		
D10/CRCW0402-P	0402	1005	0.063	50	± 100	± 0.5	10 to 1M	E24; E96		
D10/ChGW0402-P	0402	1003	0.003	50	± 50	± 0.25, ± 0.5, ± 1	100 to 1M			
					± 100	± 0.5	10 to 10M			
D11/CRCW0603-P	0603	1608	0.1	75	± 50	± 0.25	100 to 1M	E24; E96		
						± 0.5, ± 1	100 to 10M			
	0805	2012	0.125	150	± 100	± 0.5	10 to 10M	E24; E96		
D12/CRCW0805-P					± 50	± 0.25	100 to 1M			
						± 0.5, ± 1	100 to 10M			
	1206	3216	0.25	200	± 100	± 0.5	10 to 10M	E24; E96		
D25/CRCW1206-P					± 50	± 0.25	100 to 1M			
								± 50	± 0.5, ± 1	100 to 10M
CRCW1210-P	1210	3225	0.5	200	± 100	± 0.5	100 to 1M	F04. F06		
CRCW1210-P	1210	3223	0.5	200	± 50	± 0.5, ± 1	100 to 1M	E24; E96		
CDCW/1010 D	1010	3246	1.0	200	± 100	± 0.5	100 to 2.2M	F04. F06		
CRCW1218-P	1218				± 50	± 0.5, ± 1	100 to 2.2M	E24; E96		
CRCW2010-P	2010	5025	0.75	400	± 100	± 0.5	10 to 10M	E24: E96		
UNUVVZU10-F					± 50	± 0.5, ± 1	100 to 10M	Z24, E90		
CRCW2512-P	2512	12 6332	1.0	500	± 100	± 0.5	10 to 10M	E04: E06		
UNUW2312-F	2312				± 50	± 0.5, ± 1	100 to 10M	E24; E96		

### **Notes**


- These resistors do not feature a limited lifetime when operated within the limits of rated dissipation, permissible operating voltage and permissible film temperature. However, the resistance typically increase due to the resistor's film temperature over operating time generally known as drift. The drift may exceed the stability requirements of an individual application circuit and thereby limits the functional time.
- Marking and packaging: See datasheet "Surface Mount Resistor Marking" (www.vishay.com/doc?20020).
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.



TECHNICAL SPECIFICATIONS									
PARAMETER	UNIT	D10/ CRCW0402-P	D11/ CRCW0603-P	D12/ CRCW0805-P	D25/ CRCW1206-P	CRCW1210-P	CRCW1218-P	CRCW2010-P	CRCW2512-P
Rated Dissipation at P <sub>70</sub> <sup>(1)</sup>	W	0.063	0.1	0.125	0.25	0.33	1	0.5	1
Operating Voltage U <sub>max.</sub> AC <sub>RMS</sub> /DC	V	50	75	150	200	200	200	400	500
Insulation Voltage U <sub>ins</sub> (1 min)	V	75	100	200	300	300	300	300	300
Insulation Resistance	Ω				> .	10 <sup>9</sup>			
Operating Temperature Range	°C				- 55 to	+ 155			
Failure Rate	h <sup>-1</sup>				0.3 x	( 10 <sup>-9</sup>			
Weight	mg	0.65	2	5.5	10	16	29.5	25.5	40.5


#### Note

<sup>(1)</sup> The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.






PACKAGING						
MODEL	CODE	QUANTITY	CARRIER TAPE	WIDTH	PITCH	REEL DIAMETER
D10/CRCW0402-P	TD = RT7	10 000		8 mm	0	180 mm/7"
D10/ChCV0402-P	TE = RF4	50 000		0 111111	2 mm	330 mm/13"
	TA = RT1	5000				180 mm/7"
D11/CRCW0603-P	TB = RT5	10 000		8 mm	4 mm	285 mm/11.25"
	TC = RT6	20 000				330 mm/13"
	TA = RT1	5000		8 mm	4 mm	180 mm/7"
D12/CRCW0805-P	TB = RT5	10 000	Paper tape acc. to IEC 60068-3			285 mm/11.25"
	TC = RT6	20 000	Type I			330 mm/13"
	TA = RT1	5000	] "	8 mm	4 mm	180 mm/7"
D25/CRCW1206-P	TB = RT5	10 000				285 mm/11.25"
	TC = RT6	20 000				330 mm/13"
	TA = RT1	5000		12 mm	4 mm	180 mm/7"
CRCW1210-P	TB = RT5	10 000				285 mm/11.25"
	TC = RT6	20 000				330 mm/13"
CRCW1218-P	TK = RT9	4000		12 mm	4 mm	180 mm/7"
CRCW2010-P	TF = R02	4000	Blister tape acc. to IEC 60068-3	12 mm	4 mm	180 mm/7"
CRCW2512-P	TG = R67	2000	Type II	12 mm	8 mm	180 mm/7"
	TH = R82	4000	· ·		4 mm	100 11111/7





## **FUNCTIONAL PERFORMANCE**



TEST PROCEDURES AND REQUIREMENTS						
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (Δ <i>R</i> )		
			Stability for product types:	STABILITY CLASS 1 OR BETTER		
			D/CRCW-P	1 Ω to 10 MΩ		
4.5	-	Resistance	-	± 0.25 %; ± 0.5 %; ± 1 %		
4.7	-	Voltage proof	$U = 1.4 \times U_{ins}$ ; 60 s	No flashover or breakdown		
4.13	-	Short time overload	$U = 2.5 \text{ x } \sqrt{P_{70} \text{ x } R} \le 2 \text{ x } U_{\text{max.}};$ duration acc. to style	± (0.25 % R + 0.05 Ω)		
417.0	1.17.2 58 (Td)	Caldavahilitu	Solder bath method; Sn60Pb40 non-activated flux; $(235 \pm 5)$ °C $(2 \pm 0.2)$ s	Good tinning (≥ 95 % covered) no visible damage		
4.17.2		Solderability	Solder bath method; Sn96.5Ag3Cu0.5 non-activated flux; (245 ± 5) °C (3 ± 0.3) s	Good tinning (≥ 95 % covered) no visible damage		
4.8.4.2	-	Temperature coefficient	(20/- 55/20) °C and (20/125/20) °C	± 50 ppm/K; ± 100 ppm/K		
4.32	21 (Uu <sub>3</sub> )	Shear (adhesion)	RR 1608 and smaller: 9 N RR 2012 and larger: 45 N	No visible damage		
4.33	21 (Uu <sub>1</sub> )	Substrate bending	Depth 2 mm; 3 times	No visible damage, no open circuit in bent position $\pm$ (0.25 % $R$ + 0.05 $\Omega$ )		
4.19	14 (Na)	Rapid change of temperature	30 min at - 55 °C; 30 min at 125 °C 5 cycles 1000 cycles	± (0.25 % R + 0.05 Ω) ± (1 % R + 0.05 Ω)		



TEST PROCEDURES AND REQUIREMENTS						
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (△R)		
			Stability for product types:	STABILITY CLASS 1 OR BETTER		
			D/CRCW-P	1 Ω to 10 MΩ		
4.23	-	Climatic sequence:	-			
4.23.2	2 (Ba)	Dry heat	125 °C; 16 h			
4.23.3	30 (Db)	Damp heat, cyclic	55 °C; ≥ 90 % RH; 24 h; 1 cycle			
4.23.4	1 (Aa)	Cold	- 55 °C; 2 h	± (1 % R + 0.05 Ω)		
4.23.5	13 (M)	Low air pressure	1 kPa; (25 ± 10) °C; 1 h			
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; ≥ 90 % RH; 24 h; 5 cycles			
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R}$			
			$U = \sqrt{P_{70} \times R} \le U_{\text{max.}};$ 1.5 h on; 0.5 h off;			
4.25.1	-	Endurance at 70 °C	70 °C; 1000 h	± (1 % R + 0.05 Ω)		
			70 °C; 8000 h	± (2 % R + 0.05 Ω)		
4.18.2	58 (Td)	Resistance to soldering heat	Solder bath method $(260 \pm 5)$ °C; $(10 \pm 1)$ s	± (0.25 % R + 0.05 Ω)		
4.35	-	Flamability, needle flame test	IEC 60695-11-5; 10 s	No burning after 30 s		
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; (93 ± 3) % RH; 56 days	± (1 % R + 0.05 Ω)		
4.25.3	-	Endurance at upper category temperature	155 °C, 1000 h	± (1 % R + 0.05 Ω)		
4.40	-	Electrostatic discharge (human body model)	IEC 61340-3-1; 3 pos. + 3 neg. discharges; ESD voltage acc. to size	± (1 % R + 0.05 Ω)		
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; 50 °C; method 2	No visible damage		
4.30	45 (XA)	Solvent resistance of marking	Isopropyl alcohol; 50 °C; method 1, toothbrush	Marking legible, no visible damage		
4.22	6 (Fc)	Vibration, endurance by sweeping	$f=10 \text{ Hz to } 2000 \text{ Hz}; \\ x, y, z \leq 1.5 \text{ mm}; \\ A \leq 200 \text{ m/s}^2; \\ 10 \text{ sweeps per axis}$	± (0.25 % R + 0.05 Ω)		
4.37	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R}$ $\leq 2 \times U_{\text{max.}};$ 0.1 s on; 2.5 s off; 1000 cycles	± (1 % R + 0.05 Ω)		
4.27	-	Single pulse high voltage overload, 10 µs/700 µs	$\hat{U} = 10 \times \sqrt{P_{70} \times R}$ $\leq 2 \times U_{\text{max.};}$ 10 pulses	± (1 % R + 0.05 Ω)		

All tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 140400, sectional specification
- EN 140401-802, detail specification
- IEC 60068-2-x, variety of environmental test procedures

Packaging of components is done in paper or blister tapes according to IEC 60286-3.



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.