	4			3			2			1	
ITEM	CONNECTOR PART NO.					Applicable Housings					
1	SSH-003T-P0.2-H					SH SERIES			APSH SERIES		
2	UL1571, 28 AWG	BLACK - BCD							NG PART NO		
									VITHOUT	•	
									TRUSIONS		
					NU. U		WITH PROTRUS			HOUSING PART NO.	
					2		SHR-02V-S-B	SHR-02		APSHR-03V-S	
					3		SHR-03V-S-B	SHR-03			
					4			SHR-04			
					5		SHR-05V-S-B	SHR-05			
					6		SHR-06V-S-B	SHR-06			
					/		SHR-07V-S-B	SHR-07			
					8		SHR-08V-S-B	SHR-08			
					9		SHR-09V-S-B	SHR-09			
					10		SHR-10V-S-B	SHR-10			
					11		SHR-11V-S-B	SHR-11			
					12		SHR-12V-S-B	SHR-12			
					13		SHR-13V-S-B	SHR-13			
					14		SHR-14V-S-B	SHR-14			
					15		SHR-15V-S-B	SHR-15	SV-S		
					20		SHR-20V-S-B	-			
			(58.6 +/- 5.0) 50.8 +/- 5.0		1					Electrical Specifications Current: 1.0A AC/DC	
			2			SCALE			JST	Voltage: 50V AC/DC	
			Ú				1:1				
3	Add electrical specificat	ions		7/2/2018	SP	tolerance	ns are in MM with a e of +/- 3.0 unless	DESCRIPTION 1.0 mm Pitch SH &	& APSH Series Star DOUBLE-END	ndard Leads - 2" Inside Length D LEADS	
	Add electrical specificat Revised wire to BCD (Hi		tter processing	7/2/2018 8/4/2017	SP SP	All dimension tolerance <u>otherv</u> DRAWN BY	ns are in MM with a of +/- 3.0 unless vise specified.		DOUBLE-END	DLEADS	
3 2 1		tachi) type for be	·			All dimension tolerance <u>otherv</u> DRAWN BY	ns are in MM with a e of +/- 3.0 unless vise specified. N PILKINGTON	1.0 mm Pitch SH &	DOUBLE-END	0 LEADS 8K51	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.