

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



EVO connector set, B24 series, plastic housing, consisting of sleeve housing, panel mounting base, push-in contact inserts: 1407735, 1407736, 1407660, 1407656, 1407671

Your advantages

- Both contact insert PE sheets are connected by means of a metal frame integrated in the sleeve housing
- Metal inlays ensure leading PE contact with angled plugs
- Halogen-free plastic
- Marking label can be attached



Key Commercial Data

Packing unit	1 pc	
GTIN	4 0 4 6 3 5 6 8 3 4 1 1 7	
GTIN	4046356834117	

Technical data

General

Number of positions	24+PE	
Туре	B24	
Connection method	Push-in connection	
Cable outlet	straight	
	lateral	
Degree of protection for housing	IP66	
	12 (UL 50e)	
Connection method	Push-in connection	



Technical data

General

Rated voltage (III/3)	500 V	
Rated surge voltage	6 kV	
Rated current	16 A	
Conductor cross section	0.14 mm ² 2.5 mm ² (with ferrule)	
Connection cross section AWG	26 14 (with ferrule)	
External cable diameter	11 mm 21 mm	
Ambient temperature (operation)	-40 °C 100 °C	
Length of the assembly cutout	113 mm	
Width of the assembly cutout	35 mm	
Housing material	PA	
Contact carrier material	PA	
Locking latch material	PA	
Integrated protective cover	Yes	

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50	
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"	

Articles in set

Contact insert - HC-B24-I-PT-F - 1407735



Contact insert, number of positions: 24+PE, size: B24, number of connections per position: 1, Socket, Push-in connection, 500 V, 16 A, 0.14 mm² ... 2.5 mm², application: Power

Contact insert - HC-B24-I-PT-M - 1407736



HEAVYCON pin insert, B24 series, 24 + PE-pos., push-in connection



Articles in set

Housing - HC-EVO-B24-BWSC-PLRBK - 1407660



HEAVYCON EVO panel mounting base, plastic housing, B24, with single locking latch, height 30.5 mm, with flat gasket, with protective cover

Housing - HC-EVO-B24-HHFS-PLBK - 1407656



HEAVYCON EVO sleeve housing, plastic, with bayonet flange for EVO screw connection, B24, for single locking latch, height: 87.5 mm, without EVO screw connection

Cable gland - HC-B-G-M32-PLRBK - 1407671



EVO plastic cable gland with bayonet locking, for housing series B, size M32, cable diameter: 11 ... 21 mm

Approvals		
Approvals		
Approvals		
EAC / EAC / DNV GL		
Ex Approvals		
Approval details		
EAC	EAC	RU C- DE.Al30.B.01102
EAC	EAC	EAC-Zulassung



Approvals

DNV GL https://approvalfinder.dnvgl.com/ TAE000037S

Phoenix Contact 2019 © - all rights reserved http://www.phoenixcontact.com

PHOENIX CONTACT GmbH & Co. KG Flachsmarktstr. 8 32825 Blomberg Germany Tel. +49 5235 300

Fax +49 5235 3 41200 http://www.phoenixcontact.com