
Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering



The Type FCP's combination of high capacitance density and excellent high frequency response makes it a great choice for wireless and instrumentation applications.

Type FCP stacked metallized polyphenelene sulfide (PPS) film capacitors offer high capacitance per unit volume, stable capacitance and DF over a wide temperature range, and excellent high frequency performance. Type FCP capacitors conform to standard EIA 0603, 0805, 1206, 1210, 1913 & 2416 surface mount case sizes and are packaged on tape and reel.

Highlights

- Stacked metallized polyphenylene sulfide (PPS) film.
- High operating temperature to +125 °C
- High capacitance per unit volume
- Excellent high frequency performance
- Typical Δ C from −55 °C to 105 °C ≤ ±1.5%
- Stable cap and DF over wide temperature range

Specifications

Capacitance Range	100 pF to 0.22 μF (1kHz at ≤5 Vrms)
Capacitance Tolerance	±5% (J) Standard, ±2% (G) Optional
Rated Voltage	16 Vdc and 50 Vdc
Dissipation Factor (Tan δ)	0.6% Max. (1 kHz at ≤5 Vrms)
Operating Temperature Range	-55 °C to $+125$ °C (See Voltage derating chart for 0.12 - 0.22 μF above 105 °C)
Dielectric Strength	150% of rated Vdc for 60 s
Insulation Resistance	3000 MΩ Min. at 20 °C, after 60 s (16 Vdc rated, test 10 Vdc; 50 Vdc rated, test 50 Vdc)
Construction	Stacked metallized polyphenylene sulfide (PPS) film. Terminations are lead free with a Sn-Ag-Cu solder finish.
Life Test	Capacitors subjected to 1000 hours of maximum rated temperature and 125% of the rated voltage will not have any significant visual damage, thecapacitance will be within ±2% of the initial measured value, DF will be a maximum of 0.66%, and IR will be a minimum of 1000 Megohms.
Resistance to Soldering Heat	Capacitors subjected to a maximum of 260 °C reflow soldering process will not have any significant visual damage, the dielectric strength will be as specified, the capacitance will be within ±3% of the initial measured value, DF will be a maximum of .66%, and IR will be a minimum of 1000 Megohms.
Moisture Resistance	Capacitors subjected to 1000 h at 40 °C and 90% to 95% RH and rated voltage will not have any significant visual damage, will withstand 1.3 times the rated voltage for one minute, the capacitance will be within $\pm 2\%$ of the initial measured value, DF will be a maximum of 0.9%, and IR will be a minimum of 1000 Megohms.
	RoHS Compliant


Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering Ratings


	50 Vdc		16 Vdc		Capacitance		
Case	Catalog	Case	Catalog				
Code	Part Number	Code	Part Number	(pF)	(nF)	(μ F)	
	FCP0805H101J-J1		FCP0603C101J-K1	100	.10	.00010	
- 0805	FCP0805H121J-J1		FCP0603C121J-K1	120	.12	.00012	
	FCP0805H151J-J1		FCP0603C151J-K1	150	.15	.00015	
	FCP0805H181J-J1	7	FCP0603C181J-K1	180	.18	.00018	
	FCP0805H221J-J1		FCP0603C221J-K1	220	.22	.00022	
	FCP0805H271J-J1		FCP0603C271J-K1	270	.27	.00027	
	FCP0805H331J-J1	1	FCP0603C331J-K1	330	.33	.00033	
	FCP0805H391J-J1		FCP0603C391J-K1	390	.39	.00039	
	FCP0805H471J-J1		FCP0603C471J-K1	470	.47	.00047	
	FCP0805H561J-J1	0603	FCP0603C561J-K1	560	.56	.00056	
	FCP0805H681J-J1		FCP0603C681J-K1	680	.68	.00068	
	FCP0805H821J-J1		FCP0603C821J-K1	820	.82	.00082	
	FCP0805H102J-J1	7	FCP0603C102J-K1	1000	1.00	.0010	
	FCP0805H122J-J1		FCP0603C122J-K1	1200	1.20	.0012	
	FCP0805H152J-J1		FCP0603C152J-K1	1500	1.50	.0015	
	FCP0805H182J-J1	1	FCP0603C182J-K1	1800	1.80	.0018	
	FCP0805H222J-J1		FCP0603C222J-K1	2200	2.20	.0022	
	FCP0805H272J-J1		FCP0603C272J-K1	2700	2.70	.0027	
	FCP1206H332J-H1		FCP0805C332J-J1	3300	3.30	.0033	
1206	FCP1206H392J-H1		FCP0805C392J-J1	3900	3.90	.0039	
	FCP1206H472J-H1		FCP0805C472J-J1	4700	4.70	.0047	
	FCP1206H562J-H1	805	FCP0805C562J-J1	5600	5.60	.0056	
	FCP1206H682J-H1		FCP0805C682J-J1	6800	6.80	.0068	
	FCP1206H822J-H2		FCP0805C822J-J2	8200	8.20	.0082	
	FCP1206H103J-H2		FCP0805C103J-J2	10000	10	.010	
	FCP1210H123J-G1		FCP1206C123J-H1	12000	12	.012	
	FCP1210H153J-G1		FCP1206C153J-H1	15000	15	.015	
	FCP1210H183J-G2		FCP1206C183J-H1	18000	18	.018	
1210	FCP1210H223J-G2	1 [FCP1206C223J-H1	22000	22	.022	
	FCP1210H273J-G2	1206	FCP1206C273J-H2	27000	27	.027	
	FCP1210H333J-G3		FCP1206C333J-H2	33000	33	.033	
1	FCP1210H393J-G3	1	FCP1206C393J-H3	39000	39	.039	
	FCP1913H473J-E1		FCP1206C473J-H3	47000	47	.047	
1913	FCP1913H563J-E1		FCP1210C563J-G2	56000	56	.056	
	FCP1913H683J-E1		FCP1210C683J-G2	68000	68	.068	
1	FCP1913H823J-E2	1210	FCP1210C823J-G3	82000	82	.082	
	FCP1913H104J-E2		FCP1210C104J-G3	100000	100	.100	
 	FCP2416H124J-D1			120000	120	.12	
	FCP2416H154J-D1			150000	150	.15	
2416	FCP2416H184J-D3			180000	180	.18	
	FCP2416H224J-D4			220000	220	.22	


Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering


Typical Temperature Characteristics


Typical Frequency Characteristics
















Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering


Outline Dimensions



Case Code	Outline Dimensions (in.)			Case Code	Outline Dimensions (mm)				Packaging	
	L ±0.008	W	T±0.008	t	(metric)	L ±0.2	W	T±0.2	t	Code
0603	0.063	0.032±0.006	0.028±0.006	0.014±0.008	1608	1.6	0.80±0.15	0.70±0.15	0.35±0.2	K1
0805	0.079	0.049±0.008	0.035	0.018±0.010 20	2012	2.0	.0 1.25±0.2	0.9	0.45±0.25	J1
			0.043		2012	2.0		1.1		J2
			0.035					0.9		H1
1206	0.126	0.126 0.063±0.008	0.043	0.026±0.012	3216	3.2	1.6±0.2	1.1	0.65±0.3	H2
			0.059					1.5		H3
			0.043					1.1		G1
1210	0.126	0.098±0.008	0.059	0.026±0.012	3225	3.2	2.5±0.2	1.5	0.65±0.3	G2
			0.083					2.1		G3
1913	0.189	0.189 0.130±0.012	0.059	0.031±0.012	4833	4.8	3.3±0.3	1.5	0.80±0.3	E1
			0.083					2.1		E2
			0.075					1.9		D1
2416	0.236	0.161±0.012	0.098	0.031±0.012	6041	6.0	4.1±0.3	2.5	0.80±0.3	D3
			0.110					2.8		D4





Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering




If the temperature on the surface of the capacitor is above 105°C, then the maximum voltage for FCP 50 Vdc ratings from .12 µF to .22µF must be derated linearly from full rated voltage at 105°C to 75% of the rated voltage at 125°C.


FCP 0805 50 Vdc Rating Vrms and Arms vs. Frequency






FCP 1206 50 Vdc Rating Vrms and Arms vs. Frequency






Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering


FCP 1210 50 Vdc Rating Vrms and Arms vs. Frequency




FCP 1913 & 2416 50 Vdc Rating Vrms and Arms vs. Frequency



Maximum AC Voltage FCP 16Vdc Series




Stable Stacked Metallized Film (PPS) Chips for Reflow Soldering Typical Applications



The capacitance of SMT film chips is much more stable with applied voltage and with changes in temperature than multilayer ceramic capacitors. Add in the low ESR characteristics of film chips and the final result is improved performance in filter circuit applications.

PLL Circuit: Cellular phone, Blue Tooth, Data Communication Cards



In PLL circuit applications, FCP SMT film capacitor advantages are tight tolerance on the capacitance value, stable capacitance with temperature, faster lock-up times, and no noise due to piezoelectric effects.

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.