# **Leaded Thermistors**Interchangeable Thermistor

# KT Series Standard Precision Interchangeable Thermistors




#### **Description**

Littelfuse precision interchangeable thermistors are low cost, highly accurate, stable devices designed specifically for temperature sensing and control applications. They are particularly suited for uses where their precision interchangeability eliminates the necessity for costly individual circuit calibration.

### **Options**

- Non-standard resistance values and tolerances
- Special lead materials and lengths
- Special encapsulants or probe housings

#### **Dimensions**




Dimensions shown in inches.

Α	В	С	D		
0.250"	30 AWG	0.095"	1.5"		
Nom	0.010"	Max	±0.250"		

#### **Features**

- High accuracy
- Fast thermal response
- Low cost
- Small size
- Epoxy encapsulated
- High stability
- Long life
- R/T Curve-matched

# **Part Numbering System**



Note: Not all combinations of Part Number codes are available. Contact Littelfuse for details.



# KT Series Standard Precision Interchangeable Thermistors

## **Specifications**

Part Number	Resistance Ohms @ 25°C	Accuracy (±°C) 0-70°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Max. Power Rating (mW)	Dissipation Constant, Nominal (mW/°C)	Thermal Time Constant, Max Still Air (seconds)	Thermal Time Constant, Max Well Stirred Oil (seconds)	Temperature Range (°C)	Storage & Operation Temp for Best L/T Stability (°C)
KT102J2	1000	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT222J2	2252	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT302J2	3000	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT502J2	5000	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT602J2	6000	±0.2°C	J	-4.4	4140	30	1	10	1	-80 to +150	-80 to +75
KT602J2	6000	±0.1°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT103G2	10000	±0.2°C	G	-4.04	3575	30	1	10	1	-80 to +150	-80 to +75
KT103J2	10000	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT203J2	20000	±0.2°C	J	-4.4	4140	30	1	10	1	-80 to +150	-80 to +75
KT303J2	30000	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT503J2	50000	±0.2°C	J	-4.4	3892	30	1	10	1	-80 to +150	-80 to +75
KT503R2	50000	±0.2°C	R	-4.68	3892	30	1	10	1	-80 to +150	-80 to +75
KT104R2	100000	±0.2°C	R	-4.68	3892	30	1	10	1	-80 to +150	-80 to +75

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: <a href="https://www.littelfuse.com/disclaimer-electronics">www.littelfuse.com/disclaimer-electronics</a>