HIGH-SPEED LTE NETWORKING PLATFORM

DIGI TRANSPORT LR54

High-speed LTE Advanced and Wi-Fi router in a durable hardware package for demanding M2M applications

Digi TransPort[®] LR54 is a high-speed LTE Advanced networking platform designed for retail, commercial and managed networking applications across distributed enterprises. Each device features an LTE Advanced CAT6 modem with speeds up to 300 Mbps and support for global deployments with a single hardware version, as well as a 4-port Gigabit Ethernet switch and serial port for console access. The routers include license-free enterprise software features like VPN, firewall and SNMP.

The two FIPS models make use of an embedded FIPS 140-2 validated cryptographic module for all encryption and authentication functions. The LR54 FIPS model is often used

FEATURES AND BENEFITS

DIGI

- High-speed LTE Advanced for digital content and business networking applications
- Powerful dual Wi-Fi radios provide 802.11 b/g/n/ac _ connection to local users and end devices
- Automated fail-over/fail-back between Ethernet, Cellular (dual SIMs), and IPsec tunnels
- Enables compliance with NIST SP 800-171 requirement for FIPS-validated cryptography
- On-board Python environment for custom application programming
- Digi Remote Manager[®] provides mass configuration, device management and troubleshooting tools

RELATED PRODUCTS



sPort®



Digi TransPort®



Digi TransPort® WR44 R






Digi Remote

as a VPN gateway to bridge local private subnets through public or untrusted networks, ensuring message privacy and integrity.

The Wi-Fi variant features dual-band, dual-concurrent 5 GHz and 2.4 GHz radios, personal/enterprise security, and multiple SSIDs for maximum range and throughput performance in M2M applications.

Digi TransPort LR54 is ideal for connecting:

- Retail branch sites
- Digital media installations
- Self-service kiosks
- Security monitoring equipment
- Remote offices/equipment
- Guest and employee Wi-Fi users



SPECIFICATIONS	Digi TransPort [®] LR54						
WIRELESS INTERFACES							
CELLULAR*							
LTE/HSPA+	Coverage: North America/EMEA LTE Advanced CAT 6: 700(B12,B13,B29)/800(B20,B26)/850(B5)/900(B8)/AWS(B4)/1800(B3)/ 1900(B2,B25)/2100(B1)/2300(B30)/2500(B41)/2600(B7) 3G HSPA+: 850/900/AWS/1800/1900/2100 MHz Transfer rate (max): 300 Mbps down, 150 Mbps up Approvals: PTCRB, AT&T, Verizon						
CONNECTOR	(2) 50 Ω SMA (Center pin: female)						
SIM SLOTS	(2) Mini-SIM (2FF)						
SIM SECURITY	SIM slot cover plate						
WI-FI							
802.11	Wi-Fi maximum data rates: 54 Mbps (802.11a); 11 Mbps (802.11b); 54 Mbps (802.11g); 300 Mbps (802.11n); 866 Mbps (802.11ac)						
TX POWER	2.4 GHz 19 dBm (802.11g/n), 19 dBm (802.11b) 5 GHz 22.9 dBm for all modes						
RX SENSITIVITY	-87 dBm / 11 Mbps (802.11b) -71 dBm / 54 Mbps and -90 dBm / 6 Mbps (802.11a) -74 dBm / 54 Mbps and -92 dBm / 6 Mbps (802.11g) -66 dBm / 300 Mbps and -92 dBm / 6 Mbps (802.11n 2.4 GHz) -67 dBm / 300 Mbps and -89 dBm / 6 Mbps (802.11n 5 GHz) -57 dBm / 866 Mbps and -83 dBm / 29 Mbps (802.11ac)						
MODES	Access point, support for multiple SSID						
SECURITY	Mixed WPA/WPA2 Personal; WPA2 Personal; Mixed WPA/WPA2 Enterprise; WPA2 Enterprise						
CONNECTORS	(2) 50 Ω RP-SMA (Center pin: male)						
WIRED INTERFACES							
SERIAL							
PORTS	(1) DB-9; DCE						
STANDARD	RS-232						
SIGNAL SUPPORT	TXD, RXD, RTS, CTS, DTR, DCD, DSR, RI						
FLOW CONTROL	Software (XON/XOFF), hardware supported						
ETHERNET							
PORTS	(4) RJ-45; 10/100/1000 Mbit/s (auto-sensing)						
MANAGEMENT							
REMOTE MANAGEMENT	Digi Remote Manager° (cloud based); SNMP v1/v2c/v3 (user installed/managed)						
LOCAL MANAGEMENT	Web interface (HTTPS); CLI (SSH, Serial port)						
MEMORY	256 MB of Flash; 100 MB user available memory						
POWER							
INPUT	12 VDC						
CONNECTOR	4-pin terminal block; Power supply comes with US plug (IEC Type A) and an EU plug (IEC Type C)						
CONSUMPTION	13.68W max, 11.4W average						
DC POWER SUPPLY	100-240 VAC 50/60 Hz						
PHYSICAL							
DIMENSIONS (L X W X H)	8.15 in x 5.5 in x 1.5 in (207 mm x 140 mm x 38 mm)						
WEIGHT	2.90 lb (1.32 kg)						
STATUS LEDS	Power, WWAN signal, WWAN service, SIM 1, SIM 2, 2.4 GHz and 5 GHz LEDs on Wi-Fi version						
MATERIAL/RATING**	Industrial (Metal) / IP30						
MOUNTING	Wall mount bracket sold separately						

* Transfer rates are network operator dependent

 $^{\star\star} The enclosure rating is self-declared and has not been formally verified by an independent lab$

SPECIFICATIONS	Digi TransPort [®] LR54					
ENVIRONMENTAL						
OPERATING TEMPERATURE ***	-20° C to +70° C					
STORAGE TEMPERATURE	-40° C to +85° C					
RELATIVE HUMIDITY	0% to 95% (non-condensing) @ 25° C					
APPROVALS						
CELLULAR	PTCRB					
WI-FI	Wi-Fi Alliance [®] Wi-Fi CERTIFIED™					
MATERIALS	RoHS					
SAFETY	CB Scheme, IEC 60950-1					
EMISSIONS/IMMUNITY	CE, FCC Part 15 Class B					
WARRANTY						
PRODUCT WARRANTY	3 years + Digi Foundations****					

The enclosure rating is self-declared and has not been formally verified by an independent lab *Digi Foundations can extend the standard three-year warranty to a Limited Lifetime Warranty that provides replacement with a new or similar Digi product for a period of five years from the data of purchase. After five years from the purchase date, the warranty value will revert to a 40 percent credit towards the MSRP of an equivalent product from Digi.

ENTERPRISE SOFTWARE	DESCRIPTION
MANAGEMENT PROTOCOLS	HTTPS, TLS1.0/1.1/1.2, SFTP, SCP,SNMP (v1/v2c/v3), SSHv2,CLI for web management; remote management via Digi Remote Manager; protocol analyzer, ability to capture PCAP for use with Wireshark, Syslog support for streaming event and system logs
SECURITY/VPN	Stateful inspection firewall with scripting; VPN: IPSec with IKEv1; OpenVPN (32) VPN Tunnels; Cryptology: SHA-1/SHA256, RSA, DH Groups 5,14,15,16,17,18 ; Encryption: AES up to 256-bit; Ethernet Port Isolation; RADIUS
ROUTING/FAILOVER	NAT, NAPT with IP Port Forwarding; IP Failover: Automatic failover/failback to second GSM network/Standby APN, IP Port forwarding
OTHER PROTOCOLS	IPv4, IPv6, DHCP, GRE, DMNR, DSCP (QoS)

PRODUCT IMAGES

DIGI TRANSPORT LR54



DIGI TRANSPORT LR54 (WITH WI-FI)





DIGI REMOTE MANAGER®

North Anna (D	Device "yeps 0			2				ACCOUNT
DEVICE HEALTH CONF	GURATION: TR	ANSPORT WE	11				0 ×	ALABA SUMMARY
нте	EMBLED	HESOLI					ACTORS	
Y GREED								
21 Average Laborary		-	-100	-	-2010	-	-	
as macroam Latercy		-	-14.00	-		-		
35 Minimum Latimety		-	-26 m	-	-814	-		
Bi humps (alony		- 10	10.00		100.00	-	-	Barta facilit e 📕 decar Statione 2:
35 Macrourt Labre)		-	-28-86		-214	-		MONTON STATUS
35 Holmuni Latorez		-	-10.00	-	1000	-	-	and the statut
45 Aurope Latency		-	-846		- 200		-	
4) Machael Labora		-	1914		100	-	-	
45 Misimum Labertz		-	-14	-	101.00	-	-	
							HeryB	Basermaning B B Germating S

INFRASTRUCTURE

5

- Hosted in a commercial-grade SAS 70-certified environment
- Superior availability, operating to 99.9% or greater
- Open APIs available to support application development

CAPABILITIES

- Centralized management of remote devices over 3G/4G LTE
- Define standard configurations and automatically monitor individual devices _ for PCI security compliance
- Report and alert on performance statistics, including connection history, signal quality, latency, data usage and packet loss
- No servers or applications to operate and maintain
- Complete tasks for your entire device network in minutes
- Edit configurations and update firmware for your individual devices or groups
- Monitor the status and location of your remote device via a web browser
- Active or deactivate cellular lines and monitor data to ensure you never incur overage charges

SECURITY

- Certified SSAE-16 facilities
- Member of the Cloud Security Alliance
- Over 175 Security Controls in place to protect your data
- Enables compliance with security frameworks like PCI, HIPAA, NIST and more
- Earned SkyHigh's Cloud Trust Program highest ranking of Enterprise-Ready

PART NUMBERS	DIGI TRANSPORT LR54						
LR54-AA401	Digi TransPort LR54 - 4G LTE North America/EMEA, No Wi-Fi						
LR54-AW401	Digi TransPort LR54 - 4G LTE North America/EMEA, Wi-Fi						
LR54-AA403	Digi TransPort LR54 - 4G LTE North America/EMEA, No Wi-Fi, FIPS 140-2						
LR54-AW403	Digi TransPort LR54 - 4G LTE North America/EMEA, Wi-Fi, FIPS 140-2						
PART NUMBERS	DIGI FOUNDATIONS ADD-ONS						
DGF-BDL-PREM-1YR	Digi Foundations add-on bundle 1 year						
DGF-BDL-PREM-3YR	Digi Foundations add-on bundle 3 years						
DGF-BDL-PREM-5YR	Digi Foundations add-on bundle 5 years						
PART NUMBERS	ACCESSORIES						
78000001	Mounting Bracket - Wall-mount						

FOR MORE INFORMATION PLEASE VISIT WWW.DIGI.COM



DIGI SERVICE AND SUPPORT / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit www.digi.com/support.

© 1996-2019 Digi International Inc. All rights reserved. All trademarks are the property of their respective owners.

95003316 A16/619

DIGI INTERNATIONAL WORLDWIDE HQ 877-912-3444 / 952-912-3444 / www.digi.com

DIGI INTERNATIONAL GERMANY +49-89-540-428-0

DIGI INTERNATIONAL JAPAN

DIGI INTERNATIONAL SINGAPORE +65-6213-5380

DIGI INTERNATIONAL CHINA +86-21-50492199 / www.digi.com.cn



+81-3-5428-0261 / www.digi-intl.co.jp