
# 230 EDLC-HV ENYCAP™


Vishay BCcomponents

# **Electrical Double Layer Energy Storage Capacitors** Up to 3 V Operating Voltage



www.vishay.com

Image is not to scale



QUICK REFERENCE	DATA
DESCRIPTION	VALUE
Nominal case sizes (Ø D x L in mm)	$\begin{array}{c} 10 \times 20; \ 10 \times 25; \ 10 \times 30; \\ 12.5 \times 20; \ 12.5 \times 25; \ 12.5 \times 30; \\ 12.5 \times 40; \ 16 \times 20; \ 18 \times 20; \\ 16 \times 25, \ 18 \times 25; \ 16 \times 31; \\ 18 \times 31, \ 18 \times 35, \ 18 \times 40; \ 20 \times 40 \end{array}$
Rated capacitance range, $C_R$	5 F to 100 F
Rated voltage, U <sub>R</sub> (65 °C / 85 °C)	3.0 V / 2.6 V
Category temperature range	-40 °C to +85 °C
Endurance test at 85 °C	Up to 1500 h
Useful life at 85 °C	Up to 2000 h
Useful life at 20 °C	> 10 years
Shelf life at 20 °C	2 years
Cycle life	> 500 000 cycles

# **FEATURES**

- · Polarized energy storage capacitor with high capacity and energy density
- Rated voltage: 3.0 V
- Available in through-hole (radial) version
- Useful life: up to 2000 h at 85 °C
- Rapid charge and discharge
- Maintenance-free, no service necessary
- AEC-Q200 gualified
- UL 810A recognized
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

# APPLICATIONS

- Power backup
- Burst power support
- Storage device for energy harvesting
- Micro UPS power source
- Energy recovery

# MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in F)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- · Code indicating factory of origin
- Logo of manufacturer
- Negative terminal identification
- Series number (230)

# PACKAGING

Supplied loose in box, taped ammo, or in ESD trays.



COMPLIANT

Revision: 02-Feb-2021

For technical questions, contact: <u>energystorage@vishay.com</u>



# 230 EDLC-HV ENYCAP™


# Vishay BCcomponents

SELECTION CHART FOR C <sub>R</sub> , U <sub>R</sub> , AND RELEVAN	T NOMINAL CASE SIZES
C <sub>R</sub> (F)	U <sub>R</sub> (V) = 3.0 V
5	10 x 20
7	10 x 25
8	12.5 x 20
10	10 x 30
12	12.5 x 25
15	12.5 x 30
20	16 x 20
22	12.5 x 40
25	16 x 25; 18 x 20
30	18 x 25
35	16 x 31
40	18 x 31 <sup>(1)</sup>
50	18 x 35
60	18 x 40
100	20 x 40

Note

<sup>(1)</sup> Preferred case size

### **DIMENSIONS** in millimeters **AND AVAILABLE FORMS**






Fig. 2 - Form CA / TRAY: long leads

#### Fig. 3 - Form TFA: taped in box (ammopack)

### Table 1

DIMENSIONS in millimeters, MASS, AND PACKAGING QUANTITIES									
NOMINAL CASE SIZE	CASE CODE	Ød	Ø D <sub>max.</sub>		F	MASS	PACKAGING Q		TITIES
ØDxL	OAGE CODE	bu	D D max.	L <sub>max.</sub>	•	(g)	FORM CA	FORM TFA	FORM TRAY
10 x 20	16	0.6	10.5	22	$5.0 \pm 0.5$	≈ 2.2	500	800	-
10 x 25	16L	0.6	10.5	27	$5.0 \pm 0.5$	≈ 3.0	500	800	-
10 x 30	16LL	0.8	10.5	32	$5.0 \pm 0.5$	≈ 3.5	500	800	-
12.5 x 20	17	0.6	13.0	22	$5.0 \pm 0.5$	≈ 4.0	500	500	-
12.5 x 25	18	0.6	13.0	27	$5.0 \pm 0.5$	≈ 5.0	250	500	-
12.5 x 30	18L	0.8	13.0	33.5	$5.0 \pm 0.5$	≈ 5.5	250	500	-
12.5 x 40	18LL	0.8	13.0	42.5	$5.0 \pm 0.5$	≈ 7.0	250	-	-
16 x 20	19a	0.8	16.5	22	$7.5 \pm 0.5$	≈ 6.0	250	250	200
16 x 25	19	0.8	16.5	27	$7.5 \pm 0.5$	≈ 8.0	250	250	200
18 x 20	1820	0.8	18.5	22	$7.5 \pm 0.5$	≈ 7.0	100	250	200
18 x 25	1825	0.8	18.5	27	$7.5 \pm 0.5$	≈ 10.0	100	250	200
16 x 31	20	0.8	16.5	33.5	$7.5 \pm 0.5$	≈ 9.0	100	250	200
18 x 31	1831	0.8	18.5	33.5	$7.5 \pm 0.5$	≈ 12.5	100	250	200
18 x 35	22	0.8	18.5	37.5	$7.5 \pm 0.5$	≈ 14.5	100	250	200
18 x 40	1840	0.8	18.5	42.5	$7.5 \pm 0.5$	≈ 16.5	100	-	150
20 x 40	2040	1.0	20.5	43.5	$7.5 \pm 0.5$	≈ 20.0	100	-	-

2

Document Number: 28450

For technical questions, contact: <u>energystorage@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u> www.vishay.com

# ELECTRICAL DATA

SYMBOL	DESCRIPTION
C <sub>R</sub>	Rated capacitance, tolerance -20 % / +50 %
I <sub>P</sub>	Max. peak current
١L	Max. leakage current after 0.5 h / 72 h at $U_R$

Note

- Unless otherwise specified, all electrical values in Table 2 apply at  $T_{amb}$  = 20 °C, P = 86 kPa to 106 kPa and RH = 45 % to 75 %

#### Table 2

**Vishay BCcomponents** 

### **ORDERING EXAMPLE**

Capacitor series 230 EDLC-HV

40 F / 3.0 V

Nominal case size: Ø 18 mm x 31 mm; Form TRAY Ordering code: MAL223091001E3

EL	ELECTRICAL DATA AND ORDERING INFORMATION																	
U <sub>R</sub> (V)	U <sub>MT</sub> <sup>(1)</sup> (V)	(V)	U <sub>S</sub> (V) (< 1 s)	(F)	NOMINAL CASE SIZE Ø D x L (mm)	E ESR <sub>AC</sub> PEAK EESR <sub>DC</sub> <sup>(3)</sup> INITIAL, CURRENT INITIAL 1 KHz (A)		li MA LEAK CURF AFT (mA)	X. AGE RENT ER	STO ENE E AT (W	RGY 「U <sub>R</sub>	ENE Ed A	CIFIC RGY T U <sub>R</sub> /kg)		ERING C AL2230			
65 °C	75 °C	85 °C					(	65 °C	85 °C	0.5 h	72 h	65 °C	85 °C	65 °C	85 °C	FORM CA	FORM TFA	FORM TRAY
3.0	2.8	2.6	3.15	5	10 x 20	45	32	12	10	2	25	0.006	0.005	2.8	2.1	51011E3	31011E3	-
3.0	2.8	2.6	3.15	7	10 x 25	40	28	12	10	3	35	0.009	0.007	2.9	2.2	51012E3	31012E3	-
3.0	2.8	2.6	3.15	8	12.5 x 20	42	25	15	12	4	40	0.010	0.008	2.5	1.9	51014E3	31014E3	-
3.0	2.8	2.6	3.15	10	10 x 30	31	24	15	12	4	45	0.013	0.009	3.6	2.7	51013E3	31013E3	-
3.0	2.8	2.6	3.15	12	12.5 x 25	34	23	17	14	5	55	0.015	0.011	3.0	2.3	51015E3	31015E3	-
3.0	2.8	2.6	3.15	15	12.5 x 30	27	20	20	17	6	70	0.019	0.014	3.4	2.6	51016E3	31016E3	-
3.0	2.8	2.6	3.15	20	16 x 20	28	22	25	20	8	75	0.025	0.019	4.2	3.1	51003E3	31003E3	91003E3
3.0	2.8	2.6	3.15	22	12.5 x 40	22	15	25	20	9	75	0.028	0.021	3.9	3.0	51017E3	-	-
3.0	2.8	2.6	3.15	25	16 x 25	26	20	25	20	8	75	0.031	0.023	3.9	2.9	51006E3	31006E3	91006E3
3.0	2.8	2.6	3.15	25	18 x 20	24	19	25	20	8	75	0.031	0.023	4.5	3.4	51004E3	31004E3	91004E3
3.0	2.8	2.6	3.15	30	18 x 25	23	17	30	25	12	140	0.038	0.028	3.8	2.8	51007E3	31007E3	91007E3
3.0	2.8	2.6	3.15	35	16 x 31	24	18	30	25	15	200	0.044	0.033	4.9	3.7	51002E3	31002E3	91002E3
3.0	2.8	2.6	3.15	40	18 x 31	22	16	35	30	20	200	0.050	0.038	4.0	3.0	51001E3	31001E3	91001E3
3.0	2.8	2.6	3.15	50	18 x 35	19	14	35	30	25	250	0.063	0.047	4.3	3.2	51008E3	31008E3	91008E3
3.0	2.8	2.6	3.15	60	18 x 40	17	13	35	30	30	300	0.075	0.056	4.5	3.4	51009E3	-	91009E3
3.0	2.8	2.6	3.15	100	20 x 40	17	13	35	30	50	500	0.125	0.090	6.3	4.7	51024E3	-	-

#### Notes

<sup>(1)</sup> U<sub>MT</sub> = rated voltage at 75 °C

<sup>(2)</sup>  $U_{CT}$  = rated voltage at upper category temperature

<sup>(3)</sup> Rated capacitance C<sub>R</sub> and maximum ESR<sub>DC</sub> are typical values for case sizes

### Table 3

NOMINAL CASE SIZE Ø D x L	CASE CODE	ENDURANCE AT 85 °C (h)	USEFUL LIFE AT 85 °C (h)
10 x 20	16	750	1000
10 x 25	16L	750	1000
10 x 30	16LL	750	1000
12.5 x 20	17	1000	1500
12.5 x 25	18	1000	1500
12.5 x 30	18L	1000	1500
12.5 x 40	18LL	1000	1500
16 x 20	19a	1000	2000
16 x 25	19	1000	2000
18 x 20	1820	1000	2000
18 x 25	1825	1000	2000
16 x 31	20	1000	2000
18 x 31	1831	1000	2000
18 x 35	22	1000	2000
18 x 40	1840	1000	2000
20 x 40	2040	1000	2000

3

Document Number: 28450



# Vishay BCcomponents

TEST PROCEDURES	AND REQUIR	EMENTS <sup>(1)</sup>					
NAME OF TEST	PROCEDURE (quick reference)						
Capacitance $C_R$ and $ESR_DC$	Measured by DC discharging method as described in "Measuring of Characteristics". (2)						
Maximum peak current	Non-repetitive current for maximum 1 s at specified operating temperature. Maximum operating voltage (refer to derating table) must not be exceeded. Usually to be tested with constant current discharge from $U_R$ to 0.5 x $U_R$ . Maximum current should not be used in normal operation and is only provided as reference value.						
Leakage current $I_L$	Measured at $U_R$ . Capacitor is charged to the rated voltage at 20 °C. Leakage current is the current at specitime that is required to keep the capacitor charged at the rated voltage.						
		apacitor of specified time at maximum category temperature $T_{max.}$ = 85 °C and derated um operating voltage U = 2.6 V, following parameters are valid within a timeframe as 3:					
Endurance	Capacitance	Within $\pm$ 30 % of minimum initial specified value					
	ESR	Less than 3 x initial specified value					
	Leakage	Within specified value					
		apacitor of specified time at maximum category temperature T <sub>max.</sub> = 85 °C and derated um operating voltage U = 2.6 V, following parameters are valid within a timeframe as 3:					
Useful life	Capacitance	Within ± 50 % of minimum initial specified value					
	ESR	Less than 4 x initial specified value					
	Leakage	Within specified value					
	After loading the capacitor of specified time at maximum category temperature T <sub>max.</sub> = 85 °C and without charge and under 40 % RH, following parameters are valid within a timeframe of 1000 h:						
Storage at upper	Capacitance	Within ± 30 % of minimum initial specified value					
category temperature	ESR	Less than 3 x initial specified value					
	Leakage	Within specified value					
Shelf life	Stored uncharged at 20 °C. Parameter within initial specification						
		ween rated voltage and half of rated voltage ${\rm U}_{\rm R}$ with constant current and 1 s rest between rge: $>500~000$ cycles					
Cycle life	Capacitance	Within $\pm$ 30 % of minimum initial specified value					
	ESR	Less than 3 x initial specified value					
	$E [Wh] = \frac{1}{2} \times C \times ($	U <sub>R</sub> ) <sup>2</sup> x 1/3600					
Stored energy E, specific energy Ed and Ev	Ed [Wh/kg] = ½ x C x (U <sub>R</sub> ) <sup>2</sup> x 1/3600 x 1/mass						
	Ev [Wh/L] = ½ x C x (U <sub>R</sub> ) <sup>2</sup> x 1/3600 x 1/volume						
Soldering	Hand or wave soldering allowed. For details refer to soldering requirements for radial aluminum electrolytic capacitors in supplementary document.						
Cleaning	For printed circuit board cleaning apply non-aggressive cleaning agents only. For details refer to cleaning requirements for aluminum electrolytic capacitors in supplementary docu						
Environmental conditions	Do not expose capacitors to • temperatures outside specified range • high humidity atmospheres • corrosive atmospheres, e.g. halogenides, sulphurous or nitrous gases, acid or alkaline solutions, etc. • environments containing oil and grease						

#### Notes

· General remark: temperatures to be measured at capacitor case

<sup>(1)</sup> Conditions: electrical measurements at 20 °C, unless otherwise specified

<sup>(2)</sup> Rated capacitance C<sub>R</sub> and ESR<sub>DC</sub>

# 230 EDLC-HV ENYCAP™



# **MEASURING OF CHARACTERISTICS**

www.vishay.com

### **CAPACITANCE (C)**

Capacitance shall be measured by constant current discharge method.

- Constant current charge with 10 mA/F to U<sub>B</sub>
- Constant voltage charge at U<sub>R</sub>
- Constant current discharge with 10 mA/F to 0.1 V




Fig. 4 - Voltage Diagram for Capacitance Measurement

Capacitance value C<sub>R</sub> is given by discharge current I<sub>D</sub>, time t and rated voltage U<sub>B</sub>, according to the following equation:

$$C_{R}[F] = \frac{I_{D}[A] x (t_{2}[s] - t_{1}[s])}{U_{1}[V] - U_{2}[V]}$$

- CR Rated capacitance, in F
- U<sub>R</sub> Rated voltage, in V
- U1 Starting voltage, 0.8 x U<sub>R</sub> in V
- U<sub>2</sub> Ending voltage, 0.4 x U<sub>R</sub> in V
- Voltage drop at internal resistance, in V  $\Delta U_3$
- Time from start of discharge until voltage U<sub>1</sub> is t1 reached, in s
- Time from start of discharge until voltage U<sub>2</sub> is t<sub>2</sub> reached, in s
- $I_D$ Absolute value of discharge current, in A

# EQUIVALENT SERIES RESISTANCE (ESR<sub>DC</sub>)

- Constant current charge to U<sub>R</sub>
- Constant voltage charge at U<sub>B</sub>
- Constant current discharge to 0.1 V

$$\mathsf{ESR}_{\mathsf{DC}}\left[\Omega\right] = \frac{\Delta \mathsf{U}_{\mathsf{3}}\left[\mathsf{V}\right]}{\mathsf{I}_{\mathsf{D}}\left[\mathsf{A}\right]}$$

ESR <sub>DC</sub>	Equivalent series resistance, in $\Omega$
$\Delta U_{R}$	Voltage drop at internal resistance, in V
Iп	Absolute value of discharge current, in A

Absolute value of discharge current, in A

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.