

14 JAN 19 Rev D

The Z45 Platform containing the part numbers X-2325807-X and X-2325811-X described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore, TE Connectivity (TE) makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, TE may change these requirements based on the results of additional testing and evaluation. Contact TE Engineering for further details. The Z35 Platform has completed qualification testing per the 501-19231 document listed in Section 2.1 of this document.

#### Mini CoB LED Holder Platform

#### SCOPE

#### 1.1. Content

This specification covers performances, tests and quality requirements of the Mini CoB LED Holder Platform with part numbers X-2213678-X & X-2213929-X applied according application specification 114-133062. Part numbers X-2325807-X and X-2325811-X applied per app specification 114-133107.

#### 1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 1 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

#### 1.3. Qualification Test Results

Successful qualification testing on the subject product line has not been completed. The Qualification Test Report number will be issued upon successful qualification testing.

## 2. APPLICABLE DOCUMENTS AND FORMS

The following documents and forms constitute a part of this specification to the extent specified herein. Unless otherwise indicated, the latest edition of the document applies.

#### 2.1. TE Documents

114-133062: Application Specification for Z35 Platform
 114-133107: Application Specification for Z45 Platform

• 114-32208: LUMAWISE LED Holders (for cross-reference of LED holders & customer COBs)

501-19231: Qualification Test Report – Z35 Platform
 501-XXXX: Qualification Test Report – Z45 Platform

## 2.2. Industry Documents

UL 8754: UL Standard for Safety Holders, Bases, and Connectors for Solid-State (LED)

Light Engines and Arrays

• IEC 60838-2-2: Miscellaneous lamp holders – Part 2-2: Particular requirements – Connectors for

LED-modules

#### 2.3. Reference Document

109-197 Test Specification (TE Test Specification vs EIA and IEC Test Methods)

#### 3. REQUIREMENTS

### 3.1. Design and Construction

Product shall be of the design, construction, materials and physical dimensions specified on the applicable product drawing.

# 3.2. Ratings

Wire: 18AWG to 20AWG, solid, stranded (maximum 16 strands for 18 AWG and maximum 7 strands for 20AWG) and fused.





# NOTE

The maximums for energy presented here are independent of each other. It is not possible to meet two of them without violating the third one.

Voltage	Current	Energy	Temperature
60V DC (maximum)	3 Ampere (maximum)	100W maximum	-40°C to 105° C (operating)

# 3.3. Test Requirements and Procedures Summary

Unless otherwise specified, all tests shall be performed at ambient environmental conditions.

REQUIREMENT		PROCEDURE			
Meets requirements of product drawing.		Visual, dimensional, and functional inspection according to the quality inspection plan.			
The product shall not have visible marks of damage, break, or defect before and after the execution of the tests.		EIA-364-18B			
ELECTRICAL					
Initial bulk resistance maximum $20m\Omega$ . Maximum $\Delta 20m\Omega$ of the bulk resistance after testing.	Оре	-364-23, Option 1 en voltage: 20 mV maximum rent 100 mA maximum			
No creeping discharge.  No flashover shall occur.  Leakage current shall not exceed 0.5 mA. Test between contact and ground plate with dummy LED mated.	The samples shall be exposed fo 48 hours to moist air having a relative humidity of 93±5% at a temperature of 25±2°C. Following the 48-hour period and while still exposed to moist air, the device shall be subjected to the dielectric Withstanding voltage test.  2.0 kV AC for 1 minute with 1-mn thick plastic insulated LED dummers.				
		1.6 kV AC for 1 minute with FR4 LED dummy having a distance of 1.4 mm from top contour edge of LED to contact pad.			
500 MΩ minimum	EIA	364-21			
Construction and base material of applied COB LED can give different results.	Voltage: 500 VDC for 1 minute. Tes between contact and ground plate.				
		EIA 364-70, Method 2			
		Measure temperature rise at 1 A and increase current in steps of 1 A. After a stabilization period of 1 hour and up to 5A. The holder with LED is mounted on a cooling device made from a bare aluminum plate with dimensions 80x100x8 mm.			
	Meets requirements of product drawing. The product shall not have visible marks damage, break, or defect before and after the execution of the tests.	Meets requirements of product drawing.  The product shall not have visible marks of damage, break, or defect before and after the execution of the tests. <b>ELECTRICAL</b> Initial bulk resistance maximum $20m\Omega$ .  Maximum $\Delta 20m\Omega$ of the bulk resistance after testing.  No creeping discharge.  No flashover shall occur.  Leakage current shall not exceed 0.5 mA. Test between contact and ground plate with dummy LED mated.  The data of the bulk resistance after testing.  The data of the bulk resistance and after the bulk resistance after testing.  The data of the bulk resistance and after the bulk resistance after testing.  The data of the bulk resistance and after the bulk resistance after testing.  The data of the bulk resistance and after the bulk resistance after testing.  The data of the data of the bulk resistance after testing.			

Figure 1 cont.

Rev D 2 of 4



TEST DESCRIPTION	REQUIREMENT	PROCEDURE		
	MECHANICAL			
Wire insertion force	Maximum 15N.  No visual damage. For test group 2 stranded wire can be omitted as it is omitted on wire insertion repairability section as well.	EIA 364-13 method A		
Wire retention force	Minimum 22.3N. No visual damage.	EIA 364-13 method A		
Vibration	No electrical discontinuity greater than 1µsec shall occur.  No physical damage.	EIA 364-28 Vibration frequency: 20 to 500 Hz, 3.10 g peak. Vibration direction: 3 mutually perpendicular directions Duration: 15 minutes each		
Mechanical Shock	No electrical discontinuity greater than 1µsec shall occur.  No physical damage.	EIA 364-27, Test Condition H Accelerated velocity: 30 G half sinusoidal shock pulses Number of shocks: 3 in each direction applied along 3 mutually perpendicular directions with 18 total shocks.		
LED repairability (during LED assembly in production)	LED still locks in holder. See note.	Mate and un-mate specimen 3 times. One un-mating/mating cycle: unscrew socket, remove LED, replace LED and screw down socket. Test should be done before any energized use in application.		
Wire insertion repairability (solid and tined wires only)	See note.	Extract wire and replace with new wire 3 times.  One cycle: extracting wire by turning and pulling, replace with same size wire		
	ENVIRONMENTAL			
Temperature life	See note	EIA-364-17, Method A, Test Condition 4 Subject mated specimens for 125 hours. Test temperature: 125°C		
Thermal shock	See note.	EIA-364-32, Test Condition VIII Subject specimens to 25 cycles between -40° and 105°C with 30-minute dwells at temperature extremes and 1- minute transition between temperatures.		

Figure 1 cont.

Rev D 3 of 4



TEST DESCRIPTION	REQUIREMENT	PROCEDURE
Damp heat cycling	See note.	EIA-364-31, Method IV
		Subject specimens to 10 cycles (10 days) between 25° and 65°C at 80 to 100% RH.
Contact normal force relaxation	Normal force should be at least 0.5N at maximum deflection.	500 hours on 125°C mounted on plate with dummy LED.
		Measurement points: initial and after 500h

# i

## NOTE

Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in Product Qualification/ Requalification Test Sequence shown in Figure 2.

# 3.4. Product Qualification and Requalification Test Sequence

	TEST GROUP (a)					
TEST OR EXAMINATION	1	2	3	4	5	6
	TEST SEQUENCE (b)					
Initial examination of product	1	1	1	1	1	1
Final Examination of Product	9	9	7	9	4	5
Contact resistance	2,4,6,8	2,4,6	2,4,6	2,4,6,8		2,4
Withstanding Voltage	3					
Insulation Resistance	5					
Temperature Rise	7					
Wire insertion force					2	
Wire retention force		7			3	
Vibration		3				
Mechanical Shock		5				
LED repairability (during LED assembly in production)			3			
Wire insertion repairability (solid and tined wires only)			5			
Temperature life				3		
Thermal shock				5		
Damp heat cycling				7		
Contact normal force relaxation						3(c)



## NOTE

- (a) Test groups 1,4 and 5 contain 5 samples on solid 18AWG, 5 samples on solid 20AWG, 5 samples on stranded 18AWG and 5 samples on stranded 20AWG. All other samples should contain a minimum of ten total samples.
- (b) Numbers indicate sequence in which tests are performed.
- (c) LLCR to be measured midway through step 3. LLCR to be measured right before 500h on 125°C and immediately after.

Figure 2

Rev D 4 of 4