WSBS8518...P4



Vishay Dale

еЗ

ROHS COMPLIANT

HALOGEN

FREE

GREEN (5-2008)

Power Metal Strip[®] Battery Shunt Resistor With M4 Tapped Holes and Sn Plated Terminals, Very Low Value (50 $\mu\Omega$, 100 $\mu\Omega$, 125 $\mu\Omega$, and 250 $\mu\Omega$)



DESIGN SUPPORT TOOLS AVAILABLE

FEATURES

- High power to resistor size ratio
- Proprietary processing technique produces extremely low resistance values
- Tapped holes aid in PCB mounting and / or a location to attach voltage sense pins
- Sn plating assists with PCB mounting and corrosion protection
- All welded construction
- Very low inductance (< 5 nH)
- Low thermal EMF (< 3 µV/°C)
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>


STANDARD ELECTRICAL SPECIFICATIONS										
GLOBAL MODEL	SIZE	POWER RATING P ₇₀ ∘c W	TOLERANCE ± %	RESISTANCE VALUE RANGE Ω	RESISTANCE VALUES CURRENTLY AVAILABLE ⁽¹⁾ Ω	WEIGHT (typical) g				
WSBS8518P4	8518	36	5, 10	50µ to 250µ	50µ, 100µ, 125µ, 250µ	50μ = 37.9, 100μ / 125μ = 36.5, 250μ = 33.7				

Note

3D Models

⁽¹⁾ Other values may be available, contact factory

TECHNICAL SPECIFICATIONS						
PARAMETER	UNIT	RESISTOR CHARACTERISTICS				
		\pm 200 for 50 $\mu\Omega$				
Temperature coefficient	ppm/°C	± 175 for 100 μΩ, 125 μΩ				
		\pm 110 for 250 $\mu\Omega$				
Temperature coefficient (element material)	ppm/°C	± 20				
Operating temperature range	°C	-65 to +170				
Maximum current rating	А	(P/R) ^{1/2}				



Revision: 26-Feb-2019

1 For technical questions, contact: <u>ww2cresistors@vishay.com</u> Document Number: 30393


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



www.vishay.com

Vishay Dale

DIMENSIONS in inches (millimeters)




Note

• Plating on top / bottom is Sn 2.5 µm to 8.0 µm over Ni 0.5 µm to 4.0 µm, edges are not plated


RESISTANCE VALUE (μΩ)	ELEMENT MATERIAL	A REFERENCE	B ± 0.005 (± 0.13)
50	Mn-Cu	0.145 (3.68)	0.357 (9.07)
100	Mn-Cu	0.360 (9.14)	0.571 (14.50)
125	Mn-Cu	0.454 (11.5)	0.666 (16.9)
250	Mn-Cu	0.900 (22.86)	1.112 (28.2)

DERATING



TOLERANCES ON DECIMALS .xxx ± 0.005 (.x ± 0.1) UNLESS OTHERWISE LISTED

PULSE CAPABILITY



www.vishay.com/resistors/large-shunt-power-metal-strip-calculator/

PERFORMANCE						
TEST	CONDITIONS OF TEST	TEST LIMITS				
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	± 0.5 % ∆R				
Short time overload	5 x rated power for 5 s	± 0.5 % ΔR				
Short time overload	10 x rated power for 5 s	± 1.0 % ∆R				
Low temperature storage	-65 °C for 24 h	± 0.5 % ΔR				
High temperature exposure	1000 h at +170 °C	± 1.0 % Δ <i>R</i>				
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 0.5 % ∆R				
Mechanical shock	100 g's for 6 ms, 5 pulses	$\pm 0.5 \% \Delta R$				
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	$\pm 0.5 \% \Delta R$				
Load life	1000 h at +70 °C, 1.5 h "ON", 0.5 h "OFF"	± 1.0 % ∆R				
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7b not required	± 0.5 % ΔR				

Revision: 26-Feb-2019

Document Number: 30393



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.