


NOTE:

- 1. ALL DIMENSIONS IN MM [INCH]
- 2. GENERAL TOLERANCE: $X.X = \pm 0.4$

 $X.XX = \pm 0.25$

- 3. TERMINAL NUMBERS FOR REF ONLY
- 4. PLATING MATERIAL: GOLD
- 5. RATING: SWITCH: 25mA @ 24VDC CARRY: 100mA @ 50VDC
- 6. OPERATING LIFE: 2,000 CYCLES, EACH CIRCUIT
- 7. INSULATION RESISTANCE: 100 M Ω min. @ 500VDC
- 8. DIELECTRIC STRENGTH: 500 V RMS @SEA LEVEL.
- 9. OPERATING FORCE: 1,000gf MAX.
- 10. OPERATING TEMP: -40°C to 85°C
- 11. CONTACT RESISTANCE: INITAL: 50m Ω TYP. @ 2-4VDC @ 100mA
- ▲ 12. PART SUPPLIED WITH ALL POLES IN THE "OFF" POSITION.
- 13. ▲ DENOTES CRITICAL PARAMETER.
- 14. 2011/65/EU (ROHS) COMPLIANT



F	23022	update PCB Layout	9/27/17	MW			
Е	22982	Redrawn, New Switch Body	8/8/17	rc			
REV	PCR NO DESCRIPTION		DATE	BY			

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E+SWITCH®							
TITLE KAS2108E							
SCALE 2:1	DATE 8/8/2017	DR rc	DWG N321080	REV F			