Niobium Oxide Capacitor







FEATURES

- Multi-anode Construction
- Super Low ESR
- 100% Surge Current Tested
- Non-Burn Safe Technology
- CV Range: 220-680µF / 1.8-6.3V
- IBM Global Approval Received in 2004
- Elektra Award Received in 2005

APPLICATIONS

High Power Low Voltage Industrial Power Supplies




LEAD-FREE COMPATIBLE COMPONENT












NOM MULTIANODE CONSTRUCTION

millimeters (inches)

MARKING

ECASE




CASE DIMENSIONS:


Code	EIA Code	EIA Metric	L±0.20 (0.008)	W+0.20 (0.008) -0.10 (0.004)	H+0.20 (0.008) -0.10 (0.004)	W ₁ ±0.20 (0.008)	A+0.30 (0.012) -0.20 (0.008)	S Min.	
E	2917	7343-43	7.30 (0.287)	4.30 (0.169)	4.10 (0.162)	2.40 (0.094)	1.30 (0.051)	4.40 (0.173)	

W₁ dimension applies to the termination width for A dimensional area only.

R

HOW TO ORDER











004 = 4Vdc 006 = 6.3Vdc





ESR in $m\Omega$

TECHNICAL SPECIFICATIONS

Technical Data:	All technical data relate to an ambient temperature of +25°C is not stated								
Capacitance Range:	220 μF to 680 μF								
Capacitance Tolerance:			±20%						
Leakage Current DCL:		0.02CV							
Rated Voltage DC (V _R)	≤ +85°C:	1.8	2.5	4	6.3				
Category Voltage (V _C)	≤ +125°C:	0.9	1.3	2	3				
Surge Voltage (V _s)	≤ +85°C:	2.3	3.3	5.2	8				
Surge Voltage (V _s)	≤ +125°C:	1.2	1.7	2.6	4				
Temperature Range:		-55°C to	+125°C						
Reliability:	0.2% per 1000 hours at 85°C, V _R , 0.1Ω/V series impedance, 60% confidence level								
		Meets re	eguiremer	nts of AE	C-0200				





CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capac	itance	Rated Voltage DC (V _R) to 85°C							
μF	Code	1.8V (x)	2.5V (e)	4.0V (G)	6.3V (J)				
220	227				E(40)				
330	337			E(35)	E(23,35)				
470	477		E(30)	E(23,30)					
680	687	E(23)	E(23)						

Released ratings, (ESR ratings in mOhms in parentheses)

Note: Voltage ratings are minimum values. AVX reserves the right to supply

higher voltage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

AVX	Case	Capacitance	Rated Voltage	Rated Temperature (°C)	Category Voltage (V)	Category Temperature (°C)	DCL Max. (μA)	DF Max. (%)	ESR Max. @ 100kHz (mΩ)	100kHz RMS Current (A)			MSL
Part No.	Size	(μF)	(V)							25°C	85°C	125°C	IVISL
1.8 Volt @ 85°C													
NOME687M001#0023	E	680	1.8	85	0.9	125	24.5	6	23	3.753	3.378	1.501	3
2.5 Volt @ 85°C													
NOME477M002#0030	Е	470	2.5	85	1.3	125	23.5	10	30	3.286	2.958	1.315	3
NOME687M002#0023	E	680	2.5	85	1.3	125	34	6	23	3.753	3.378	1.501	3
					4 Volt @	9 85°C							
NOME337M004#0035	E	330	4	85	2	125	26.4	8	35	3.043	2.738	1.217	3
NOME477M004#0023	E	470	4	85	2	125	37.6	6	23	3.753	3.378	1.501	3
NOME477M004#0030	E	470	4	85	2	125	37.6	6	30	3.286	2.958	1.315	3
6.3 Volt @ 85°C													
NOME227M006#0040	E	220	6.3	85	3	125	26.4	12	40	2.846	2.561	1.138	3
NOME337M006#0023	E	330	6.3	85	3	125	39.6	6	23	3.753	3.378	1.501	3
NOME337M006#0035	E	330	6.3	85	3	125	39.6	6	35	3.043	2.738	1.217	3

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts.

DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 125 times catalog limit post mounting.

For typical weight and composition see page 274.

NOTE: AVX reserves the right to supply higher voltage ratings or tighter tolerance part in the same case size, to the same reliability standards.





QUALIFICATION TABLE


TEST			NOS series ((Temperature range -55°C to +125°C)								
1531		Conditio	n	Characteristics								
			Visual examination	no visibl	no visible damage							
		d voltage (Ur) at 85°C		DCL	initial lin	initial limit						
Endurance		c) at 125°C for 2000 h e of ≤0.1Ω/V. Stabilize		ΔC/C	within ±	within ±10% of initial value						
		e of \$0.107 v. Stabilize urs before measuring.	at room temperature	DF	initial lim	initial limit						
		3		ESR	1.25 x in	1.25 x initial limit						
				Visual examination	no visibl	e damage						
	Store at 1	25°C, no voltage appli	ed for 2000 hours	DCL	initial lim	initial limit						
Storage Life		it room temperature fo		ΔC/C	within ±	within ±10% of initial value						
	measuring	J .		DF	initial lim	initial limit						
				ESR	1.25 x in	1.25 x initial limit						
				Visual examination	no visib	no visible damage						
	Store at 6	5°C and 95% relative h	umidity for 500 hours	DCL	1.5 x ini	1.5 x initial limit						
Humidity			e at room temperature	ΔC/C	within ±	within ±10% of initial value						
	and humic	dity for 1-2 hours befor	e measuring.	DF	1.2 x ini	1.2 x initial limit						
				ESR	1.25 x ir	1.25 x initial limit						
				Visual examination	_	no visible damage						
	A malu rata	d voltoge (Ur) at 0500	OE% relative humaidity	DCL		2 x initial limit						
Biased Humidity	Apply rated voltage (Ur) at 85°C, 85% relative humidity for 1000 hours. Stabilize at room temperature and humidity for 1-2 hours before measuring.			ΔC/C		within ±10% of initial value						
Diasca Flammarty				DF		1.2 x initial limit						
				ESR		1.25 x initial limit						
	Step	Temperature°C	Duration(min)	LOIX	+20°C	-55°C	+20°C	+85°C	+125°C	+20°C		
	1	+20	15	DOI	1L*		1L*			1L*		
Temperature	2	-55	15	DCL		n/a		12 x IL*	15xIL*			
Stability	3 4	+20 +85	15 15	ΔC/C	n/a	+0/-10%	±5%	+10/-0%	+12/-0%			
·	5	+125	15	DF	IL*	1.5 x IL*	IL*	1.5 x IL*	2xIL*	IL*		
	6	+20	15	ESR	1.25 x IL*	2.5 x IL*	1.25 x IL*	1.25 x IL*	1.25 x IL*	1.25 x IL*		
				Visual examination	no visibl	no visible damage						
_		category voltage (Uc)		DCL	initial lim	initial limit						
Surge		duration 6 min (30 sec) through a charge / di		ΔC/C	within ±	within ±5% of initial value						
Voltage	of 10000) tillough a charge / til	scharge resistance	DF	initial lim	initial limit						
				ESR	1.25 x in	1.25 x initial limit						
				Visual examination	no visib	no visible damage						
				DCL	initial lir	initial limit						
Mechanical	MIL-STD-2	202, Method 213, Cond	lition F	ΔC/C	within ±	within ±5% of initial value						
Shock		,		DF	initial lir	initial limit						
				ESR		1.25 x initial limit						
				Visual examination	no visib	le damage	!					
				DCL		initial limit						
Vibration	MIL-STD-2	202, Method 204, Cond	lition D	ΔC/C		within ±5% of initial value						
		,		DF DF		initial limit						
				ESR		1.25 x initial limit						

^{*}Initial Limit

Niobium Oxide Capacitor



AVX SOLID ELECTROLYTIC CAPACITOR ROADMAP



FIVE CAPACITOR CONSTRUCTION STYLES



SERIES LINE UP: NIOBIUM OXIDE OxiCap® CAPACITORS

