



#### **KD3300-SERIES 3-CHANNEL DC LINEAR POWER SUPPLIES**



### **Product Description**

KD3300-Series multiple channel digital control and programmable DC power supplies take full advantage of KORAD's consistent top quality in the field of R&D and production of the power supplies. The line features digital panel control, large LED, bright LED indicators, high output resolution, USB & RS232 remote control, intelligent temperature-controlled fan and more.

#### **Key Features**

- 30VX2.5V/3.3V2.5V
- 10mV/1mAhigh accuracy resolution
- Shutdown memory
- Complete digital control
- Industrial grade, with load for a long time
- Intelligent temperature-controlled fan
- Compact design

- Over-current protection
- Output ON/OFF control
- Knob LOCK function to avoid improper operation
- Optional interfaces: LAN, USB & Rs232





## TECHNICAL DATASHEET



# **Specifications**

| Models  | KD3303D/KD3303P                  | KD3305D/KD3305P                    |
|---|----------------------------------|------------------------------------|
| /oltage                                       | 0-30V/0-3A*2                     | 0-30V/0-5A*2                       |
| urrent  | 5V,3.3V,2.5V/3A*1                | 5V,3.3V,2.5V/3A*1                  |
| oad Regulation                                |                                  |                                    |
| oltage /                                      | ≤0.01%+3mV                       | ≤0.01%+5mV                         |
| Current                                       | ≤0.1%+5mA                        | ≤0.1%+10mA                         |
| ine Regulation                                |                                  |                                    |
| /oltage                                       | ≤0.01%+3mV                       | ≤0.01%+3mV                         |
| Current                                       | ≤0.1%+3mA                        | ≤0.1%+3mA                          |
| etup Resolution                               |                                  |                                    |
| /oltage                                       | 10mV                             | 10mV                               |
| Current                                       | 1mA                              | 1mA                                |
| Setup Accuracy(25°C ± 5°C)                    |                                  |                                    |
| /oltage                                       | ≤0.5%+20mV                       | ≤0.5%+20mV                         |
| Current                                       | ≤0.5%+5mA                        | ≤0.5%+10mA                         |
| Ripple(20hz-20M)                              |                                  |                                    |
| /oltage                                       | ≤1mVrms                          | ≤2mVrms                            |
| Current                                       | ≤3mArms                          | ≤3mArms                            |
| emp.Coefficient                               |                                  |                                    |
| /oltage                                       | ≤100ppm+10mV                     | ≤100ppm+10mV                       |
| Current                                       | ≤100ppm+5mA                      | ≤100ppm+5mA                        |
| Read Back Accuracy                            |                                  |                                    |
| /oltage                                       | 10mV                             | 10mV                               |
| Current                                       | 1mA                              | 1mA                                |
| lead Back Temp.Coefficient                    |                                  |                                    |
| /oltage                                       | ≤100ppm+10mV                     | ≤100ppm+10mV                       |
| Current                                       | ≤100ppm+5mA                      | ≤100ppm+5mA                        |
| Reaction Time(10% Rated load)                 |                                  |                                    |
| /oltage Rise                                  | ≤100mS                           | ≤100mS                             |
| oltage Drop                                   | ≤100mS                           | ≤100mS                             |
| oad Regulation of Parallel                    |                                  |                                    |
| oltage  | ≤(                               | 0.1%+0.2V                          |
| oad Regulation of Series                      |                                  |                                    |
| voltage                                       | ≤(                               | 0.1%+0.2V                          |
| CH3 Soecifications                            |                                  |                                    |
| /oltage Accuracy                              | ±50mV                            |                                    |
| oad Regulation                                | ±50mV                            |                                    |
| Accessories                                   |                                  |                                    |
| lser manual,power cord(KD3303D & KD3305D      |                                  |                                    |
| Jser manual, power cord, USB cable & software |                                  |                                    |
| nterfaces(for programmable models KD3303P     | & KD3305P)                       |                                    |
| JSB,RS232 & LAN                               |                                  |                                    |
| Weight and Dimension                          | 7.8kg/146mm(W)*252mm(H)*375mm(D) | 10.33kg/146mm(W)*252mm(H)*375mm(D) |



