

### UltraTEC™ UT Series Thermoelectric Cooler

The UT15-24-F2-5252-TB-RT-W6 is a high heat flux density thermoelectric cooler. The thermoelectric module is assembled with a large number of semiconducting thermoelectric couples to achieve a higher heat pumping capacity than standard single stage thermoelectric coolers. It has a maximum Qc of 234 Watts when  $\Delta T=0$  and a maximum  $\Delta T$  of 68.9 °C at Qc = 0.


#### **Features**

- High heat pump density
- Precise temperature control
- Reliable solid-state operation
- No sound or vibrationDC operation
- RoHS-compliant

#### **Applications**


- Thermoelectric Coolers and Assemblies for Medical Applications
- Thermoelectric Coolers for Handheld Cosmetic Lasers
- Industrial Laser Cooling
- Peltier Cooling for Digital Light Processors







Note: Allow 0.020 in [0.5 mm] around perimeter of the thermoelectric cooler and lead wire attachment to accommodate sealant


## **ELECTRICAL AND THERMAL PERFORMANCE**













## **SPECIFICATIONS\***

**Hot Side Temperature** 

 $Qcmax (\Delta T = 0)$ 

 $\Delta T max (Qc = 0)$ 

Imax (I @ \Darmax)

Vmax (V @ ΔTmax)

**Module Resistance** 

**Max Operating Temperature** 

Weight

<sup>\*</sup> Specifications reflect thermoelectric coefficients updated March 2020

27.0 °C	35.0 °C	50.0 °C
234.0 Watts	241.1 Watts	253.7 Watts
68.9°C	71.8°C	77.0°C
15.2 Amps	15.1 Amps	14.9 Amps
26.0 Volts	27.0 Volts	28.8 Volts
1.60 Ohms	1.66 Ohms	1.79 Ohms
80 °C		
47.0 gram(s)		

## **FINISHING OPTIONS**

Suffix Thickness		Flatness / Parallelism	<b>Hot Face</b>	<b>Cold Face</b>	<b>Lead Length</b>
ТВ	$3.300 \pm 0.013 \text{ mm}$ $0.130 \pm 0.001 \text{ in}$	0.013 mm / 0.013 mm 0.0005 in / 0.0005 in	Lapped	Lapped	152.4 mm 6.00 in

## **SEALING OPTIONS**

Suffix	Sealant	Color	<b>Temp Range</b>	Description
RT	RTV	White	-60 to 204°C	Non-corrosive, silicone adhesive

# **NOTES**

- 1. Max operating temperature: 80°C
- 2. Do not exceed Imax or Vmax when operating module
- 3. Reference assembly guidelines for recommended installation

Any information furnished by Laird and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Laird. All specifications are subject to change without notice. Laird assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Laird products are sold subject to the Laird Terms and Conditions of sale (including Laird's limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2020 Laird Thermal Systems GmbH. All Rights Reserved. Laird, Laird Technologies, Laird Thermal Systems, the Laird Logo, and other word marks and logos are trademarks or registered trademarks of Laird Limited or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.

Date: 04/24/2020