

## .062 MINIATURE PIN TERMINALS

## 1.0 SCOPE

This specification covers the .062 diameter pin and socket terminal product line with their associated connector housings designed for use on copper wire.

## 2.0 PRODUCT DESCRIPTION

The product line described in general terms is found in catalog M200. The connector is made in 1, 2, 3, 4, 5, 6, 8, 9, 12, 15, 24 and 36 circuit sizes. Connector plugs and receptacles are nylon and provided with optional mounting ears for snap-in panel mounting. The housing accepts wire ranges 30 thru 18 AWG and insulation diameters of .040 thru .120 inches.

## 3.0 RECOGNIZED AGENCY APPROVALS

- 3.1 Underwriters' Laboratories: File #E29179.
- 3.2 Canadian Standards Association: File #LR 19980.

#### 4.0 MECHANICAL SPECIFICATIONS

#### 4.1 Materials, dimensions

<u>REVISION:</u> E	ECR/ECN INFORMATION: EC No: UCP2008-0413 DATE: 2007 / 09 / 05	-	TITLE: PRODUCT SPECIFICATION COMING CONNECTOR					
DOCUMENT NU	MBER:	CREATED / REVISED BY:	CHECKED BY:	APPROV	/ED BY:			
	PS-02-06	HM/MSIBARRA	DMORGAN	SMIL	LER			
			TEN	IPLATE FILENAME: PRODUCT	T_SPEC[SIZE_A](V.1).DOC			




Circuits (a)				1		2	2		3		4		4		5	(	5	1	8		3	1	2	15	5(b)	2	4	36	5(c)
RECEPTACLE			1	625-1		162	5-2	162	25-3	163	25-4	20	04	16:	25-5	162	25-6	16	549	16.	25-9	162	25-12	15	25-15	162	25-24	1	772
			R	P		R	Р	R	Р	R	Р	R	P	R	Р	R	P	R	P	R	P	R	P	R	P	R	P	R	P
A			N/A	N/A	.2	265	.318	.265	.318	.260	.312	.400	.465	.265	.318	.505	.607	.330	N/A	.552	.615	.563	.614	.563	.614	.715	.765	.707	.825
В		•	N/A	N//	٩ .5	505	.609	.650	.754	.785	.865	.506	.615	.940	1.044	.552	.615	1.715	N/A	.650	.752	.795	.903	.934	1.042	1.079	1.182	1.677	1.79
C			N/A	N//	A N	I/A	.295	N/A	.295	.207	.292	N/A	.537	N/A	.305	N/A	.600	.310	.268	.530	.530	.530	.530	.527	.550	.665	.693	.855	.802
D	•	•	.781	.750	) .7	781	.750	.781	.750	.781	.750	.750	.750	.781	.750	.781	.750	.781	.750	.781	.750	.781	.750	.781	,750	.750	.7.50	.781	.750
E			.192 Dia	N//	.1	192	.295	.192	.295	.192	.297	.339	.537	.192	.305	.494	.600	.2.20	,308	.494	.592	.489	.592	.487	.590	.634	.742	.689	.802
F			N/A	.298 Dia	3 .3	340	.443	.485	.588	.630	.734	.339	.537	.775	.888	.344	.450	1.505	1.595	.489	.587	.634	.737	.770	.876	.918	1.027	1.508	1.61
G			N/A	N/#	.3	395	.375	.395	.375	.395	.375	.370	.350	.395	.375	.395	.395	.395	.375	.395	.375	.395	.375	,395	.375	.370	,350	395	.375
Н		•	N/A	N/A	.1	88	.188	.188	.188	.188	.188	.250	.250	.188	.188	.375	.375	.310	N/A	.375	.375	.375	.375	.375	.375	.500	.500	.625	,625
I			N/A	.200 Dia	) N	/A	.348	N/A	.488	N/A	.635	N/A	.340	N/A	.780	N/A	.345	N/A	1.505	N/A	.490	N/A	.635	N/A	.774	N/A	.928	N/A	N/A
J			N/A	N/A	.2	21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21	.21

4.1.1 Standard .062" molded nylon connectors .145 inch center to center spacings

Available with strain relief 1815: Collar dia. .230" - Part 15-04-0201; .342" - Part 1504-0206; .280" - Part 15-04-0208.

-Available with strain relief 1864: Collar dia. .415" - Part 15-04-0202; .500" - Part 15-04-0203. Dimensions C to J are included for reference only. Dimensions subject to nominal variations. N/A - Not available or not applicable.





- 4.1.2 Terminals: Refer to sales drawing 02-06-\* (SD-1560 Series)
- 4.2 Temperature Rise: Maximum Temperature rise is 30°C for all connector assemblies when used at their maximum rated current (Underwriters' Laboratories requirement).

## 4.3 Temperature:

- 4.3.1 Operating Temperature: -40°C to +105°C
- 4.3.2 Non-operating Temperature: -30°C to +60°C

## 4.4 Humidity

- 4.4.1 Test Method exposure shall be 96 hours with a 95% to 100% relative humidity and a temperature of 100° ± 5% F. A one ampere current shall be placed through a male/female assembly within one hour after removing from the Humidity Chamber (18 AWG stranded wire).
- 4.4.2 Requirement the maximum MV drop across both terminals shall be 15 MV. The probe should be placed on the wire approximately 1" from the crimp barrel.

## 4.5 Engage/Disengage forces for standard terminal (.008 stock 70/30 brass):

#### 4.5.1 Plug and Receptacle Connector

	AVG. SINGLE (	AVG. SINGLE CIRCUIT FORCES:									
No. of											
<b>Cycles</b>	<u>Engage</u>	<b>Disengage</b>									
1st	2.0 lbs.	1.8 lbs.									
10th	1.3 lbs.	1.0 lbs.									

<u>REVISION:</u>	ECR/ECN INFORMATION: EC No: UCP2008-0413 DATE: 2007 / 09 / 05	TITLE: PRC		<u>SHEET No.</u> <b>3</b> of <b>5</b>	
DOCUMENT NU		<u>CREATED / REVISED BY:</u> HM/MSIBARRA	CHECKED BY: DMORGAN	APPROV SMIL	
			TEN	IPLATE FILENAME: PRODUCT	F SPECISIZE AI(V.1).DOC



## 4.5.2 Terminal Insertion and Retention in Connector Housing

	INSERTION	RETENTION
Male and Female	2.5 lbs.	20 lbs. min. using 18 AWG (by wire
	2.5 IDS.	pull test method)

# 4.6 Terminal crimp strength – minimum pull out force in pounds is given in the following table for various wire sizes (AWG)

WIRE GAGE	18	20	22	24	26	28	30
PULL OUT FORCE (LBS.)	20	15	10	8	5	3	2

## 5.0 ELECTRICAL SPECIFICATIONS

## 5.1 Rated Voltage, currents

**5.1.1** Initial resistance thru 2 adjacent terminals is 2 milliohms.

Circuits (a)	1	2	3	4	4	5	6	8	9.	12	15(b)	24	36(c)
RECEPTACLE	1625-1	1625-2	1625-3	1625-4	2004	1625-5	1625-6	1649	1625-9	1625-12	1625-15	1625-24	1772
Max. Amp.	5	5	5	5	5	5	5 -	5	5	5	5	4	4
Max. Volts	250	250	250	250	250	250	250	250	250	250	250	250	250
Holding Tabs Only	03-06-1011	03-06-1023	03-06-1032	03-06-1042	03.06-1044	03-06-1056	03-06-1062	N/A	03-06-1092	03-06-1122	03.06-1152	03-06-1242	03.06.1362
WITH EARS AND TABS	N/A	03.06.1022	03-06-1031	03.06-1041	03.06.1043	03.06.1055	03.06-1061	03.06-1081	03.06-1091	03.06.1121	03.06.1151	03.06.1241	03-06-1361
•				•							-		
PLUG	21	2				1							
Max. Amp	5	5	5	5	5	5	5	5	5	5	5	4	4
Max. Volts	250	250	250	250	250	250	250	250	250	250	250	250-	250
With Mounting Ears Only	N/A	03-06-2022	03.06.2031	03.06.2041	03-06-2043	03.06.2054	03.05-2062	N/A	03.06.2091	03.06.2121	03-06-2151	03.06.2241	D3.06.2361
Without Mounting Ears	03.06.2011	03.06.2023	03.06.2032	03.06.2042	03.06.2044	03.06.2055	03.06.2061	03.06.2081	03.06.2092	03.06.2122	0306.2152	03.06.2242	03.06.2362
REVISION:	ECR/ECN I	NFORMATIO	<u>SN:</u>	TITLE:		P			CIFICAT			Sł	HEET No.
E	C No: UCP	2008-0413				•		-		-			<b>4</b> of <b>5</b>
	DATE: <b>2007</b>	/ 09 / 05					COMIN						<b>-</b> 01 <b>J</b>
DOCUMENT NUMBER:				CREATED / REVISED BY:				CHECKED BY:			APPROVED BY:		
PS-02-06				HM/MSIBARRA DMORGAN SMIL								SMILLER	
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE									SIZE_A](V.1).DC				



- **5.1.2** Initial resistance thru 3 interconnected terminals is 3 milliohms.
- **5.1.3** Initial resistance thru 15 interconnected terminals is 15 milliohms.
- **5.1.4** After Humidity Cycling per Mil. Std. 202E. Method 106C or 96 hours @ 120 C oven aging, terminal resistance change shall not exceed 2.0 times the initial values.
- 5.2 Terminal resistance (voltage drop measured at one amp) (18AWG stranded wire).

1)  $1^{st}$  Terminal Engagement3.2 MV  $\pm$  10%2)  $10^{th}$  Terminal Engagement3.4 MV  $\pm$  10%

The above voltage is measured across the friction connection of pin. The voltage drop is approximately 1 MV greater when including the mated terminals plus both crimps. In this case the probes should be placed on the wire approximately 1" from the crimp barrel.

#### 5.3 High Voltage Test

Terminals mounted in a connector must withstand 1500 volts RMS applied between adjacent terminals for 60 seconds without breakdown.

#### 6.0 REFERENCE

QC spec M-50-003

REVISION:	ECR/ECN INFORMATION:	PRC	SHEET No.		
Е	<u>EC No:</u> UCP2008-0413	C C	<b>5</b> of <b>5</b>		
•	<u>DATE:</u> 2007 / 09 / 05				
DOCUMENT NU	MBER:	CREATED / REVISED BY:	CHECKED BY:	<u>APPROV</u>	<u>/ED BY:</u>
	PS-02-06	HM/MSIBARRA	DMORGAN	SMIL	LER
			TEN	IPLATE FILENAME: PRODUCT	SPEC[SIZE_A](V.1).DOC